
Stainless steel bevel gear

Ratio 1:1

Stainless steel 304L

- ***Module 0.8 to 2.5***
- *Pressure angle 20°*
- *Teeth Gleason*
- *Material:*
  stainless steel 304L
- *Two gears must be ordered to make a pair*





TORQUE AND POWER INDICATION	For 20 teeth at 1000 rpm					
	2.5 MOD	2.0 MOD	1.5 MOD	1.25 MOD	1.0 MOD	0.8 MOD
Torque (Nm)	4.30	2.20	0.94	0.71	0.57	0.14
Power (kW)	0.455	0.231	0.097	0.08	0.03	0.015

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-12%	On request

Part number	Teeth Z	Module	ØP	E	ØD	ØA	ØM	F	G	H	ØR	T	Price each 1 to 5
SSB0.8-16	16		12,80	20	13,93	6	10	16,00	12,21	3,00	M3	7,00	44,47 €
SSB0.8-25	25	**0,8**	20,00	20	21,13	6	16	13,35	8,00	4,24	M3	5,00	48,27 €
SSB0.8-30	30		24,00	20	25,13	6	20	11,96	6,00	5,09	M3	4,00	52,17 €
SSB1-20	20	**1**	20,00	25	21,41	8	18	18,45	14,00	4,24	M4	8,00	53,13 €
SSB1-30	30		30,00	25	31,41	8	26	14,95	8,00	6,35	M4	5,00	60,39 €
SSB1.25-20	20	**1,25**	25,00	23	26,70	8	22	15,27	9,00	6,00	M4	3,50	55,81 €
SSB1.25-30	30		37,50	36	39,30	10	30	23,47	13,50	8,00	M4	5,00	63,23 €
SSB1.5-20	20	**1,5**	30,00	35	32,12	10	26	25,17	18,00	6,35	M4	10,00	57,62 €
SSB1.5-30	30		45,00	35	47,12	10	38	19,92	9,00	9,50	M4	5,00	70,91 €
SSB2-20	20	**2**	40,00	42	43,00	12	34	29,00	19,00	8,50	M5	10,00	67,40 €
SSB2-30	30		60,00	42	63,00	12	50	21,87	7,00	12,70	M5	4,00	84,44 €
SSB2.5-16	16	**2,5**	40,00	50	43,50	15	35	36,80	27,50	8,00	M5	15,00	68,91 €
SSB2.5-25	25		62,50	50	66,00	15	55	30,50	15,00	15,00	M5	8,00	97,78 €

Dimensions in mm

Our other products


GBSz

Cylindrical ballscrew nut, Cylindrical leadscrew nut


ACLEFS

Floor anchor for aluminium profile, Adjustable


ACL-PR

Joining plate for aluminium profile, Right angled connection


NCT

Square tube connector, Fixed angle


BMF

Knurled knob - female, Knurled - blind


RURt

Swivel castor with central hole, Polyurethane - Aluminium rim (Free


PR85

Articulated foot Ø83, Ø 83


RPCtcss

Swivel castor with central hole, Stainless steel - Polyamide - with ...


PRF_GAL

Roller for aluminium profile, Flat roller


RIMtce

Locking castor, with central hole


CHML63

Worm and wheel gear reducer, up to 138



SHTC

Drylin® Linear table, Maintenance free

Complementary products


MEB

Moulded plastic bevel gear (nylon), 1:1


B

Steel bevel gear, 1:1