
Shock absorber - stop collar

STC


Mounting accessory

- ***Stop collar for shock absorber***
- *Please note: for certain shock absorbers, the use of this stop collar is essential*





STC10 to 12



STC14 to 25



Typical application

DISCOUNTS

Qty	1+	4+	6+
Disc.	List	-10%	On request

Part number	Ød1	Ød5	Ød6	b3	b4	b5	AF	For shock-absorber	Stock*	Price each 1 to 3
STC10	M10x1	-	14,3	20	-	-	-	MC25	✔	13,42 €
STC12	M12x1	-	16,0	20	-	-	-	MC75	✔	13,42 €
STC14	M14x1,5	14,5	18,0	19	12	6	13	MC150	-	14,57 €
STC20	M20x1,5	20,5	25,0	25	12	8	22	RMSA500	-	21,71 €
STC25	M25x1,5	25,5	32,0	45	16	10	27	RMSA600-900	✔	30,86 €

**Depending on availability - Dimensions in mm*

Our other products


SCE_SS

Stainless steel U-shaped clamp, Stainless seel


CLSCLP_SS

Clevis components, short version, Stainless steel - short range


BG


Oldham coupling, With set screw


PTRSS

Idler chain sprocket, For hostile environments


RBS

Dynamic washer DIN2093, Steel


IN1

Internal gear, Machined plastic (delrin)


PDM_PDV

Detectable plastic palm grip, by metal detectors


BAG-MISS

Split shaft collar with clamp lever, Stainless steel


CHA138

Screwed hinge with threaded insert, 138 degrees


G3

Steel spur gear, Steel 20NCD2


DILC

Indexing plunger with cam, with cam


MAX22

Motor-gearbox 12V and 24V DC, from 0,07 to 0,2Nm

Complementary products


RMSA

Adjustable shock-absorber, Adjustable


MC

Self-compensating shock-absorber, Self-compensating - without adjust...