Size XS Eco

T-type timing pulley


Moulded nylon PA6

Pitch T2.5

Belt width 6mm

- **Positioning pulley**
- Pitch 2.5mm (T2.5)
- Material:
  Moulded PA6 nylon reinforced with 30% glass fibre
- **We are unable to modify these parts**

Economy range




ØA: Pilot bore must be finished

Info

- Moulded pre-bore must be machined to suit the application
- *Pilot bore dimension given as a guide only

Accessories

- T2,5 belt *(tome 4 p.53)*



1 flange

DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-12%	-25%	-33%	-37%	On request

Part number	Z teeth	ØD	ØM	Pilot bore not guaranteed ØA*(mm)	ØE	Stock*	Price each 1 to 5
10T2.5-10-N1F	10	7,40	12	3	12	✔	5,45 €
12T2.5-10-N1F	12	9,00	12	3	12	✔	5,45 €
15T2.5-10-N1F	15	11,40	12	2	15	-	On request
16T2.5-10-N1F	16	12,18	12	2	16	✔	On request
22T2.5-10-N1F	22	17,00	14	4	22	-	On request
25T2.5-10-N1F	25	19,35	14	3	24	-	On request
26T2.5-10-N1F	26	20,14	16	4	26	-	On request
30T2.5-10-N1F	30	23,35	18	5	30	✔	9,05 €
32T2.5-10-N1F	32	24,95	18	5	32	-	On request
33T2.5-10-N1F	33	25,70	18	5	32	-	On request

*Depending on availability - Dimensions in mm

T-type timing pulley


Stock* Alu Eco


Pitch T2,5

Aluminium

For 6mm belts

- **For use with T2.5 belts**
- Pitch 2.5mm
- Material: Aluminium





Economy range

Info

- Pilot bore size given as indication, may vary between batches.
- Will require re-machining by customer
- **We are unable to modify this product**

Accessories

- T2.5 belts **(tome 4 p.53)**
- GTC tension rollers **(tome 4 p.146)**

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-12%	On request

Part number	No. of teeth	ØP PCD	ØD external	ØE flange	ØM	F	L	Pilot bore no guaranteed ØA*	Stock*	Price each 1 to 5
12T2.5-10/ECO	12	9,60	9,00	13	13	9	16	solid	✔	6,19 €
14T2.5-10/ECO	14	11,20	10,60	15	15	9	16	solid	✔	6,31 €
15T2.5-10/ECO	15	12,00	11,40	15	15	9	16	solid	-	6,67 €
16T2.5-10/ECO	16	12,80	12,20	16	16	9	16	solid	✔	7,32 €
18T2.5-10/ECO	18	14,40	13,80	17,5	10	10	16	solid	-	6,24 €
19T2.5-10/ECO	19	15,20	14,60	20	10	10	16	solid	-	6,85 €
20T2.5-10/ECO	20	16,00	15,40	20	11	10	16	solid	✔	6,82 €
22T2.5-10/ECO	22	17,60	17,00	22	11	10	16	solid	✔	6,26 €
24T2.5-10/ECO	24	19,15	18,55	22	12	10	16	4	✔	7,35 €
25T2.5-10/ECO	25	19,95	19,35	25	13	10	16	4	✔	7,44 €
26T2.5-10/ECO	26	20,75	20,15	26	14	10	16	4	✔	7,73 €
28T2.5-10/ECO	28	22,35	21,75	26	14	10	16	4	✔	8,08 €
30T2.5-10/ECO	30	23,95	23,35	26	16	10	16	6	✔	8,42 €
32T2.5-10/ECO	32	25,55	24,95	32	16	10	16	6	✔	6,46 €
36T2.5-10/ECO	36	28,75	28,10	36	20	10	16	6	✔	7,07 €
40T2.5-10/ECO	40	31,90	31,30	38	22	10	16	6	✔	7,63 €
44T2.5-10/ECO	44	35,10	34,50	-	24	10	16	6	✔	8,67 €
48T2.5-10/ECO	48	38,30	37,70	-	26	10	16	6	✔	7,92 €
60T2.5-10/ECO	60	47,85	47,25	-	34	10	16	8	✔	10,54 €

*Depending on availability - Dimensions in mm


T-type timing pulley

Aluminium

Pitch T2.5

Belt width 4mm

- **Pitch 2.5mm**
- Materials:
  Pulley: Aluminium 6082
  Flanges: Aluminum for pulleys with up to 84 teeth, steel for 85 teeth or more
- All pulleys have flanges



Options

- **Choose from 10 to 230 teeth**

bore-size, keyway
MODIFY IT!
tapped hole, pin, etc...

PT (optional)

DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-12%	-25%	On request

Part number	Z Teeth	Ø PCD	ØD	ØM	ØA	Flange ref.	ØE	Price each 1 to 5 T	Price each 1 to 5 PT
10T2.5-8	10	7,96	7,40	13	3	10 X,Y	13,00	On request	On request
12T2.5-8	12	9,55	9,00	13	3	10 X,Y	13,00		
14T2.5-8	14	11,14	10,60	18	3	16 X,Y	18,00		
15T2.5-8	15	11,94	11,40	18	3	16 X,Y	18,00		
16T2.5-8	16	12,73	12,20	18	4	16 X,Y	18,00		
18T2.5-8	18	14,32	13,80	18	4	31 X,Y	18,00		
19T2.5-8	19	15,12	14,60	20	4	32 X,Y	20,00		
20T2.5-8	20	15,92	15,40	20	4	32 X,Y	20,00		
21T2.5-8	21	16,71	16,20	20	4	32 X,Y	20,00		
22T2.5-8	22	17,51	17,00	20	4	32 X,Y	20,00		
24T2.5-8	24	19,10	18,55	13	4	12 XL	25,15		
25T2.5-8	25	19,89	19,35	13	4	12 XL	25,15		
26T2.5-8	26	20,69	20,15	13	5	12 XL	25,15		
30T2.5-8	30	23,87	23,35	20	5	16 XL	31,74		
31T2.5-8	31	24,67	24,15	20	5	18 XL	34,80		
32T2.5-8	32	25,46	24,95	20	5	18 XL	34,80		
40T2.5-8	40	31,83	31,30	24	6	21XL	39,68		
44T2.5-8	44	35,01	34,50	24	6	21XL	39,68		
48T2.5-8	48	38,20	37,70	24	6	24XL	44,70		
52T2.5-8	52	41,38	40,85	24	6	24XL	44,70		
57T2.5-8	57	45,36	44,85	24	6	28XL	51,05		
60T2.5-8	60	47,75	47,25	24	6	30XL	54,36		
80T2.5-8	80	63,66	63,16	24	6	17H	74,61		
84T2.5-8	84	66,85	66,35	24	6	18H	79,38		
↓	**Pulleys available up to this size**							↓	
230T2,5-8	**230**	**Dimensions : contact us**							

Dimensions in mm

T-type timing pulley


Alu Size XS

Pitch T2.5

Aluminium

Belt width 6mm

- **Pitch 2.5mm**
- Matierials:
  Pulley: Aluminium 6082
  Flanges: Aluminum for pulleys with up to 84 teeth, steel for 85 teeth or more
- All pulleys have flanges



Options

- **Choose from 10 to 230 teeth**

bore-size, keyway
MODIFY IT!
tapped hole, pin, etc...

DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-12%	-25%	On request

Part number	Z Teeth	Ø PCD	ØD	ØM	ØA	Flange ref.	ØE	Stock*	Price each 1 to 5 T	Price each 1 to 5 PT
10T2.5-10	10	7,96	7,40	13	3	10 X,Y	13,00		On request	On request
12T2.5-10	12	9,55	9,00	13	3	10 X,Y	13,00			
14T2.5-10	14	11,14	10,60	18	3	16 X,Y	18,00			
15T2.5-10	15	11,94	11,40	18	3	16 X,Y	18,00			
16T2.5-10	16	12,73	12,20	18	4	16 X,Y	18,00			
18T2.5-10	18	14,32	13,80	18	4	31 X,Y	18,00			
19T2.5-10	19	15,12	14,60	20	4	32 X,Y	20,00			
20T2.5-10	20	15,92	15,40	20	4	32 X,Y	20,00			
21T2.5-10	21	16,71	16,20	20	4	32 X,Y	20,00			
22T2.5-10	22	17,51	17,00	20	4	32 X,Y	20,00			
24T2.5-10	24	19,10	18,55	13	4	12 XL	25,15			
25T2.5-10	25	19,89	19,35	13	4	12 XL	25,15			
26T2.5-10	26	20,69	20,15	13	5	12 XL	25,15			
30T2.5-10	30	23,87	23,35	20	5	16 XL	31,74			
31T2.5-10	31	24,67	24,15	20	5	18 XL	34,80			
32T2.5-10	32	25,46	24,95	20	5	18 XL	34,80			
40T2.5-10	40	31,83	31,30	24	6	21XL	39,68			
44T2.5-10	44	35,01	34,50	24	6	21XL	39,68			
48T2.5-10	48	38,20	37,70	24	6	24XL	44,70			
52T2.5-10	52	41,38	40,85	24	6	24XL	44,70			
57T2.5-10	57	45,36	44,85	24	6	28XL	51,05			
60T2.5-10	60	47,75	47,25	24	6	30XL	54,36			
80T2.5-10	80	63,66	63,16	24	6	17H	74,61			
84T2.5-10	84	66,85	66,35	24	6	18H	79,38			
↓	**Pulleys available up to this size**								↓	
230T2,5-10	**230**	**Dimensions : contact us**								

*Depending on availabiliity - Dimensions in mm

T-type timing pulley

Aluminium

Pitch T5


Economy range


For 10mm belts

- ***For use with T5 belts***
- *Pitch 5mm*
- *Material:*
  Aluminium

Info

- *Pilot bore size given as indication, may vary between batches.*
- *Will require re-machining by customer*
- ***We are unable to modify this products***





Supplied with a pilot bore

Accessories

- ***T5** belts **(tome 4 p.54)***
- ***GTC** tension rollers **(tome 4 p.146)***

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-12%	On request

Part number	No. of teeth	ØP PCD	ØD external	ØE flange	ØM	F	L	Pilot bore no guaranteed ØA*	Stock*	Price each 1 to 5
10T5-15/ECO	10	15,92	15,05	19,5	8	15	21	solid	✔	3,76 €
12T5-15/ECO	12	19,10	18,25	23	11	15	21	solid	✔	4,24 €
14T5-15/ECO	14	22,29	21,45	25	13	15	21	solid	✔	4,75 €
15T5-15/ECO	15	23,88	23,05	28	16	15	21	6	✔	5,18 €
16T5-15/ECO	16	25,47	24,60	32	18	15	21	6	✔	5,67 €
18T5-15/ECO	18	28,65	27,80	32	20	15	21	6	✔	5,94 €
19T5-15/ECO	19	30,25	29,40	36	22	15	21	6	✔	6,49 €
20T5-15/ECO	20	31,83	31,00	36	23	15	21	6	✔	6,75 €
22T5-15/ECO	22	35,02	34,15	38	24	15	21	6	✔	7,58 €
24T5-15/ECO	24	38,21	37,40	42	26	15	21	6	✔	8,10 €
25T5-15/ECO	25	39,80	38,95	44	26	15	21	6	✔	8,93 €
26T5-15/ECO	26	41,39	40,60	44	26	15	21	6	✔	9,53 €
27T5-15/ECO	27	42,98	42,20	48	30	15	21	8	✔	9,96 €
28T5-15/ECO	28	44,58	43,75	48	32	15	21	8	✔	10,43 €
30T5-15/ECO	30	47,76	46,95	51	34	15	21	8	✔	11,27 €
32T5-15/ECO	32	50,94	50,10	54	38	15	21	8	✔	12,51 €
36T5-15/ECO	36	57,31	56,45	64	38	15	21	8	✔	14,63 €
40T5-15/ECO	40	63,66	62,85	66,5	40	15	21	8	✔	16,38 €
42T5-15/ECO	42	66,86	66,00	70	40	15	21	8	-	17,65 €
44T5-15/ECO	44	70,05	69,20	-	45	15	21	8	-	17,49 €
48T5-15/ECO	48	76,42	75,55	-	50	15	21	8	✔	19,79 €
60T5-15/ECO	60	95,52	94,65	-	65	15	21	8	✔	29,55 €

**Depending on availability - Dimensions in mm*

T-type timing pulley

Alu € Eco


Pitch T5

Aluminium

Economy range

For 16mm belts

- ***For use with T5 belts***
- *Pitch 5mm*
- *Material: Aluminium*





Supplied with a pilot bore

Info

- *Pilot bore size given as indication, may vary between batches.*
- *Will require re-machining by customer*
- ***We are unable to modify this product***

Accessories

- ***T5** belts **(tome 4 p.54)***
- ***GTC** tension rollers **(tome 4 p.146)***

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-12%	On request

Part number	No. of teeth	ØP PCD	ØD external	ØE flange	ØM	F	L	Pilot bore no guaranteed ØA*	Stock*	Price each 1 to 5
10T5-21/ECO	10	15,92	15,05	19,5	8	21	27	solid	✔	4,10 €
12T5-21/ECO	12	19,10	18,25	23	11	21	27	solid	✔	4,86 €
14T5-21/ECO	14	22,29	21,45	25	13	21	27	solid	✔	5,36 €
15T5-21/ECO	15	23,88	23,05	28	16	21	27	6	✔	5,84 €
16T5-21/ECO	16	25,47	24,60	32	18	21	27	6	✔	6,41 €
18T5-21/ECO	18	28,65	27,80	32	20	21	27	6	✔	6,85 €
19T5-21/ECO	19	30,25	29,40	36	22	21	27	6	-	7,57 €
20T5-21/ECO	20	31,83	31,00	36	23	21	27	6	✔	7,89 €
22T5-21/ECO	22	35,02	34,15	38	24	21	27	6	✔	9,05 €
24T5-21/ECO	24	38,21	37,40	42	26	21	27	6	✔	9,64 €
25T5-21/ECO	25	39,80	38,95	44	26	21	27	6	✔	10,25 €
26T5-21/ECO	26	41,39	40,60	44	26	21	27	6	-	11,55 €
27T5-21/ECO	27	42,98	42,20	48	30	21	27	8	✔	11,33 €
28T5-21/ECO	28	44,58	43,75	48	32	21	27	8	-	12,26 €
30T5-21/ECO	30	47,76	46,95	51	34	21	27	8	✔	13,07 €
32T5-21/ECO	32	50,94	50,10	54	38	21	27	8	✔	14,81 €
36T5-21/ECO	36	57,31	56,45	64	38	21	27	8	✔	17,23 €
40T5-21/ECO	40	63,66	62,85	66,5	40	21	27	8	✔	19,48 €
42T5-21/ECO	42	66,86	66,00	70	40	21	27	8	-	20,83 €
44T5-21/ECO	44	70,05	69,20	-	45	21	27	8	✔	21,53 €
48T5-21/ECO	48	76,42	75,55	-	50	21	27	8	-	24,02 €
60T5-21/ECO	60	95,52	94,65	-	65	21	27	8	✔	35,70 €

**Depending on availability - Dimensions in mm*


T-type timing pulley


Aluminium

Pitch T5

Belt width 6mm

- **Pitch 5mm**
- Materials:
  Pulley: Aluminium 6082
  Flanges: Aluminum for pulleys with up to 46 teeth, steel for 47 teeth or more
- All pulleys have flanges





Options

- **Choose from 10 to 150 teeth**



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-12%	-25%	On request

Part number	Z Teeth	PCD (mm)	ØD (mm)	ØM (mm)	ØA (mm)	Flange ref.	ØE (mm)	Price each 1 to 5 T	Price each 1 to 5 PT
10T5-11	10	15,92	15,05	12	5	11XL	23,62	On request	On request
12T5-11	12	19,10	18,25	13	5	12XL	25,15		
14T5-11	14	22,28	21,45	16	5	14XL	28,44		
15T5-11	15	23,87	23,05	16	6	14XL	28,44		
16T5-11	16	25,46	24,60	16	6	14XL	28,44		
17T5-11	17	27,06	26,20	16	6	16XL	31,74		
18T5-11	18	28,65	27,80	20	6	18XL	34,80		
19T5-11	19	30,24	29,40	20	6	18XL	34,80		
20T5-11	20	31,83	31,00	20	6	20XL	38,10		
24T5-11	24	38,20	37,80	25	6	24XL	44,70		
25T5-11	25	39,79	39,00	25	6	24XL	44,70		
30T5-11	30	47,75	46,95	30	8	28XL	51,05		
32T5-11	32	50,93	50,10	30	8	16L	55,56		
36T5-11	36	57,30	56,45	30	8	14H	61,91		
37T5-11	37	58,89	58,05	40	8	15H	66,68		
40T5-11	40	63,66	62,85	40	8	16H	69,85		
45T5-11	45	71,62	70,80	40	8	18H	79,38		
48T5-11	48	76,39	75,55	40	8	19H	82,55		
50T5-11	50	79,58	78,75	60	10	20H	85,73		
56T5-11	56	89,13	88,30	60	10	22H	95,25		
60T5-11	60	95,49	94,65	60	10	24H	103,19		
70T5-11	70	111,41	110,60	60	10	28H	119,06		
80T5-11	80	127,32	126,50	60	10	32H	134,94		
84T5-11	84	133,69	132,85	60	10	33H	139,70		
↓	Pulleys available up to this size							↓	
150T5-11	150	dimensions : contact us							

Dimensions in mm


T-type timing pulley


Alu

Pitch T5 — Aluminium

Belt width 10mm

- Pitch 5mm
- Materials:
  Pulley: Aluminium 6082
  Flanges: Aluminum for pulleys with up to 46 teeth, steel for 47 teeth or more
- All pulleys have flanges





Options

- **Choose from 10 to 150 teeth**

bore-size, keyway
MODIFY IT!
tapped hole, pin, etc...

DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-12%	-25%	On request

Part number	Z Teeth	PCD (mm)	ØD (mm)	ØM (mm)	ØA (mm)	Flange ref.	ØE (mm)	Price each 1 to 5 T	Price each 1 to 5 PT
10T5-15	10	15,92	15,05	12	5	11XL	23,62	On request	On request
12T5-15	12	19,10	18,25	13	5	12XL	25,15		
14T5-15	14	22,28	21,45	16	5	14XL	28,44		
15T5-15	15	23,87	23,05	16	6	14XL	28,44		
16T5-15	16	25,46	24,60	16	6	14XL	28,44		
17T5-15	17	27,06	26,20	16	6	16XL	31,74		
18T5-15	18	28,65	27,80	20	6	18XL	34,80		
19T5-15	19	30,24	29,40	20	6	18XL	34,80		
20T5-15	20	31,83	31,00	20	6	20XL	38,10		
24T5-15	24	38,20	37,35	25	6	24XL	44,70		
25T5-15	25	39,79	39,00	25	6	24XL	44,70		
30T5-15	30	47,75	46,95	30	8	28XL	51,05		
32T5-15	32	50,93	50,10	30	8	16L	55,56		
36T5-15	36	57,30	56,45	30	8	14H	61,91		
37T5-15	37	58,89	58,05	40	8	15H	66,68		
40T5-15	40	63,66	62,85	40	8	16H	69,85		
45T5-15	45	71,62	70,80	40	8	18H	79,38		
48T5-15	48	76,39	75,55	40	8	19H	82,55		
50T5-15	50	79,58	78,75	60	10	20H	85,73		
56T5-15	56	89,13	88,30	60	10	22H	95,25		
60T5-15	60	95,49	94,65	60	10	24H	103,19		
70T5-15	70	111,41	110,60	60	10	28H	119,06		
80T5-15	80	127,32	126,50	60	10	32H	134,94		
84T5-15	84	133,69	132,85	60	10	33H	139,70		
↓	**Pulleys available up to this size**							↓	
150T5-11	**150**	**dimensions : contact us**							

Dimensions in mm


T-type timing pulley

Aluminium

Pitch T5

Belt width 16mm

- **Pitch 5mm**
- *Materials:*
  Pulley: Aluminium 6082
  Flanges: Aluminum for pulleys with up to 46 teeth, steel for 47 teeth or more
- *All pulleys have flanges*



Options

- **Choose from 10 to 150 teeth**

bore-size, keyway
MODIFY IT!
tapped hole, pin, etc...

DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-12%	-25%	On request

Part number	Z Teeth	PCD (mm)	ØD (mm)	ØM (mm)	ØA (mm)	Flange ref.	ØE (mm)	Price each 1 to 5 T	Price each 1 to 5 PT
10T5-21	10	15,92	15,05	12	5	11XL	23,62	On request	On request
12T5-21	12	19,10	18,25	13	5	12XL	25,15		
14T5-21	14	22,28	21,45	16	5	14XL	28,44		
15T5-21	15	23,87	23,05	16	6	14XL	28,44		
16T5-21	16	25,46	24,60	16	6	14XL	28,44		
17T5-21	17	27,06	26,20	16	6	16XL	31,74		
18T5-21	18	28,65	27,80	20	6	18XL	34,80		
19T5-21	19	30,24	29,40	20	6	18XL	34,80		
20T5-21	20	31,83	31,00	20	6	20XL	38,10		
24T5-21	24	38,20	37,35	25	6	24XL	44,70		
25T5-21	25	39,79	39,00	25	6	24XL	44,70		
30T5-21	30	47,75	46,95	30	8	28XL	51,05		
32T5-21	32	50,93	50,10	30	8	16L	55,56		
36T5-21	36	57,30	56,45	30	8	14H	61,91		
37T5-21	37	58,89	58,05	40	8	15H	66,68		
40T5-21	40	63,66	62,85	40	8	16H	69,85		
45T5-21	45	71,62	70,80	40	8	18H	79,38		
48T5-21	48	76,39	75,55	40	8	19H	82,55		
50T5-21	50	79,58	78,75	60	10	20H	85,73		
56T5-21	56	89,13	88,30	60	10	22H	95,25		
60T5-21	60	95,49	94,65	60	10	24H	103,19		
70T5-21	70	111,41	110,60	60	10	28H	119,06		
80T5-21	80	127,32	126,50	60	10	32H	134,94		
84T5-21	84	133,69	132,85	60	10	33H	134,94		
↓		**Pulleys available up to this size**						↓	
150T5-21	**150**	**dimensions : contact us**							

Dimensions in mm

T-type timing pulley

Alu | € Eco | Stock

Pitch T10




Belt width 16mm

Aluminium

Economy range

- **Pitch 10mm**
- Materials:
  Pulley: aluminium
  Flanges: steel




Info.

- **Pilot bore given as a guide only
- **We are unable to modify these parts**

Accessoire

- **T10** belt
  (tome 4 p.56)



DISCOUNTS

Qty	1+	6+	10+	20+
Disc.	List	-12%	-20%	On request

Part number	Z teeth	PCD (mm)	ØD (mm)	ØE (mm)	ØM (mm)	Pilot bore not garanteed ØA**	Stock*	Price each 1 to 5
12T10-21-AL	12	38,35	36,35	42	28	6	✔	8,38 €
14T10-21-AL	14	44,70	42,70	48	32	8	-	10,08 €
15T10-21-AL	15	47,90	45,90	51	32	8	✔	11,32 €
16T10-21-AL	16	51,10	49,10	54	35	8	✔	12,42 €
18T10-21-AL	18	57,45	55,45	60	40	8	✔	14,86 €
19T10-21-AL	19	60,65	58,65	66	44	8	-	15,96 €
20T10-21-AL	20	63,80	61,80	66	46	8	✔	17,20 €
22T10-21-AL	22	70,20	68,20	75	52	8	-	21,72 €
24T10-21-AL	24	76,55	74,55	83	58	8	✔	24,34 €
25T10-21-AL	25	79,75	77,75	83	60	8	-	24,50 €
26T10-21-AL	26	82,90	80,90	87	60	8	-	27,31 €
27T10-21-AL	27	86,10	84,10	91	60	8	-	29,75 €
28T10-21-AL	28	89,25	87,25	93	60	8	-	30,00 €
30T10-21-AL	30	95,65	93,65	102	60	8	-	35,75 €
32T10-21-AL	32	102,00	100,00	106	65	10	-	38,61 €
36T10-21-AL	36	114,75	112,75	119	70	10	✔	45,62 €
40T10-21-AL	40	127,45	125,45	131	80	10	-	56,72 €

*Depending on availability - Dimensions in mm

T-type timing pulley

Aluminium

Pitch T10

Belt width 25mm


- **Pitch 10mm**
- Materials:
  Pulley: aluminium
  Flanges: steel


Info.

- **Pilot bore given as a guide only
- **We are unable to modify these parts**

Accessoire

- **T10** belt
  (tome 4 p.56)





Economy range

DISCOUNTS

Qty	1+	6+	10+	20+
Disc.	List	-12%	-20%	On request

Part number	Z teeth	PCD (mm)	ØD (mm)	ØE (mm)	ØM (mm)	Pilot bore not garanteed ØA**	Stock*	Price each 1 to 5
12T10-30-AL	12	38,35	36,35	42	28	6	✔	9,83 €
14T10-30-AL	14	44,70	42,70	48	32	8	✔	12,17 €
15T10-30-AL	15	47,90	45,90	51	32	8	✔	13,38 €
16T10-30-AL	16	51,10	49,10	54	35	8	✔	14,97 €
18T10-30-AL	18	57,45	55,45	60	40	8	✔	17,78 €
19T10-30-AL	19	60,65	58,65	66	44	8	✔	19,30 €
20T10-30-AL	20	63,80	61,80	66	46	8	✔	20,62 €
22T10-30-AL	22	70,20	68,20	75	52	8	-	26,29 €
24T10-30-AL	24	76,55	74,55	83	58	8	-	29,37 €
25T10-30-AL	25	79,75	77,75	83	60	8	-	29,70 €
26T10-30-AL	26	82,90	80,90	87	60	8	-	32,97 €
27T10-30-AL	27	86,10	84,10	91	60	8	-	36,31 €
28T10-30-AL	28	89,25	87,25	93	60	8	✔	36,53 €
30T10-30-AL	30	95,65	93,65	102	60	8	✔	43,38 €
32T10-30-AL	32	102,00	100,00	106	65	10	-	47,15 €
36T10-30-AL	36	114,75	112,75	119	70	10	✔	55,69 €
40T10-30-AL	40	127,45	125,45	131	80	10	✔	69,31 €

*Depending on availability - Dimensions in mm

Nylon T-type timing pulley

Pla Eco

Pitch T10

Nylon PA6 moulded

Belt width 16mm




- **Positioning pulley**
- Pitch 10mm (T10)
- Material: Moulded PA6 nylon reinforced with 30% glass fibre
- We are unable to modify these parts


Info


- ** Pilot bore not guaranteed

Accessories

- **T10** belt **(tome 4 p.56)**







DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-12%	-25%	-33%	-37%	On request

Part number 1 flange	Part number 2 flanges	Z teeth	ØD (mm)	ØM (mm)	Pilot bore** ØA (mm)	ØE (mm)	Price each 1 to 5 1 flange	Price each 1 to 5 2 flanges
-	18T10-21-N2F	18	55,45	40	13	60	-	14,35 €
-	20T10-21-N2F	20	61,80	40	12	67	-	18,42 €
-	24T10-21-N2F	24	74,75	40	13	83	-	On request
30T10-21-N1F	-	30	93,65	50	14	99	19,94 €	-
32T10-21-N1F	-	32	100,00	50	14	105	On request	-

Dimensions in mm