

Alu T type toothed timing pulley bar stock

Aluminium

T5-BAR




- **Toothed bar stock to be cut to length by the customer**
- The overall length is the same as the maximum length
- Material : Aluminium suitable for hard anodic oxidation
- Finish : Supplied not-treated



Info.

- We are unable to modify this product



DISCOUNTS

Qty	1+	2+	4+
Disc. List	-20%		On request

Part number	Z Teeth	ØD External	Length of teeth LD	Total length LT	Price each
10T5-BAR	10	15,05	125	140	7,92 €
11T5-BAR	11	16,65	125	140	8,58 €
12T5-BAR	12	18,25	125	140	9,37 €
13T5-BAR	13	19,85	125	140	9,40 €
14T5-BAR	14	21,45	140	140	11,01 €
15T5-BAR	15	23,05	140	140	11,93 €
16T5-BAR	16	24,60	140	140	13,39 €
17T5-BAR	17	26,20	140	140	14,01 €
18T5-BAR	18	27,00	140	140	15,56 €
19T5-BAR	19	29,40	140	140	16,89 €
20T5-BAR	20	31,00	160	160	19,41 €
21T5-BAR	21	32,70	160	160	20,25 €
22T5-BAR	22	34,15	160	160	22,55 €
23T5-BAR	23	35,85	160	160	22,77 €
24T5-BAR	24	37,40	160	160	24,42 €
25T5-BAR	25	38,95	160	160	26,23 €
26T5-BAR	26	40,60	160	160	28,92 €
27T5-BAR	27	42,20	160	160	29,14 €
28T5-BAR	28	43,75	160	160	32,07 €
29T5-BAR	29	45,35	160	160	32,23 €
30T5-BAR	30	46,95	160	160	34,33 €
32T5-BAR	32	50,10	160	160	39,90 €
34T5-BAR	34	53,25	160	160	43,61 €
35T5-BAR	35	54,85	160	160	43,89 €
36T5-BAR	36	56,45	160	160	46,34 €
37T5-BAR	37	58,06	160	160	48,93 €
38T5-BAR	38	59,65	160	160	49,19 €
40T5-BAR	40	62,85	160	160	53,47 €
42T5-BAR	42	66,00	160	160	58,03 €
44T5-BAR	44	69,20	160	160	67,94 €
45T5-BAR	45	70,80	160	160	68,42 €
46T5-BAR	46	72,40	160	160	69,02 €
48T5-BAR	48	75,55	160	160	76,42 €
50T5-BAR	50	78,75	160	160	85,22 €
60T5-BAR	60	94,65	160	160	114,98 €
72T5-BAR	72	113,75	160	160	161,63 €
80T5-BAR	80	126,48	160	160	188,59 €
90T5-BAR	90	142,40	160	160	248,23 €
100T5-BAR	100	158,31	160	160	320,88 €

Dimensions in mm

Our other products



KB_WW
Closed linear
precision bearing,
Economy range



RCC_RCX
Spherical tilt washer -
DIN6319, concave



BLHB30
Right angled gearbox,
bored shafts, up to
4.47 Nm



Q6
Deep groove ball
bearing, Steel




SH2
Parallel axis helical
gear, Machined plastic
(delrin)




DER80
Stainless steel AC
asynchronous motor
0.55 - 0.75kW, 0.55 to
0.75kW



PSG25
Spur gear - precision
range, Stainless steel
316



BH01
Single housed
bearing, Bearing fitted
with adhesive



LAT2
2A motorised linear
actuator, 2 amperes



SVT20
Screwjack with
travelling screw, with
translating screw



RGS
Rotex® GS backlash
free jaw coupling,
from 0.5 to 190Nm



BLM
Spring loaded plunger
with ball tip, Plastic
body


Complementary products




T5-10ECO
T type timing pulley,
Economy range - T5
aluminium



T5-16ECO
T type timing pulley,
Economy range - T5
aluminium



T5courroie
T type timing belt, T5
Steel cored
polyurethane



T5courroie
T type timing belt, T5
Steel cored
polyurethane