

T-Clip - Aluminium profile attachment

Hook

TCL-CR

- **Hook**
- **Description:** A cable holder equipped with 2 base plates that makes it possible to run 2 electrical cables along an aluminium profile.

Advantages

- Allows all kinds of objects (brushes, keys, dusters, etc.) to easily be hung from a profile
- Objects can be stored tidily but remain easily accessible
- Being manufactured from 304 stainless steel, they are suitable for use in all sorts of environments.



DISCOUNTS

Qty	1+	20+	50+
Disc.	List	-5%	On request

Part number	Material	Dimensions	Compatibility	Capacity	Stock*	Price each 1 to 19
TCL-CR	Inox 304	53x24x2	8 and 10mm T-Clip	5 kg	4	8,93 €

Dimensions in mm

Magnetic object holder


TCL-PM

- **Magnetic object holder**
- **Description:** A magnetic holder that allows various metal objects to be attached to an aluminium profile.

Advantages

- Allows various metal objects to be quickly attached

Powerful magnet



DISCOUNTS

Qty	1+	20+	50+
Disc.	List	-5%	On request

Part number	Dimensions	Compatibility	Powerful magnet	Stock*	Price each 1 to 19
TCL-PM	38,5x32x7,5	8 and 10mm T-Clip	0,9kg/cm ²	-	8,91 €

Dimensions in mm

Fax

0 825 88 6000

Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

229

Our other products



RTT
Locking Assembly,
Medium/high torque



DER63

Stainless steel AC
asynchronous motor
0.18 kW, 0.18kW



BAN

Angular clamp,
Universal



BLHB50

Right angled gearbox,
bored shafts, up to 30
Nm



CLLCLLP

Clevis components,
long version, Steel -
long range



BABS

630 Stainless steel
compact ball pin,
Hardened stainless
steel



VELM6

Screw-on base for
hook-and-loop strip,
Polyamide



ZG3

Plastic spur gear,
Machined plastic
(delrin)



PW_PWG1

Wheel - precision
range, Bronze



UGAC_UGET

Connection for
threaded actuator
rod, Connection for



BLM

Spring loaded plunger
with ball tip, Plastic
body



SRP

Slotted spring pin
ISO8752, Split ISO
8752

Complementary products



PRF4545

Standard aluminium
profile, 45 x 45 mm