



Support rod for heavy loads


Max load 90,000 N

TCL

- Threaded levelling stem, suitable for heavy loads
- Hollowed stem
- Fine pitch thread allows accurate levelling
- Material:
Chromed steel

Applications

- Machine tools, assembly machines, automated lines



DISCOUNTS

Qty	1+	6+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	ØD	ØD1	SW	ØF	H	Static	Price each
						load (N)	1 to 5
TCL-M30C-110	M30x2	27	24	17	110	70000	18,92 €
TCL-M36C-110	M36x2	33	27	17	110	90000	20,71 €

Dimensions in mm

Adjusting nut


Fine thread

ECL

- Adjusting nut
- Fine thread
- Fine pitch thread allows accurate levelling
- Material:
Chromed steel

Applications

- Machine tools, assembly machines, automated lines



DISCOUNTS

Qty	1+	6+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	ØD	SW	H	Price each
				1 to 5
ECL-M24C	M24x2	36	18	2,16 €
ECL-M27C	M27x2	41	12	4,07 €
ECL-M30C	M30x2	36	11	5,58 €
ECL-M35C	M35x2	55	15	8,92 €
ECL-M36C	M36x2	55	15	8,92 €
ECL-M36C3	M36x3	55	15	8,92 €
ECL-M42C	M42x2	65	20	16,16 €

Dimensions in mm

Our other products



LVT

Miniature motorised actuator 4A, 4 amperes



SCA

Flat cable clamp, Steel



NT92

Spur gear coaxial gearbox, from 15 to 40 Nm - In-line



J66

Spur gear coaxial gearbox, from 0.90 to 2.80 Nm - In-line



T5P_T10P

Connecting plate for T type timing belts, T10



VAB

Flanged nut for ball screw, For VAB ballscrew



PRF_SDD

Support for Ø12mm Prox detector, Ø12



ARTE

Flexible bush, For multi-directional loads



CHMR110

Worm and wheel gear reducer, up to 980 Nm



SH1

Parallel axis helical gear, Machined plastic (delrin)



PTA100

Articulated levelling foot, pressed base Ø100, Ø 100



PDM_PDV

Detectable plastic palm grip, blue thermoplastic

Complementary products



TCL-ECL

Support rod for heavy loads, Support spindle