Rigid manual tensioner

TMR

Ideal for belts

steel or stainless steel



- ***Suitable for mounting and positioning GTC belt rollers and PTR sprockets***
- *Material:*
  Plated XC38 steel
  304L stainless steel

Accessories


- **GTC** *belt tensioner* ***(tome 4 p.146)***
- **PTR** *idler chain sprocket* ***(tome 4 p.140)***



Typical application using GTC belt roller



Typical application using PTR sprocket



DISCOUNTS

Qty	1+	4+	10+
Disc.	List	-10%	On request

Part number	Material	ØF	Stock*	Price each 1 to 3
TMR-8	Steel	M8	✔	25,97 €
TMR-10	Steel	M10	-	25,97 €
TMR-8/SS	Stainless steel	M8	-	33,44 €
TMR-10/SS	Stainless steel	M10	-	33,44 €


**Depending on avaibility - Dimensions in mm*

- ***Suitable for mounting and positioning GTC belt rollers and PTR sprockets in a variety of positions***
- *Material:*
  Plated XC38 steel
  304L stainless steel
- **Anti-rotation system*




Accessories

- **GTC** *belt tensioner* ***(tome 4 p.146)***
- **PTR** *idler chain sprocket* ***(tome 4 p.140)***




TFR83



TFR125 et TFR150

Typical application using GTC belt roller



Typical application using PTR sprocket

DISCOUNTS

Qty	1+	4+	10+
Disc.	List	-10%	On request


Part number	A	B	C	ØD	E	F	G	J	L	ØM	R	Stock*	Price each 1 to 3
Steel version													
TFR83-8	28	27,5	-	8,5	8	10	24	30	83,5	M8	10,5	✔	14,77 €
TFR83-10	28	27,5	-	8,5	8	10	24	30	83,5	M10	10,5	-	15,22 €
TFR125-8	28	27,5	14	10,5	8	10	24	30	125	M8	10,5	✔	15,80 €
TFR125-10	28	27,5	14	10,5	8	10	24	30	125	M10	10,5	✔	16,40 €
TFR125-12	28	27,5	14	10,5	8	10	24	30	125	M12	10,5	✔	17,30 €
TFR150-12	33,5	33,5	16	12,5	8	15	29	35	150	M12	12,5	✔	25,38 €
TFR150-16	33,5	33,5	16	12,5	8	15	29	35	150	M16	12,5	-	26,27 €
Stainless steel version													
TFR83-8/SS	28	27,5	-	8,5	8	10	24	30	83,5	M8	10,5	-	23,28 €
TFR83-10/SS	28	27,5	-	8,5	8	10	24	30	83,5	M10	10,5	-	24,19 €
TFR125-8/SS	28	27,5	14	10,5	8	10	24	30	125	M8	10,5	-	29,28 €
TFR125-10/SS	28	27,5	14	10,5	8	10	24	30	125	M10	10,5	-	30,15 €
TFR125-12/SS	28	27,5	14	10,5	8	10	24	30	125	M12	10,5	-	32,26 €
TFR150-10/SS	33,5	33,5	16	12,5	8	15	29	35	150	M10	12,5	-	45,11 €
TFR150-12/SS	33,5	33,5	16	12,5	8	15	29	35	150	M12	12,5	-	45,72 €
TFR150-16/SS	33,5	33,5	16	12,5	8	15	29	35	150	M16	12,5	-	47,21 €

**Depending on avaibility - Dimensions in mm*

Our other products



Flat suction cup, silicon



Wormwheel , Machined plastic (delrin)



Self-lubricating blanks, Bronze BP25



Connecting kits, XZ linking kit



Joining plate for aluminium profile, Angle connection



Stainless steel articulated levelling foot, Ø 30 & 40



Flanged drill bushing, Steel



Lifting sling, 2 eyelinks



Magnetic stop for aluminium profile,



Swivel castor with central hole, Steel -



Rotating bent lever, Common applications



Corner reinforcement, Corner reinforcement

Complementary products



Belt tensioner, For standard applications



Idler chain sprocket, For standard applications



Idler chain sprocket, For standard applications