


- Short threaded stud

- Material:

Stainless steel, 304



DISCOUNTS

Qty	1+	5+	15+
Disc.	List -5%	On request	

Part number	ØF	L	Qty per pack	Price each 1 to 4
TIF6-30/SS/B	M6	30	100	54,12 €
TIF6-40/SS/B	M6	40	100	55,44 €
TIF6-50/SS/B	M6	50	100	60,16 €
TIF6-60/SS/B	M6	60	100	66,64 €
TIF6-70/SS/B	M6	70	100	73,56 €
TIF6-80/SS/B	M6	80	100	79,59 €
TIF6-100/SS/B	M6	100	100	92,55 €
TIF6-120/SS/B	M6	120	100	105,50 €
TIF8-30/SS/B	M8	30	100	56,72 €
TIF8-40/SS/B	M8	40	100	66,64 €
TIF8-50/SS/B	M8	50	100	77,01 €
TIF8-60/SS/B	M8	60	100	92,11 €
TIF8-70/SS/B	M8	70	100	106,78 €
TIF8-80/SS/B	M8	80	100	121,47 €
TIF8-100/SS/B	M8	100	100	133,54 €
TIF8-120/SS/B	M8	120	100	148,23 €
TIF8-140/SS/B	M8	140	100	169,38 €
TIF10-30/SS/B	M10	30	100	80,89 €
TIF10-40/SS/B	M10	40	100	97,73 €
TIF10-50/SS/B	M10	50	100	114,55 €
TIF10-60/SS/B	M10	60	100	130,10 €
TIF10-70/SS/B	M10	70	100	142,18 €
TIF10-80/SS/B	M10	80	100	156,86 €
TIF10-100/SS/B	M10	100	100	186,64 €
TIF10-120/SS/B	M10	120	100	216,86 €
TIF10-140/SS/B	M10	140	100	250,54 €
TIF10-160/SS/B	M10	160	100	285,07 €
TIF12-40/SS/B	M12	40	100	149,08 €
TIF12-50/SS/B	M12	50	100	181,02 €
TIF12-60/SS/B	M12	60	100	207,80 €
TIF12-80/SS/B	M12	80	100	263,48 €
TIF12-100/SS/B	M12	100	100	315,70 €
TIF12-120/SS/B	M12	120	100	370,54 €
TIF12-140/SS/B	M12	140	100	426,20 €
TIF12-160/SS/B	M12	160	100	493,98 €


Dimensions in mm

Fax 0 825 88 6000
Service 0,15 € / min
+ prix appel

Our other products




PSG25S
Spur gear - precision range, Stainless steel 316



PRFbou
Emergency release button for aluminium profile, Emergency release bu...



OPFL OPPM
Numerical counter accessories, Locking clamp



GMC
Flat profile - Round guide, Flat profile - round guide



CAP881
Side flexing slim slat top chain stainless steel, Narrow range 881



PPS
Lifting ring, Universal threaded



EBH
Cap nut Hygienic Design®, With collar



T5M T10M
T type timing belt per metre, T5 Steel cored polyurethane



SLB
Indexing plunger, stainless steel



LWH
High rigidity linear slide, Rail - from 9320 N to 71300 N



M0
Worm and wheel set, Bronze



AK
Bellows coupling Gerwah®, from 36 to 800Nm

Complementary products



SHN
Hexagonal nut DIN934, A2 Stainless steel



SHW
Plain washer, A2 Stainless steel



NIN
Self-locking nut, Steel



MCLred
Reducing sleeve female/female, Cylindrical - stainless steel