


- Short threaded stud

- Material:

Stainless steel, 304



DISCOUNTS

Qty	1+	5+	15+
Disc.	List -5%	On request	

Part number	ØF	L	Qty per pack	Price each 1 to 4
TIF6-30/SS/B	M6	30	100	54,12 €
TIF6-40/SS/B	M6	40	100	55,44 €
TIF6-50/SS/B	M6	50	100	60,16 €
TIF6-60/SS/B	M6	60	100	66,64 €
TIF6-70/SS/B	M6	70	100	73,56 €
TIF6-80/SS/B	M6	80	100	79,59 €
TIF6-100/SS/B	M6	100	100	92,55 €
TIF6-120/SS/B	M6	120	100	105,50 €
TIF8-30/SS/B	M8	30	100	56,72 €
TIF8-40/SS/B	M8	40	100	66,64 €
TIF8-50/SS/B	M8	50	100	77,01 €
TIF8-60/SS/B	M8	60	100	92,11 €
TIF8-70/SS/B	M8	70	100	106,78 €
TIF8-80/SS/B	M8	80	100	121,47 €
TIF8-100/SS/B	M8	100	100	133,54 €
TIF8-120/SS/B	M8	120	100	148,23 €
TIF8-140/SS/B	M8	140	100	169,38 €
TIF10-30/SS/B	M10	30	100	80,89 €
TIF10-40/SS/B	M10	40	100	97,73 €
TIF10-50/SS/B	M10	50	100	114,55 €
TIF10-60/SS/B	M10	60	100	130,10 €
TIF10-70/SS/B	M10	70	100	142,18 €
TIF10-80/SS/B	M10	80	100	156,86 €
TIF10-100/SS/B	M10	100	100	186,64 €
TIF10-120/SS/B	M10	120	100	216,86 €
TIF10-140/SS/B	M10	140	100	250,54 €
TIF10-160/SS/B	M10	160	100	285,07 €
TIF12-40/SS/B	M12	40	100	149,08 €
TIF12-50/SS/B	M12	50	100	181,02 €
TIF12-60/SS/B	M12	60	100	207,80 €
TIF12-80/SS/B	M12	80	100	263,48 €
TIF12-100/SS/B	M12	100	100	315,70 €
TIF12-120/SS/B	M12	120	100	370,54 €
TIF12-140/SS/B	M12	140	100	426,20 €
TIF12-160/SS/B	M12	160	100	493,98 €

Dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

Our other products



BEF
Bearing housing for
miniature ballscrew,
Bearing housing



METC
Flanged sintered
bronze bush, Self-
lubricating sintered
bronze



TCLar
Automatic chain
tensioner, With wide
guide



PLC_PLT
Magnetic stud with
threaded hole, With
threaded hole



PFM
Fixed levelling foot,
Flanged plate



CAP880
Side flexing slim slat
top chain acetel,
Narrow range 880



BAGSS
Stainless steel
Clamping collar,
Stainless steel



DER80
Stainless steel AC
asynchronous motor
0.55 - 0.75kW, 0.55 to
0.75kW



PM4
Worm and wheel set,
Machined plastic



WINGbrEcrou
Manually tightened
wing nut DIN315,



DFG
Flat suction cup,
nitrile



PR125
Articulated foot Ø123,
Ø 123

Complementary products



SHN
Hexagonal nut
DIN934, A2 Stainless
steel



SHW
Plain washer, A2
Stainless steel



NIN
Self-locking nut, Steel



MCLred
Reducing sleeve
female/female,
Cylindrical - stainless
steel