

- ***For guiding profile***
- *Materials:*
  Body: stainless steel 304
  Nut/washer: stainless steel

stainless steel



Typical application





DISCOUNTS

Qty.	1+	10+	20+
Disc.	List	-5%	On request

Part number	ØD	For Axis	H	W	Weight (kg)	Price each 1 to 9
TOL12-40/SS	12,5	APB12	40	55	0,28	27,48 €
TOL12-60/SS	12,5	APB12	60	75	0,38	33,57 €
TOL12-90/SS	12,5	APB12	90	105	0,55	36,86 €
TOL12-130/SS	12,5	APB12	130	145	0,77	49,17 €
TOL14-40/SS	14,5	APB14	40	56	0,28	49,17 €
TOL14-60/SS	14,5	APB14	60	76	0,38	27,48 €
TOL14-90/SS	14,5	APB14	90	106	0,55	31,79 €
TOL14-130/SS	14,5	APB14	130	146	0,77	35,09 €
TOL16-40/SS	16,5	APB16	40	57	0,28	49,17 €
TOL16-60/SS	16,5	APB16	60	77	0,38	27,48 €
TOL16-90/SS	16,5	APB16	90	107	0,55	36,86 €
TOL16-130/SS	16,5	APB16	130	147	0,77	49,17 €

**Depending on availability - Dimensions in mm*

Our other products



LC

Friction clutch, 30 to 240 Nm



DHX

Dowel pin internal thread, Extractable DIN 7979D




DOMI120

Accessories, Fixing kit



SHSS

Shoulder screw stainless steel 416, Pre-treated 416 stainless steel




T5M_T10M

T type timing belt per metre, T10 Steel cored polyurethane



ZY

Conical elasto buffer, Stainless steel



PM2

Wormwheel , Machined plastic (delrin)



AT5P_AT10P

Connecting plate for AT type timing belts, AT10



D-PAR_SS

Stainless steel elasto mount, stainless steel



SGL

Lifting sling, 2 eyelinks



MSP38

Masterplate® glueable insert Ø38, Cylindrical Ø38 with tapped ins...



RPCtcss

Swivel castor with central hole, Stainless steel - Polyamide - with ...

Complementary products



TOC

Short swivel head, Short



APB_F

Adjusting rod for clamp - Male, Threaded



APB_T

Adjusting rod for clamp - Female, Bored



RAG

Roller guide,