

## UCFss


## 4 mounting points

- Self aligning bearing with 4 mounting points
- Interchangeable with cast iron units
- Working temperature range: until +140°C
- Material:

Bearing: stainless steel

Housing: stainless steel

**For hostile environments**



### DISCOUNTS

Qty	1+	10+	26+
Disc.	List	-10%	On request

Part number	ØD	A	E	G	L	ØS	Z	F	Bi	N	Weight (kg)	Stock*	Prix Uni.
												1 à 9	
UCF204/SS	20	86	64	11	25	12	33,3	15	31,0	12,7	0,60	✓	50,71 €
UCF205/SS	25	95	70	13	27	12	35,8	16	34,1	14,3	0,86	✓	48,47 €
UCF206/SS	30	108	83	13	31	12	40,1	18	38,1	15,9	1,10	✓	78,00 €
UCF207/SS	35	117	92	15	34	14	44,4	19	42,9	17,5	1,60	-	96,61 €
UCF208/SS	40	130	102	15	36	16	51,2	21	49,2	19,0	1,90	✓	111,95 €

\*Depending on availability - Dimensions in mm

## Our other products



RURp

Swivel castor with double brake, Polyurethane - Aluminium rim (Free




PSG05S

Spur gear - precision range, Stainless steel 303



BS2

Panamech, Multi-Beam, Aluminium - with set screw



TR

Spur round rack, Stainless steel - module 0,25-1,5



GCH

Linear ball slide - Stainless steel balls, Chariot - from 514 N to 1...



HTD8M\_30

HTD Heavy duty timing pulley, HTD8 Steel



ZG1

Plastic spur gear, Machined plastic (delrin)



SVR15

Screwjack with travelling nut, with moving nut



NSU

Universal 90° support clamp, Universal 90° support clamp



PSG25S

Spur gear - precision range, Stainless steel 316



PTA50

Articulated levelling foot, pressed base Ø50, Ø 50



TBD

Manual leadscrew table with opposing threads, 5kg

## Complementary products



UCP\_SS

Stainless steel pillow block bearing, Stainless steel



UCFL\_SS

Stainless steel flanged bearing, Stainless steel



SBF

Sealed flange bearing unit for Food Industry, cover



SBF

Sealed flange bearing unit for Food Industry, cover