

H Type guide unit






UGH16 For Ø12 and Ø16 actuators (ISO 6432)

- Guide system for actuator
- Fitted with 4 smooth bronze bearings
- Slides protected by wiper joints
- Actuator coupling available on front face
- Supplied with fixing screw for actuator
- Maintenance free
- Working temperature: +5 to +80 °C
- Maximum speed: 1 m/s
- Maximum loads: See end of section
- Material:

Body + face plate:
anodised aluminium
Couplings + screws:
Zinc plated steel
Guide shafts:
Chromed steel

Excellent price/
Quality ratio

Accurate even over
long strokes



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Stroke	Ø Actuator	Ø Guide rod	Weight (kg)	Price each
UGH16-25	25	12 and 16	10	0,43	200,81 €
UGH16-50	50	12 and 16	10	0,46	201,87 €
UGH16-100	100	12 and 16	10	0,52	203,96 €
UGH16-160	160	12 and 16	10	0,59	206,45 €
UGH16-200	200	12 and 16	10	0,64	208,12 €
UGH16-250	250	12 and 16	10	0,70	210,26 €




Dimensions in mm

- Guide system for actuator
- Fitted with 4 smooth bronze bearings
- Slides protected by wiper joints
- Actuator coupling available on front face
- Supplied with fixing screw for actuator
- Maintenance free
- Working temperature: +5 to +80 °C
- Maximum speed: 1 m/s
- Maximum loads: See end of section
- Material:

Body + face plate:
anodised aluminium
Couplings + screws:
Zinc plated steel
Guide shafts:
Chromed steel

Excellent price/
Quality ratio

Accurate even over
long strokes



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Stroke	Ø Actuator	Ø Guide rod	Weight (kg)	Price each
UGH20-25	25	20	10	0,93	221,63 €
UGH20-50	50	20	10	0,96	222,65 €
UGH20-100	100	20	10	1,02	224,69 €
UGH20-160	160	20	10	1,09	227,21 €
UGH20-200	200	20	10	1,14	228,96 €
UGH20-250	250	20	10	1,20	231,01 €

Dimensions in mm

H Type guide unit



UGH25

For **Ø25** actuators ISO 6432




- Guide system for actuator
- Fitted with 4 smooth bronze bearings
- Slides protected by wiper joints
- Actuator coupling available on front face
- Supplied with fixing screw for actuator
- Maintenance free
- Working temperature: +5 to +80 °C
- Maximum speed: 1 m/s
- Maximum loads: See end of section
- Material:

Body + face plate:
anodised aluminium
Couplings + screws:
Zinc plated steel
Guide shafts:
Chromed steel



Accurate even over long strokes

Excellent price/
Quality ratio



QUICK DELIVERY

DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Stroke (mm)	Actuator Ø (mm)	Guide rod Ø (mm)	Weight (kg)	Price each
UGH25-25	25	25	10	0,93	221,63 €
UGH25-50	50	25	10	0,96	222,63 €
UGH25-100	100	25	10	1,02	224,69 €
UGH25-160	160	25	10	1,09	227,21 €
UGH25-200	200	25	10	1,14	228,94 €
UGH25-250	250	25	10	1,20	230,99 €

Dimensions in mm

H Type guide units




UGH40 For $\varnothing 40$ actuators ISO 15552 (VDMA 24562)

- Guide system for standard pneumatic actuators

- Fitted with 4 smooth bronze bearings
- Slides protected by wiper joints
- Actuator coupling supplied
- Fixing holes conform to CNOMO standards
- Supplied with 4 fixing screws for actuator
- Maintenance free
- Working temperature: +5°C to +80°C
- Maximum speed: 1 m/s
- Maximum loads : See end of section
- Material

Body + face plate:
anodised aluminium
Couplings + screws:
Zinc plated steel
Guide shafts:
Chromed steel

Accurate even for long strokes



QUICK DELIVERY

Attach cylinder using 4 off M6 screws on $\varnothing 38$

DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Stroke (mm)	Actuator \varnothing (mm)	Guide rod \varnothing (mm)	Weight (kg)	Price each
UGH40-25	25	40	16	2,38	288,82 €
UGH40-50	50	40	16	2,46	290,66 €
UGH40-100	100	40	16	2,61	294,38 €
UGH40-160	160	40	16	2,80	298,88 €
UGH40-200	200	40	16	2,92	301,82 €
UGH40-250	250	40	16	3,08	305,57 €
UGH40-320	320	40	16	3,29	310,74 €
UGH40-400	400	40	16	3,54	316,68 €
UGH40-500	500	40	16	3,85	324,12 €
UGH40-600	600	40	16	4,16	331,60 €

Dimensions in mm




H Type guide units

For **Ø50** actuators ISO 15552 (VDMA 24562) **UGH50**

- Guide system for standard pneumatic actuators
- Fitted with 4 smooth bronze bearings
- Slides protected by wiper joints
- Actuator coupling supplied
- Fixing holes conform to CNOMO standards
- Supplied with 4 fixing screws for actuator
- Maintenance free
- Working temperature: +5°C to +80°C
- Maximum speed: 1 m/s
- Maximum loads : See end of section
- Material

Body + face plate:
anodised aluminium
Couplings + screws:
Zinc plated steel
Guide shafts:
Chromed steel

Accurate even
for long strokes



QUICK DELIVERY

Attach cylinder using
4 off M6 screws on
Ø46.5

DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Stroke (mm)	Actuator Ø (mm)	Guide rod Ø (mm)	Weight (kg)	Price each
UGH50-25	25	50	20	3,82	348,92 €
UGH50-50	50	50	20	3,94	351,37 €
UGH50-100	100	50	20	4,18	356,32 €
UGH50-160	160	50	20	4,47	362,28 €
UGH50-200	200	50	20	4,66	366,22 €
UGH50-250	250	50	20	4,90	371,18 €
UGH50-320	320	50	20	5,24	378,09 €
UGH50-400	400	50	20	5,62	386,00 €
UGH50-500	500	50	20	6,10	395,93 €
UGH50-600	600	50	20	6,58	405,78 €

Dimensions in mm

H Type guide units

Load diagrams

Below (Details of guides with ball bearings can be supplied on request)

