



# Small 6 lobe threaded handle

## Black Duroplast bored insert

## VBFP


- Operating element
- Materials:  
Black phenolic Duraplast  
Insert; brass or stainless steel

### Advantages


- Easy grip
- Temperature resistant
- Good chemical resistance
- Easier to clean than technopolymer
- In machining applications, less likely to retain swarf

Good  
resistance

brass or  
stainless steel  
insert



VBFP20-VBFP30-VBFP/SS



VBFP40 to VBFP70

### DISCOUNTS

Qty	1+	10+	20+	50+	100+	200+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØA	ØB	C	ØD	E	F	G	ØD1	Weight (g)	Price each 1 to 9
<b>Brass insert</b>										
VBFP20-M4	20	13	15	M4	11	7	8	7,5	6	4,05 €
VBFP20-M5	20	13	15	M5	11	7	8	7,5	7	4,20 €
VBFP20-M6	20	13	15	M6	11	7	8	7,5	10	4,27 €
VBFP30-M6	30	17	24	M6	15	11	12,5	9	16	4,90 €
VBFP30-M8	30	17	24	M8	15	11	12,5	9	17	5,15 €
VBFP40-M8	40	21	28	M8	18	13	15	11	29	5,96 €
VBFP40-M10	40	21	28	M10	18	13	15	11	31	6,00 €
VBFP50-M8	50	25	33	M8	18	15	18	13	43	7,42 €
VBFP50-M10	50	25	33	M10	18	15	18	13	45	7,49 €
VBFP50-M12	50	25	33	M12	18	15	18	13	47	7,49 €
VBFP60-M12	60	28	35	M12	25	15	20	13	70	9,36 €
VBFP70-M12	70	32	42	M12	25	21	21	13	96	11,37 €
VBFP70-M14	70	32	42	M14	25	21	21	15	94	11,37 €
VBFP70-M16	70	32	42	M16	25	21	21	17	93	12,59 €
<b>Stainless steel insert</b>										
VBFP20-M6/SS	20	13	15	M6	11	7	8	7,5	10	9,32 €
VBFP30-M6/SS	30	17	24	M6	15	11	12,5	9	16	9,95 €
VBFP40-M8/SS	40	21	28	M8	18	13	15	11	34	11,15 €
VBFP50-M8/SS	50	25	33	M8	18	15	18	13	49	12,07 €
VBFP50-M10/SS	50	25	33	M10	18	15	18	13	52	12,69 €

Dimensions in mm

## Our other products



PITA

Locking bolt, with T handle



CLASS

Stainless steel indexing handle - female, Stainless steel



BSM\_LOK

Long-Lok spring plunger with internal hexagonal socket, LONG-LOK - s...



PTRSS

Idler chain sprocket, For hostile environments



P55

Worm and wheel gear reducer, up to 57 Nm



SA\_SAKH

Housing for linear bearing, Closed - light load



INO

Internal gear, Machined plastic (delrin)




CHAE4060PA

Decorative asymmetric screwed hinge, Polyamide



UTKpwrr

V shaped channel UtiliTrak®, V rail



LAT2

2A motorised linear actuator, 2 amperes



BAG

Steel Clamping collar, Steel



OP2

Mechanical digital position indicator, 3 numbers

## Complementary products



VB

Small 6 lobe threaded handle - female, Duroplast - Stainless steel



GLB

Small 6 lobe female handle, Technopolymer - Stainless steel