

# Self-gripping cable strip

## VEL For electric and pneumatic cables

- Velcro type tie for fixing or bundling cables
- 1 "loop" side, 1 "hook" side
- Ideal for fixing cables on aluminum profiles with the **VEL-PRF** bases
- Sold in roll
- Materials:  
Self-extinguishing polypropylene according to UL94-V2

### Advantages

- Easy mounting
- Reusable hundreds of times
- Different sizes of hook-and-loop strips available
- No risk of injury or damage to cables unlike Rilsan cable ties
- Cut-out for easy lengthening.

### Accessories

- **VEL-M** or **VEL-PRF** base



Use on the base



Use alone

### DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-10%	On request

Part number	Width (mm)	Length (metre)	Price each
VEL7.5-15/B	7,5	15	38,59 €
VEL10-25/B	10	25	80,53 €
VEL20-25/B	20	25	98,98 €
VEL30-25/B	30	25	204,70 €

\*Depending on availability - Dimensions in mm

# Clip-on base for hook-and-loop strip

For electric and pneumatic cables **VELPRF**



- **Support clip for Velcro type hook-and-loop strip**
- Connecting element for fixing a cable on a **Minitec PRF** aluminum profile
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:  
Glass fiber reinforced polyamide  
self-extinguishing according to UL94-V0

## Advantages


- Easy mounting by 45° rotation
- Reusable
- Different sizes of hook-and-loop strips available

## Accessories

- **VEL** stripe



clip-on  
on PRF profile



## DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Range of Tightening (mm)	For strip Width (mm)	A	B	H1	Price each 1 to 9
VEL7.5-PRF-420	4-20	7,5/10	19	15	15,35	4,19 €
VEL10-PRF-420	4-20	7,5/10	19	15	15,35	4,19 €
VEL20-PRF-835	8-35	20	29	26	18,05	4,36 €
VEL20-PRF-1060	10-60	20	36	26	18,05	4,51 €

\*Depending on availability - Dimensions in mm

# Screw-on base for hook-and-loop

**VELM** For electric and pneumatic cables

- **Support clip for Velcro type hook-and-loop strip**
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:  
Glass fiber reinforced polyamide  
self-extinguishing according to UL94-V0

## Advantages



- Easy mounting by screwing
- Reusable
- Different sizes of hook-and-loop strips available

## Accessories

- VEL stripe
- PRF-ECL nut and FHC screw



For 7.5 to 20 mm  
strips



## DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Range of tightening (mm)	For screw	For strips width (mm)	A	B	H	Price each
VEL7.5-M4-420	4-20	M4	7,5	18,6	15	8,6	1 to 9 3,68 €
VEL10-M4-420	4-20	M4	10,0	18,6	15	8,6	3,68 €
VEL20-M5-835	8-35	M4/M5	20,0	29,0	26	11,3	3,85 €
VEL20-M5-1060	10-60	M4/M5	20,0	36,0	26	11,3	4,01 €

\*Depending on availability - Dimensions in mm

# Screw-on base for hook-and-loop

For electric and pneumatic cables

VELM

- Support clip for Velcro type hook-and-loop strip
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:  
Glass fiber reinforced polyamide  
self-extinguishing according to UL94-V0

## Advantages



- Easy mounting by screwing
- Reusable

## Accessories


- VEL stripe
- PRF-ECL nut and CHC6 screw



For strip  
30mm



18,5



## DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Range of tightening (mm)	For screw	For strips width (mm)	Price each 1 to 9
VEL30-M6-20100	20-100	M6	30	7,70 €

Dimensions in mm

## Our other products



**TCSs**  
Automatic chain tensioner, With support



**BAGSS**  
Stainless steel  
Clamping collar,  
Stainless steel



**PDD**  
Actuating plunger,  
Non-rotating detector  
shaft



**AKD**  
Bellows coupling  
Gerwah®, from 22 to  
600Nm




**SUPss**  
Self-centering  
clamping hub  
stainless steel,  
Without locknut



**BLHT20**  
Right angled gearbox,  
from 0.66 to 1.77 Nm



**CHA138**  
Screwed hinge with  
threaded insert, 138  
degrees



**PRF-SCREEN-1**  
Screen support, Basic  
support



**MPS**  
Hexagonal spacer,  
Stainless steel 303



**PCS75K**  
Chain sprocket with  
hardened teeth,  
19.05mm (DIN12B-1)



**BLOC**  
Doorstop, Doorstop



**MHX**  
Hexagonal threaded  
sleeve, Hexagonal -  
stainless steel

## Complementary products



**VELprf**  
Clip-on base for hook-  
and-loop strip,  
Polyamide



**VELM4**  
Screw-on base for  
hook-and-loop strip,  
Polyamide



**VELM6**  
Screw-on base for  
hook-and-loop strip,  
Polyamide