

Self-gripping cable strip

VEL For electric and pneumatic cables

- Velcro type tie for fixing or bundling cables
- 1 "loop" side, 1 "hook" side
- Ideal for fixing cables on aluminum profiles with the VEL-PRF bases
- Sold in roll
- Materials:
Self-extinguishing polypropylene according to UL94-V2

Advantages

- Easy mounting
- Reusable hundreds of times
- Different sizes of hook-and-loop strips available
- No risk of injury or damage to cables unlike Rilsan cable ties
- Cut-out for easy lengthening.

Accessories

- VEL-M or VEL-PRF base



Use on the base



Use alone

DISCOUNTS

Qty	1+	2+	4+
Disc. List	-10%		On request

Part number	Width (mm)	Length (metre)	Price each
VEL7.5-15/B	7,5	15	38,59 €
VEL10-25/B	10	25	80,53 €
VEL20-25/B	20	25	98,98 €
VEL30-25/B	30	25	204,70 €

*Depending on availability - Dimensions in mm

Clip-on base for hook-and-loop strip

For electric and pneumatic cables **VELPRF**

- Support clip for Velcro type hook-and-loop strip
- Connecting element for fixing a cable on a **Minitec PRF** aluminum profile
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:
Glass fiber reinforced polyamide
self-extinguishing according to UL94-V0






Advantages

- Easy mounting by 45° rotation
- Reusable
- Different sizes of hook-and-loop strips available

Accessories

- VEL stripe



DISCOUNTS

Qty	1+	10+	20+	50+
Disc. List		-5%	-10%	On request

Part number	Range of Tightening (mm)	For strip Width (mm)	A	B	H1	Price each
						1 to 9
VEL7.5-PRF-420	4-20	7,5/10	19	15	15,35	4,19 €
VEL10-PRF-420	4-20	7,5/10	19	15	15,35	4,19 €
VEL20-PRF-835	8-35	20	29	26	18,05	4,36 €
VEL20-PRF-1060	10-60	20	36	26	18,05	4,51 €

*Depending on availability - Dimensions in mm

Screw-on base for hook-and-loop

VELM For electric and pneumatic cables

- Support clip for Velcro type hook-and-loop strip
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:
Glass fiber reinforced polyamide
self-extinguishing according to UL94-V0

Advantages



- Easy mounting by screwing
- Reusable
- Different sizes of hook-and-loop strips available

Accessories

- VEL stripe
- PRF-ECL nut and FHC screw



For 7.5 to 20 mm
strips



DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Range of tightening (mm)		For strips width (mm)			Price each	
	For screw	For screw	A	B	H	1 to 9	
VEL7.5-M4-420	4-20	M4	7,5	18,6	15	8,6	3,68 €
VEL10-M4-420	4-20	M4	10,0	18,6	15	8,6	3,68 €
VEL20-M5-835	8-35	M4/M5	20,0	29,0	26	11,3	3,85 €
VEL20-M5-1060	10-60	M4/M5	20,0	36,0	26	11,3	4,01 €

*Depending on availability - Dimensions in mm

Screw-on base for hook-and-loop

For electric and pneumatic cables

VELM

- Support clip for Velcro type hook-and-loop strip
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:


Glass fiber reinforced polyamide
self-extinguishing according to UL94-V0

Advantages



- Easy mounting by screwing
- Reusable

Accessories

- VEL stripe
- PRF-ECL nut and CHC6 screw



For strip
30mm



DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Range of tightening (mm)	For screw	For strips width (mm)	Price each 1 to 9
VEL30-M6-20100	20-100	M6	30	7,70 €

Dimensions in mm

Fax: 0 825 88 6000 Service 0,15 €/mln + prix appel

cial2@hpceurope.com


WEB
04/2021

HPC

Our other products



SF_ZZ
Deep groove ball bearing, Stainless steel



JFM
Flanged polymer bush, Universal polymer



PRF JL2
Lip seal for panel, Door seal - Ø 2mm



BCH_SS
Mushroom headed button, M3 to M8



BOX-TOR-B
Box set of Nitrile O-rings in nitrile, 20.38 x 1.78mm to 50.16 x 5.34



BAC110
Swivel storage bin, Adjustable support



BOXINS300
Box set of self tapping inserts, Boxed set - For hard materials



CLSCLP_SS
Clevis components, short version, Stainless steel - short range




KB_WW
Closed linear precision bearing, Economy range



PTAF100-PAMF100
Articulated fixable foot with pressed base Ø100, Ø 100



ESCON
Speed controller 5A accessories, Kit of 4 cables for DC motor



H0
Crossed helical gear crossed axis at 90°, Machined plastic (delrin)

Complementary products



VELprf
Clip-on base for hook-and-loop strip, Polyamide



VELM4
Screw-on base for hook-and-loop strip, Polyamide



VELM6
Screw-on base for hook-and-loop strip, Polyamide