Self-gripping cable strip

VEL For electric and pneumatic cables

- ***Velcro type tie for fixing or bundling cables***
- *1 "loop" side, 1 "hook" side*
- *Ideal for fixing cables on aluminum profiles with the* **VEL-PRF** *bases*
- *Sold in roll*
- *Materials:*
  Self-extinguishing polypropylene according to UL94-V2




Advantages

- *Easy mounting*
- *Reusable hundreds of times*
- *Different sizes of hook-and-loop strips available*
- *No risk of injury or damage to cables unlike Rilsan cable ties*
- *Cut-out for easy lengthening.*

Accessories

- **VEL-M** *or* **VEL-PRF** *base*



Use on the base



Use alone

DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-10%	On request


Part number	Width (mm)	Length (metre)	Price each
VEL7.5-15/B	7,5	15	38,59 €
VEL10-25/B	10	25	80,53 €
VEL20-25/B	20	25	98,98 €
VEL30-25/B	30	25	204,70 €

**Depending on availability - Dimensions in mm*

Clip-on base for hook-and-loop strip

For electric and pneumatic cables VELPRF

- **Support clip for Velcro type hook-and-loop strip**
- Connecting element for fixing a cable on a **Minitec PRF** aluminum profile
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:
  Glass fiber reinforced polyamide self-extinguishing according to UL94-V0





Advantages


- Easy mounting by 45° rotation
- Reusable
- Different sizes of hook-and-loop strips available


Accessories

- **VEL** stripe











DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Range of Tightening (mm)	For strip Width (mm)	A	B	H1	Price each 1 to 9
VEL7.5-PRF-420	4-20	7,5/10	19	15	15,35	4,19 €
VEL10-PRF-420	4-20	7,5/10	19	15	15,35	4,19 €
VEL20-PRF-835	8-35	20	29	26	18,05	4,36 €
VEL20-PRF-1060	10-60	20	36	26	18,05	4,51 €

**Depending on availability - Dimensions in mm*

Screw-on base for hook-and-loop

VELM For electric and pneumatic cables

- **Support clip for Velcro type hook-and-loop strip**
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:
  Glass fiber reinforced polyamide
  self-extinguishing according to UL94-V0




For 7.5 to 20 mm strips

Advantages

- Easy mounting by screwing
- Reusable
- Different sizes of hook-and-loop strips available

Accessories


- **VEL** stripe
- **PRF-ECL** nut and **FHC** screw











DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request


Part number	Range of tightening (mm)	For screw	For strips width (mm)	A	B	H	Price each 1 to 9
VEL7.5-M4-420	4-20	M4	7,5	18,6	15	8,6	3,68 €
VEL10-M4-420	4-20	M4	10,0	18,6	15	8,6	3,68 €
VEL20-M5-835	8-35	M4/M5	20,0	29,0	26	11,3	3,85 €
VEL20-M5-1060	10-60	M4/M5	20,0	36,0	26	11,3	4,01 €

**Depending on availability - Dimensions in mm*

Screw-on base for hook-and-loop

For electric and pneumatic cables VELM

- **Support clip for Velcro type hook-and-loop strip**
- Anti-return clip (the strips can only pass in one direction) for optimum cable tightening
- Materials:
  Glass fiber reinforced polyamide
  self-extinguishing according to UL94-V0



Advantages

- Easy mounting by screwing
- Reusable

Accessories


- **VEL** stripe
- **PRF-ECL** nut and **CHC6** screw














DISCOUNTS

Qty	1+	10+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Range of tightening (mm)	For screw	For strips width (mm)	Price each 1 to 9
VEL30-M6-20100	20-100	M6	30	7,70 €

Dimensions in mm

Our other products



E15

Right angle helical reducers, from 0.40 to 2.53 Nm



PTAF100-PAMF100

Articulated fixable foot with pressed base Ø100, Ø 100



PRF-SMA

Closing system for aluminium profile, Easily adjustable lock



NCT

Square tube connector, Fixed angle



BOX-WM

Box set of washer - DIN125, Box set of steel washers



NT92

Spur gear coaxial gearbox, from 15 to 40 Nm - Inline




DZYSS

Stainless steel cylindrical stop, stainless steel



FGWA

End support, With base



PPS

Lifting ring, Universal threaded



PTAF80-PAMF80

Articulated fixable foot with pressed



RVM25

Manually operated gearbox, Bevel



NPCR

Adjustable cell support, Adjustable

Complementary products



VEL

Self-gripping cable strip, electric and pneumatic cables



VELprf

Clip-on base for hook-and-loop strip, Polyamide



VELM6

Screw-on base for hook-and-loop strip, Polyamide