

Hexagonal headed screw with collar



VHEH_{HUSS}

Hygienic Usit®

- Hexagonal headed bolt with collar for use with Hygienic Usit® sealing washers

- Material:

Stainless steel 1.4404 (316L)
Polished mirror finish

Advantages


- When combined with the RDE washer, the seal obtained is ideal in areas involving contact with products or inside aseptic insulators.
- Due to the extremely low surface roughness, almost no dirt particles will adhere to the screw.
- The high gloss polished surface allows easy cleaning.
- There is no countersink or recess on the screw head and no indentations or notching under the head.

Warning


- A totally cavity-free, watertight seal will only be achieved when the RDE sealing washer is used with the specially modified VHEM screw

Accessories

- RDE sealing washer (tome 1 p.607 to p.609)
- EBH cap nut with collar (tome 1 p.613)
- Tools (spanner, socket...) (tome 1 p.627 to p.629)



A FORM



B FORM



VHEH + RDE + EBH assembled together

DISCOUNTS

Qty	1+	5+	10+
Disc	Net	-5%	On request

Part number	Form	ØD	L	ØD1	B	K	R	SW	Price each
									1 to 4
VHEH4-8/HUSS	A	M4	8	10,8	-	6,9	0,45	7	5,92 €
VHEH4-10/HUSS	A	M4	10	10,8	-	6,9	0,45	7	5,98 €
VHEH4-12/HUSS	A	M4	12	10,8	-	6,9	0,45	7	6,10 €
VHEH4-16/HUSS	A	M4	16	10,8	-	6,9	0,45	7	6,33 €
VHEH4-20/HUSS	A	M4	20	10,8	-	6,9	0,45	7	6,61 €
VHEH4-25/HUSS	B	M4	25	10,8	14	6,9	0,45	7	7,15 €
VHEH4-30/HUSS	B	M4	30	10,8	14	6,9	0,45	7	7,43 €
VHEH4-35/HUSS	B	M4	35	10,8	14	6,9	0,45	7	7,88 €
VHEH4-40/HUSS	B	M4	40	10,8	14	6,9	0,45	7	8,33 €

All dimensions in mm

Part number	Form	ØD	L	ØD1	B	K	R	SW	Price each
									1 to 4
VHEH5-10/HUSS	A	M5	10	11,8	-	8,5	0,5	8	5,07 €
VHEH5-12/HUSS	A	M5	12	11,8	-	8,5	0,5	8	5,16 €
VHEH5-16/HUSS	A	M5	16	11,8	-	8,5	0,5	8	5,23 €
VHEH5-20/HUSS	A	M5	20	11,8	-	8,5	0,5	8	5,68 €
VHEH5-25/HUSS	B	M5	25	11,8	16	8,5	0,5	8	5,97 €
VHEH5-30/HUSS	B	M5	30	11,8	16	8,5	0,5	8	6,70 €
VHEH5-35/HUSS	B	M5	35	11,8	16	8,5	0,5	8	7,43 €
VHEH5-40/HUSS	B	M5	40	11,8	16	8,5	0,5	8	8,07 €
VHEH5-45/HUSS	B	M5	45	11,8	16	8,5	0,5	8	9,47 €
VHEH5-50/HUSS	B	M5	50	11,8	16	8,5	0,5	8	10,81 €
VHEH6-12/HUSS	A	M6	12	14	-	9,2	0,55	10	6,46 €
VHEH6-16/HUSS	A	M6	16	14	-	9,2	0,55	10	6,61 €
VHEH6-20/HUSS	A	M6	20	14	-	9,2	0,55	10	6,83 €
VHEH6-25/HUSS	A	M6	25	14	-	9,2	0,55	10	7,30 €
VHEH6-30/HUSS	B	M6	30	14	18	9,2	0,55	10	7,93 €
VHEH6-35/HUSS	B	M6	35	14	18	9,2	0,55	10	8,73 €
VHEH6-40/HUSS	B	M6	40	14	18	9,2	0,55	10	9,41 €
VHEH6-45/HUSS	B	M6	45	14	18	9,2	0,55	10	10,17 €
VHEH6-50/HUSS	B	M6	50	14	18	9,2	0,55	10	11,11 €
VHEH6-60/HUSS	B	M6	60	14	18	9,2	0,55	10	15,40 €
VHEH8-16/HUSS	A	M8	16	18	-	11,7	0,6	13	10,69 €
VHEH8-20/HUSS	A	M8	20	18	-	11,7	0,6	13	10,95 €
VHEH8-25/HUSS	A	M8	25	18	-	11,7	0,6	13	11,45 €
VHEH8-30/HUSS	A	M8	30	18	-	11,7	0,6	13	11,81 €
VHEH8-35/HUSS	A	M8	35	18	-	11,7	0,6	13	12,71 €
VHEH8-40/HUSS	B	M8	40	18	22	11,7	0,6	13	13,58 €
VHEH8-45/HUSS	B	M8	45	18	22	11,7	0,6	13	14,91 €
VHEH8-50/HUSS	B	M8	50	18	22	11,7	0,6	13	15,75 €
VHEH8-60/HUSS	B	M8	60	18	22	11,7	0,6	13	17,63 €
VHEH8-70/HUSS	B	M8	70	18	22	11,7	0,6	13	19,08 €
VHEH8-80/HUSS	B	M8	80	18	22	11,7	0,6	13	23,55 €
VHEH10-20/HUSS	A	M10	20	22	-	14	0,75	16	13,91 €
VHEH10-25/HUSS	A	M10	25	22	-	14	0,75	16	14,09 €
VHEH10-30/HUSS	A	M10	30	22	-	14	0,75	16	14,76 €
VHEH10-35/HUSS	A	M10	35	22	-	14	0,75	16	15,71 €
VHEH10-40/HUSS	A	M10	40	22	-	14	0,75	16	17,30 €
VHEH10-45/HUSS	B	M10	45	22	26	14	0,75	16	18,25 €
VHEH10-50/HUSS	B	M10	50	22	26	14	0,75	16	19,44 €
VHEH10-60/HUSS	B	M10	60	22	26	14	0,75	16	21,09 €
VHEH10-70/HUSS	B	M10	70	22	26	14	0,75	16	23,30 €
VHEH10-80/HUSS	B	M10	80	22	26	14	0,75	16	25,45 €
VHEH12-25/HUSS	A	M12	25	26,6	-	17	0,9	18	20,48 €
VHEH12-30/HUSS	A	M12	30	26,6	-	17	0,9	18	22,30 €
VHEH12-35/HUSS	A	M12	35	26,6	-	17	0,9	18	22,77 €
VHEH12-40/HUSS	A	M12	40	26,6	-	17	0,9	18	24,72 €
VHEH12-45/HUSS	A	M12	45	26,6	-	17	0,9	18	26,53 €
VHEH12-50/HUSS	B	M12	50	26,6	30	17	0,9	18	27,64 €
VHEH12-60/HUSS	B	M12	60	26,6	30	17	0,9	18	30,29 €
VHEH12-70/HUSS	B	M12	70	26,6	30	17	0,9	18	32,99 €
VHEH12-80/HUSS	B	M12	80	26,6	30	17	0,9	18	38,96 €

All dimensions in mm

- Hexagonal headed bolt with collar for use with Hygienic Usit® sealing washers

- Material:

Stainless steel 1.4404 (316L)

Polished mirror finish

Advantages



- When combined with the RDE washer, the seal obtained is ideal in areas involving contact with products or inside aseptic insulators.
- Due to the extremely low surface roughness, almost no dirt particles will adhere to the screw.
- The high gloss polished surface allows easy cleaning.
- There is no countersink or recess on the screw head and no indentations or notching under the head.

Warning


- A totally cavity-free, watertight seal will only be achieved when the RDE sealing washer is used with the specially modified VHEH screw

Accessories

- RDE sealing washer (tome 1 p.607 to p.609)
- EBH flanged cap nut (tome 1 p.613)
- Tools (spanner, socket...) (tome 1 p.627 to p.629)



A FORM



B FORM



VHEH + RDE + EBH assembled together

DISCOUNTS

Qty	1+	5+	10+
Disc	Net	-5%	On request

Part number	Form	ØD	L	ØD1	B	K	R	SW	Price each
									1 to 4
VHEH16-30/HUSS	A	M16	30	35	-	21,8	1,2	24	30,92 €
VHEH16-35/HUSS	A	M16	35	35	-	21,8	1,2	24	31,88 €
VHEH16-40/HUSS	A	M16	40	35	-	21,8	1,2	24	32,68 €
VHEH16-45/HUSS	A	M16	45	35	-	21,8	1,2	24	34,47 €
VHEH16-50/HUSS	A	M16	50	35	-	21,8	1,2	24	36,65 €
VHEH16-60/HUSS	A	M16	60	35	-	21,8	1,2	24	38,75 €
VHEH16-70/HUSS	B	M16	70	35	38	21,8	1,2	24	43,04 €
VHEH16-80/HUSS	B	M16	80	35	38	21,8	1,2	24	47,41 €

All dimensions in mm