
Solid handwheel with rotating handle

VPPTss

304 stainless steel

- ***Handwheel with rotating handle***
- *Finish: turned, natural*
- *Solid hub with centering point*
- *Material:*
  1.4301 stainless steel





DISCOUNTS

Qty	1+	3+	5+	10+
Disc.	List	-5%	-10%	On request


Part N°	ØD1	ØD2	ØD3	L1	L2	L3	L4	Price each 1 to 2
VPPT76/SS	76,20	9,91	22,1	17,02	6,10	27,9	37,90	62,88 €
VPPT101/SS	101,60	11,94	25,9	18,03	7,87	31,7	39,88	70,64 €
VPPT151/SS	152,40	19,05	38,1	22,10	12,70	38,1	63,50	140,56 €
VPPT203/SS	203,20	22,10	45,7	24,13	14,22	45,7	76,20	181,08 €
VPPT254/SS	254,00	22,10	50,8	26,67	15,75	50,8	76,20	282,93 €

All dimensions in mm

Our other products



Moulded plastic bevel gear (nylon), 1:1



Joint for guiding profile, Rounded



Angular clamp, Standard



Ring operated locking bolt, with ring



Locking assembly, Medium/high torque



Moulded plastic bevel gear (nylon), 2:1



Square hinge with riveted pin, not drilled, Square with riveted pin,...



Steel bevel gear, 2:1



Suction cup, 1.5 bellows, silicon



Screw-in garnet hinge, Screw-on



Right angle helical reducers, from 0.40 to 2.53 Nm



Stainless steel closed precision linear bearing, Precision - stainle...

Complementary products



Spoked handwheel, Stainless steel 316



Handwheel without handle, Polyamide



Handwheel with handle, Polyamide



Handwheel with folding handle, Polyamide