Quarter-turn clamp lock

VQT Plastic or stainless steel button

- ***Quarter-tour lock with handle***
- *Locking element*
- *Materials:*
  Nickel-plated steel body
  Steel pins
  Button in black glass fiber reinforced PA or stainless steel
- *Working T°*
  Plastic button +130°C max.
  Stainless steel button +200°C max.



Advantages


- *Allows locking or unlocking without tools and without quarter-tour screws.*
- *Lock On/Off display.*
- *Saves time by avoiding the handling of tools.*

Infos


- *The M2 or M3 fixing screws are supplied*
- *Mounting option A for 6mm to 12 mm plates.*
- *Mounting option B for 12 to 20mm plates.*
- *The specified forces apply only for use with the* ***VQT PLQ*** *sleeves.*

Accessories


- *Clamping plates* **VQT-PLQ** ***(tome 1 p.226-227)***




Use



Make sure the handle is in the “OFF” position.




Press the pin of the quarter-turn lock into the clamping plate.



To lock the components, turn the handle to the “ON” position. A click indicates the opening/closing

Part number	Clamping force (N)	Resistance shearing (kN)	Pullout force (kN)	H	H1	ØM
Plastic button						
VQT5-15/PA	60	1,8	1,2	19,0	6,5	M2x3
VQT8-17/PA	90	3,2	2,6	26,0	10,0	M3x4
VQT8-23/PA	90	3,2	2,6	26,0	10,0	M3x4
Stainless steel button						
VQT5-15/SS	60	1,8	1,2	19,0	6,5	M2x3
VQT8-17/SS	90	3,2	2,6	25,5	10,0	M3x4
VQT8-23/SS	90	3,2	2,6	25,5	10,0	M3x4

Dimensions in mm



Example of use:
change the positions of the camera

DISCOUNTS

Qty	1+	4+	8+
Disc.	List	-5%	On request

Part number	ØD	L	ØD1	ØD2	ØD3	ØD4	ØD5	ØD6	ØD7	ØD8	T	T1	Price each 1 to 3
Plastic button													
VQT5-15/PA	5	15,5	14	25	20	21	14	26	4,4	2,4	6	6-10	53,82 €
VQT8-17/PA	8	17,0	18	34	32	28	18	35	6,5	3,4	6	6-14	55,33 €
VQT8-23/PA	8	23,0	18	34	32	28	18	35	6,5	3,4	12	12-20	55,33 €
Stainless steel button													
VQT5-15/SS	5	15,5	14	25	20	21	14	26	4,4	2,4	6	6-10	67,63 €
VQT8-17/SS	8	17,0	18	34	32	28	18	35	6,5	3,4	6	6-14	70,72 €
VQT8-23/SS	8	23,0	18	34	32	28	18	35	6,5	3,4	12	12-20	70,72 €

Dimensions in mm

Quarter-turn clamp lock - Clamping plate


VQTPLQ/P


Wall mounting


- ***Clamping plate for VQT quarter-turn lock***
- *Mounting for plate thickness 6 to 10mm.*
- *Materials:*
  Nickel-plated steel body
  Stainless steel nut


Accessories

- ***VQT** quarter-tour lock*
  (tome 1 p.224)









Surface-mounted clamping plate for 6 to 10mm plates.

DISCOUNTS

Qty	1+	4+	8+
Disc.	List	-5%	On request

Part number	ØD	ØD2	ØD4	A	M	H2	SW
VQT5-PLQ/P	5	25	21	10,5	M14X1,5	8	22
VQT8-PLQ/P	8	32	26	13,0	M20X1,5	10	30

Part number	H	H1	ØD5	ØD6	L	Price each 1 to 3
VQT5-PLQ/P	16	4,5	15	25	3,5	26,02 €
VQT8-PLQ/P	18	5,5	21	32	3,5	26,75 €

Dimensions in mm

Quarter-turn clamp lock - Clamping plate

Flush mounting

VQTPLQ/N

- ***Clamping plate for VQT quarter-turn lock***
- *Mounting for plate thickness over 10mm.*
- *Materials:*
  Nickel-plated steel body





Infos


- *The M2 or M3 fixing screws are supplied*


Accessories


- **VQT** *quarter-tour lock*
  (tome 1 p.224)











Surface-mounted clamping plate ≥10mm plates.

DISCOUNTS

Qty	1+	4+	8+
Disc.	List	-5%	On request

Part number	ØD	ØD1	ØD2	ØD4	H2	SW
VQT5-PLQ/N	5	14	25	21	8	22
VQT8-PLQ/N	8	20	32	26	10	30

Part number	H	H1	ØD3 for screw DIN912	ØD5	ØD6	L	L1	Price each 1 to 3
VQT5-PLQ/N	9	4,5	M2	14	26	5	4	24,13 €
VQT8-PLQ/N	11	5,5	M3	20	33	6	5	25,63 €

Dimensions in mm