

Hexagonal head screw **DIN933**

VTHBR

Brass

- Screw conforming to DIN933

- Material:

Brass



DISCOUNTS

Qty	1+	6+	11+
Disc.	Net	-10%	On request

Part N°	ØM	Pitch	L	A (max)	K	A/F Across flats	Qty/pack	Price each 1 to 5
VTH4-10/BR/B	M4	0,70	10	2,10	2,8	7	100	9,23 €
VTH4-16/BR/B	M4	0,70	16	2,10	2,8	7	100	10,78 €
VTH4-20/BR/B	M4	0,70	20	2,10	2,8	7	100	12,06 €
VTH4-25/BR/B	M4	0,70	25	2,10	2,8	7	100	14,81 €
VTH4-30/BR/B	M4	0,70	30	2,10	2,8	7	100	16,96 €
VTH5-10/BR/B	M5	0,80	10	2,40	3,5	8	100	12,70 €
VTH5-16/BR/B	M5	0,80	16	2,40	3,5	8	100	18,25 €
VTH5-20/BR/B	M5	0,80	20	2,40	3,5	8	100	19,96 €
VTH5-25/BR/B	M5	0,80	25	2,40	3,5	8	100	21,22 €
VTH5-30/BR/B	M5	0,80	30	2,40	3,5	8	100	25,80 €
VTH5-40/BR/B	M5	0,80	40	2,40	3,5	8	100	32,67 €
VTH6-10/BR/B	M6	1,00	10	3,00	4,0	10	100	21,60 €
VTH6-20/BR/B	M6	1,00	20	3,00	4,0	10	100	28,81 €
VTH6-25/BR/B	M6	1,00	25	3,00	4,0	10	100	33,84 €
VTH6-30/BR/B	M6	1,00	30	3,00	4,0	10	100	37,34 €
VTH6-40/BR/B	M6	1,00	40	3,00	4,0	10	100	44,32 €
VTH6-50/BR/B	M6	1,00	50	3,00	4,0	10	100	55,34 €
VTH8-16/BR/B	M8	1,25	16	3,75	5,3	13	100	53,36 €
VTH8-20/BR/B	M8	1,25	20	3,75	5,3	13	100	61,11 €
VTH8-25/BR/B	M8	1,25	25	3,75	5,3	13	100	67,75 €
VTH8-30/BR/B	M8	1,25	30	3,75	5,3	13	100	71,22 €
VTH8-40/BR/B	M8	1,25	40	3,75	5,3	13	100	110,17 €
VTH8-50/BR/B	M8	1,25	50	3,75	5,3	13	100	93,79 €
VTH8-60/BR/B	M8	1,25	60	3,75	5,3	13	100	116,77 €

All dimensions in mm

Our other products



BMM
Knurled knob - male,
Knurled



CLM
Male clevis end,
Stainless steel short




BUT
Panel stop, Panel stop



LVT
Miniature motorised
actuator 1A, 1 amp



BAN
Angular clamp,
Universal



H1
Crossed helical gear
crossed axis at 90°,
Machined plastic
(delrin)



HRV
V- rail guidance
Simple Select®
system, Rail with
carriage



GP75
Spring loaded toggle
latch, Standard
(GP75)




CHA35
Hinge for aluminium
profile, Hinge



RFKfp
Stainless steel
gearbox - accessories,



WJUM20
Drylin® W bearing
block, Slide



PRF-SCREEN-1
Screen support, Basic
support

Complementary products



WINGbr
Wing screw, hand
tightened DIN316,
Brass DIN 316



WINGbrEcrou
Manually tightened
wing nut DIN315,
Brass DIN 315



SHNbr
Hexagonal nut
DIN934, Brass



SHWbr
Washer - DIN125,
Brass