

Hexagonal head screw **DIN933**

VTHBR

Brass

- Screw conforming to DIN933

- Material:

Brass



DISCOUNTS

Qty	1+	6+	11+
Disc.	Net	-10%	On request

Part N°	ØM	Pitch	L	A (max)	K	A/F Across flats	Qty/pack	Price each 1 to 5
VTH4-10/BR/B	M4	0,70	10	2,10	2,8	7	100	9,23 €
VTH4-16/BR/B	M4	0,70	16	2,10	2,8	7	100	10,78 €
VTH4-20/BR/B	M4	0,70	20	2,10	2,8	7	100	12,06 €
VTH4-25/BR/B	M4	0,70	25	2,10	2,8	7	100	14,81 €
VTH4-30/BR/B	M4	0,70	30	2,10	2,8	7	100	16,96 €
VTH5-10/BR/B	M5	0,80	10	2,40	3,5	8	100	12,70 €
VTH5-16/BR/B	M5	0,80	16	2,40	3,5	8	100	18,25 €
VTH5-20/BR/B	M5	0,80	20	2,40	3,5	8	100	19,96 €
VTH5-25/BR/B	M5	0,80	25	2,40	3,5	8	100	21,22 €
VTH5-30/BR/B	M5	0,80	30	2,40	3,5	8	100	25,80 €
VTH5-40/BR/B	M5	0,80	40	2,40	3,5	8	100	32,67 €
VTH6-10/BR/B	M6	1,00	10	3,00	4,0	10	100	21,60 €
VTH6-20/BR/B	M6	1,00	20	3,00	4,0	10	100	28,81 €
VTH6-25/BR/B	M6	1,00	25	3,00	4,0	10	100	33,84 €
VTH6-30/BR/B	M6	1,00	30	3,00	4,0	10	100	37,34 €
VTH6-40/BR/B	M6	1,00	40	3,00	4,0	10	100	44,32 €
VTH6-50/BR/B	M6	1,00	50	3,00	4,0	10	100	55,34 €
VTH8-16/BR/B	M8	1,25	16	3,75	5,3	13	100	53,36 €
VTH8-20/BR/B	M8	1,25	20	3,75	5,3	13	100	61,11 €
VTH8-25/BR/B	M8	1,25	25	3,75	5,3	13	100	67,75 €
VTH8-30/BR/B	M8	1,25	30	3,75	5,3	13	100	71,22 €
VTH8-40/BR/B	M8	1,25	40	3,75	5,3	13	100	110,17 €
VTH8-50/BR/B	M8	1,25	50	3,75	5,3	13	100	93,79 €
VTH8-60/BR/B	M8	1,25	60	3,75	5,3	13	100	116,77 €

All dimensions in mm

Our other products



SBF

Sealed flange bearing unit for Food Industry, cover




PX

Optional output shaft stainless steel, P gearboxes single sided outp...



CHMR50

Worm and wheel gear reducer, up to 107 Nm



ACL-PR

Joining plate for aluminium profile, Right angled connection



SSDB

Stainless steel bevel gear, 2:1



BSB

Ball screw bearing unit, Support



PSG3S

Spur gear - precision range, Stainless steel 303



SH2

Parallel axis helical gear, Machined plastic (delrin)



CCL

Standard wire thimble, Steel



CHAC4040NP

Square hinge with riveted pin, not



ZA

Shaft for linear guides, Hardened



PF55

Worm and wheel gear reducer, up to 57 Nm

Complementary products



WINGbr

Wing screw, hand tightened DIN316, Brass DIN 316



WINGbrEcrou

Manually tightened wing nut DIN315, Brass DIN 315



SHNbr

Hexagonal nut DIN934, Brass



SHWbr

Washer - DIN125, Brass