



Part number	Teeth Z	PCD ØP	outside ØD	Boss ØM	Bore ØA	Weight (kg)		Stock*	Price each 1 to 5 XG	
						YG	XG		YG	XG
YG0.8-34	34	27,20	28,80	20,00	6	0,063	0,042	-	31,15 €	
YG0.8-35	35	28,00	29,60	20,00	6	0,066	0,045	✓	31,23 €	
YG0.8-36	36	28,80	30,40	20,00	6	0,069	0,048	-	31,26 €	
YG0.8-37	37	29,60	31,20	20,00	6	0,072	0,050	-	31,33 €	
YG0.8-38	38	30,40	32,00	20,00	6	0,075	0,053	✓	31,42 €	
YG0.8-39	39	31,20	32,80	20,00	6	0,078	0,056	-	31,49 €	
YG0.8-40	40	32,00	33,60	20,00	6	0,081	0,059	✓	31,52 €	
YG0.8-41	41	32,80	34,40	20,00	6	0,084	0,062	-	31,58 €	
YG0.8-42	42	33,60	35,20	20,00	6	0,087	0,066	-	31,66 €	
YG0.8-43	43	34,40	36,00	20,00	6	0,090	0,069	-	31,68 €	
YG0.8-44	44	35,20	36,80	20,00	6	0,093	0,072	-	31,86 €	
YG0.8-45	45	36,00	37,60	20,00	6	0,097	0,076	-	32,00 €	
YG0.8-46	46	36,80	38,40	20,00	6	0,100	0,079	-	32,10 €	
YG0.8-47	47	37,60	39,20	20,00	6	0,104	0,083	-	32,16 €	
YG0.8-48	48	38,40	40,00	20,00	6	0,108	0,086	-	32,30 €	
YG0.8-49	49	39,20	40,80	20,00	6	0,111	0,090	-	32,33 €	
YG0.8-50	50	40,00	41,60	20,00	6	0,115	0,094	✓	32,35 €	
YG0.8-51	51	40,80	42,40	20,00	6	0,119	0,098	-	32,62 €	
YG0.8-52	52	41,60	43,20	20,00	6	0,123	0,102	✓	32,74 €	
YG0.8-53	53	42,40	44,00	20,00	6	0,127	0,106	-	32,84 €	
YG0.8-54	54	43,20	44,80	20,00	6	0,131	0,110	✓	32,99 €	
YG0.8-55	55	44,00	45,60	20,00	6	0,135	0,114	-	33,18 €	
YG0.8-56	56	44,80	46,40	20,00	6	0,140	0,118	-	33,27 €	
YG0.8-57	57	45,60	47,20	20,00	6	0,144	0,123	-	33,50 €	
YG0.8-58	58	46,40	48,00	20,00	6	0,148	0,127	-	33,60 €	
YG0.8-59	59	47,20	48,80	20,00	6	0,153	0,132	-	33,69 €	
YG0.8-60	60	48,00	49,60	20,00	6	0,157	0,136	-	33,85 €	
YG0.8-61	61	48,80	50,40	20,00	6	0,162	0,141	-	34,02 €	
YG0.8-62	62	49,60	51,20	20,00	6	0,167	0,146	-	34,17 €	
YG0.8-63	63	50,40	52,00	20,00	6	0,172	0,151	-	34,36 €	
YG0.8-64	64	51,20	52,80	20,00	6	0,177	0,155	-	34,48 €	
YG0.8-66	66	52,80	54,40	30,00	8	0,210	0,164	-	34,56 €	
YG0.8-68	68	54,40	56,00	40,00	8	0,254	0,174	-	34,73 €	
YG0.8-70	70	56,00	57,60	40,00	8	0,265	0,185	-	35,01 €	
YG0.8-75	75	60,00	61,60	40,00	8	0,293	0,213	-	35,44 €	
YG0.8-76	76	60,80	62,40	40,00	8	0,299	0,218	✓	36,25 €	
YG0.8-80	80	64,00	65,60	40,00	8	0,323	0,242	-	37,32 €	
YG0.8-86	86	68,80	70,40	40,00	8	0,361	0,281	-	37,84 €	
YG0.8-88	88	70,40	72,00	40,00	8	0,374	0,294	-	38,50 €	
YG0.8-90	90	72,00	73,60	40,00	8	0,388	0,308	✓	39,30 €	
YG0.8-96	96	76,80	78,40	40,00	8	0,431	0,351	-	39,95 €	
YG0.8-100	100	80,00	81,60	40,00	8	0,461	0,381	✓	43,85 €	
YG0.8-112	112	89,60	91,20	40,00	8	0,559	0,479	-	50,87 €	
YG0.8-120	120	96,00	97,60	40,00	8	0,630	0,550	-	57,79 €	
YG0.8-127	127	101,60	103,20	40,00	10	0,697	0,617	-	69,41 €	
YG0.8-128	128	102,40	104,00	50,00	10	0,750	0,624	-	71,65 €	
YG0.8-140	140	112,00	113,60	50,00	10	0,873	0,748	-	75,72 €	
YG0.8-150	150	120,00	121,60	50,00	12	0,985	0,859	-	87,52 €	
YG0.8-175	175	140,00	141,60	50,00	12	1,298	1,172	-	111,24 €	
YG0.8-200	200	160,00	161,60	50,00	15	1,658	1,533	-	124,72 €	

On request

↓ **Gears available up to this size** ↓

<b>YG0.8-173</b>	173	138,40	140,00	Dimensions : contact us	on request
------------------	-----	--------	--------	-------------------------	------------

\*Depending on availability - Dimensions in mm

## Our other products



CAP882

Flexible slat top chain acetal, Large range 882



CDPC

Flanged drill bushing, Steel



PTMR

Telescopic furniture foot, threaded stud



PAMF120

Articulated fixable foot, pressed bolt-down base Ø 120, Ø 120




Q1

Self-aligning radial ball bearing, Steel



SRP

Slotted spring pin ISO8752, Split ISO 8752



JFM

Flanged polymer bush, Universal polymer



TBbutee

Axial thrust bearing, Steel balls



ABL100005

Antistatic brush, Standard



MEFC

Flanged sintered ferrous bush, Self-lubricating FP20



SH1

Parallel axis helical gear, Steel 20NCD2



GGP

Male wing knob, Technopolymer with brass spindle

## Complementary products




ZG0

Plastic spur gear, Machined plastic (delrin)



R\_RR

Narrow spur rack, Steel



TR

Spur round rack, Stainless steel - module 0,25-1,5