
Machined plastic bevel gear

Del

Ratio 1:1

Delrin

- ***Module 3 to 6***
- *Machined parts*
- *Pressure angle 20°*
- *Teeth Gleason*
- *Material:*
  Delrin plastic
- *Working temp -50° to +80°C*
- *Two identical gears must be ordered to make a pair*





TORQUE AND POWER INDICATION	For 20 teeth at 1000 rpm			
	3.0 MOD	4.0 MOD	5.0 MOD	6.0 MOD
Torque (Nm)	1.93	2.84	5	8
Power (kW)	0.20	0.83	0.54	0.85

DISCOUNTS

Qty	1+	6+	30+
Disc.	List	-22%	On request

Part number	Teeth Z	Module	ØP	E	ØD	ØA	ØM	F	G	H	ØR	T	Price each 1 to 5
ZB3-16	16	3	48	44,0	52,24	15	40,0	29,08	16,00	11	M5	8	On request
ZB3-19	19		57	49,0	61,24	16	50,0	31,01	17,02	13	M5	9	
ZB3-26	26		78	65,0	82,24	18	64,0	40,03	19,03	18	M6	10	
ZB3-30	30		90	68,5	94,24	20	76,0	39,65	16,51	21	M6	8	
ZB4-16	16	4	64	55,5	69,66	15	50,0	35,81	16,49	15	M5	8	
ZB4-19	19		76	65,0	81,66	18	62,5	41,43	20,24	18	M6	10	
ZB4-26	26		104	82,0	109,66	22	85,0	48,69	20,50	24	M6	10	
ZB4-30	30		120	90,0	125,66	25	102,0	51,51	21,00	28	M8	11	
ZB5-16	16	5	80	70,0	87,10	18	60,0	46,13	20,00	20	M8	11	
ZB5-20	20		100	80,0	107,10	20	80,0	49,04	21,50	24	M8	12	
ZB5-25	25		125	100,0	132,10	25	80,0	59,47	24,00	28	M10	14	
ZB5-30	30		150	114,0	157,10	30	100,0	65,87	26,00	35	M10	15	
ZB6-16	16	6	96	80,0	104,52	25	75,0	50,10	22,00	22	M10	12	
ZB6-20	20		120	90,0	128,52	30	96,0	52,32	18,50	28	M10	12	
ZB6-25	25		150	115,0	158,52	35	100,0	67,29	24,00	35	M10	14	
ZB6-30	30		180	130,0	188,52	35	120,0	72,24	28,00	42	M10	16	

Dimensions in mm

Our other products


DOMI80

Accessories, Fixing kit


CHAR7520

Spring hinge, screwed


RAG-12-M8

Roller guide accessory, Anchoring system


DBL880

Idler for slat top chain, Ranges 880 and 881


BOXINS300

Box set of self tapping inserts, Boxed set - For hard materials


AC156-157


Strike for toggle latch, 25.5mm


VTLB

Three-lobed knob, Thermoplastic / Brass or stainless steel insert


PRES5HR

Manual workbench press, Force up to 500kg


BPHFclip

Clip for ball transfer unit, Insert clip - Installing from above


PTR

Idler chain sprocket, For standard applications


AT5-16ECO

AT type timing pulley, Economy range - AT5 aluminium


T5-10ECO

T type timing pulley, Economy range - T5 aluminium

Complementary products


SSB

Stainless steel bevel gear, 1:1


MEB

Moulded plastic bevel gear (nylon), 1:1