



Plastic spur gear

Machined Delrin

Module
6.0

- Machined parts
- Precision class 9
- Pressure angle 20°
- Working temp. -50°C to +80°C

Option

- Different number of teeth: a datasheet is available in PDF on www.hpceurope.com


Torque indication	
For 50 teeth 1000 rpm	
Delrin	
Nm	140



ZHG



ZHPG (optional)



DISCOUNTS

Qty	1+	4+	20+
Disc.	List	-5%	On request


Part number	Teeth Z	PCD ØP	Outside ØD	Boss ØM	Bore ØA	Price each 1 to 3	
						ZHG	ZHPG
ZHG6-12	12	72,00	84,00	50	25	On request	On request
ZHG6-14	14	84,00	96,00	60	25	On request	
ZHG6-15	15	90,00	102,00	65	25	On request	
ZHG6-18	18	108,00	120,00	80	30	96,96 €	
ZHG6-19	19	114,00	126,00	80	30	On request	
ZHG6-20	20	120,00	132,00	90	30	107,74 €	
ZHG6-21	21	126,00	138,00	90	30	On request	
ZHG6-22	22	132,00	144,00	90	30	On request	
ZHG6-23	23	138,00	150,00	90	30	123,93 €	
ZHG6-24	24	144,00	156,00	90	30	On request	
ZHG6-25	25	150,00	162,00	90	30	134,69 €	
ZHG6-30	30	180,00	192,00	100	30	193,27 €	
ZHG6-31	31	186,00	198,00	100	30	On request	
ZHG6-32	32	192,00	204,00	120	38	On request	
ZHG6-35	35	210,00	222,00	120	38	300,64 €	
ZHG6-38	38	228,00	240,00	120	38	On request	
ZHG6-40	40	240,00	252,00	150	38	On request	
ZHG6-41	41	246,00	258,00	150	38	On request	
ZHG6-42	42	252,00	264,00	150	38	On request	
ZHG6-44	44	264,00	276,00	150	38	On request	
Gears available up to this size							
ZHG6-95	95	570,00	582,00	Dimensions: contact us		On request	

Dimensions in mm

Our other products



Stainless steel Dee shackle with eye bolt, Stainless steel



T type timing belt per metre, T10 Steel cored polyurethane



T type tooth bar stock, T2.5



Stainless steel spur gear, Stainless steel 304L



Manual workbench press accessory for PRES-3HR end PRES-4HR, Micromet...



Connecting plate for T type timing belts, T10



Stainless steel locking bolt, With grip - Stainless steel



Invisible hinge, Invisible - Opening up to 125°



Spur gear - precision range, Stainless steel



Marine hinge for welding/screw



Compression springs in metre length steel,



Moulded plastic bevel gear (nylon), 3:1

Complementary products



Steel spur gear, Steel 20NCD2