

Flat magnet with hook

Ferrite

PLMCR


- White plate with a threaded hole and hook
- Hook supplied
- Max working temperature 150°C

Applications


- POS material, fixing and positioning components

Infos.

- Load-carrying capacity *: Indicative average value at room temperature



A typical application, a key holder



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	Net	-15%	-20%	-30%	On request

Part N°	ØD	E	H	ØA	ØT	Load-carrying capacity* (kg)	Weight (g)	Price each
PLM25-8-M4/CR	25	7	15	8	M4	4	23	3,88 €
PLM36-8-M4/CR	36	7,7	16	8	M4	10	44	4,90 €
PLM50-8-M4/CR	50	10	18,5	8	M4	22	116	7,35 €

All dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

235