

Grey rubber wheel

RBG

For medium loads up to 120kg

- **Light industrial wheel with a semi-elastic solid rubber tyre**

- **Material:**

85° Shore vulcanised grey rubber tyre

Polypropylene rim

- **Smooth central bore**

- **Working temperature range - 20°C to + 60°C**

Advantages

- Soft and silent

- Absorbs shock and vibration

- Will not damage floors



Noise absorbing



ØD



B



C



ØA

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	C	ØA	Maximum load (kg)	Stock*	Price each 1 to 9
RBG50-22/ML	50	22	28	8	40	✓	1,50 €
RBG60-24/ML	60	24	28	8	50	✓	1,92 €
RBG80-23/ML	80	23	28	8	65	✓	3,02 €
RBG100-26/ML	100	26	28	8	75	✓	3,60 €
RBG100-32/ML	100	32	34	10	100	-	4,35 €
RBG125-32/ML	125	32	34	10	120	4	5,63 €

Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel