


Castor with mounting plate

For medium loads up to 110kg

RBGPL

- **Light industrial swivel castor with central hole**
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Materials:
 - Top plate: pressed steel sheet, protected by bright zinc plating
 - Grey vulcanized rubber wheel 85°Shore (see **RBG**)
 - Smooth central bore
- Working temperature range: - 20°C to + 60°C



Advantages

- Soft, silent wheel
- Absorbs shock and vibration
- Will not damage floors



ØD



B



H



L



M



ØT



ØK

DISCOUNTS

| | | | |
|------------|-----|-----|------------|
| Qty | 1+ | 10+ | 30+ |
| Disc. List | -5% | | On request |

| Part number | ØD | B | H | L | M | ØT | Swivel interference load (kg) | Max load (kg) | Stock* | Price each 1 to 9 |
|--------------------------------|-----|----|-----|-------|-------|----|-------------------------------|---------------|--------|-------------------|
| Fixed | | | | | | | | | | |
| RBG50/PL/F | 50 | 22 | 76 | 67x52 | 50x36 | 6 | - | 45 | ✓ | 3,12 € |
| RBG60/PL/F | 60 | 24 | 85 | 67x52 | 50x36 | 6 | - | 55 | ✓ | 3,35 € |
| RBG80/PL/F | 80 | 23 | 106 | 65x54 | 50x36 | 6 | - | 65 | ✓ | 4,37 € |
| RBG100/PL/F | 100 | 26 | 122 | 67x60 | 46x46 | 6 | - | 75 | ✓ | 5,88 € |
| RBG125/PL/F | 125 | 32 | 157 | 95x68 | 73x44 | 8 | - | 110 | ✓ | 7,10 € |
| Swivel | | | | | | | | | | |
| RBG50/PL/P | 50 | 22 | 76 | 64x48 | 50x36 | 6 | 98 | 45 | ✓ | 4,16 € |
| RBG60/PL/P | 60 | 24 | 85 | 64x48 | 50x36 | 6 | 110 | 55 | ✓ | 4,93 € |
| RBG80/PL/P | 80 | 23 | 106 | 64x48 | 50x36 | 6 | 138 | 65 | ✓ | 6,31 € |
| RBG100/PL/P | 100 | 26 | 123 | 64x48 | 50x36 | 6 | 166 | 75 | ✓ | 7,58 € |
| RBG125/PL/P | 125 | 32 | 161 | 90x70 | 70x50 | 8 | 216 | 110 | ✓ | 14,55 € |
| Swivel with double lock | | | | | | | | | | |
| RBG50/PL/PDB | 50 | 22 | 76 | 64x48 | 50x36 | 6 | 172 | 45 | ✓ | 5,79 € |
| RBG60/PL/PDB | 60 | 24 | 85 | 64x48 | 50x36 | 6 | 172 | 55 | ✓ | 6,17 € |
| RBG80/PL/PDB | 80 | 23 | 106 | 64x48 | 50x36 | 6 | 188 | 65 | ✓ | 7,75 € |
| RBG100/PL/PDB | 100 | 26 | 123 | 64x48 | 50x36 | 6 | 188 | 75 | ✓ | 9,05 € |
| RBG125/PL/PDB | 125 | 32 | 161 | 90x70 | 70x50 | 8 | 220 | 110 | ✓ | 16,15 € |

*Depending on availability - Dimensions in mm