

Black rubber covered wheel

For heavy loads up to 215kg


RBN

- Industrial castor with a semi-elastic solid rubber tyre
- Material:
 - 85° Shore vulcanised black rubber tyre
 - Polypropylene rim
- Smooth central bore
- Working temperature range: - 20°C to + 60°C

Advantages

- Soft and silent
- Absorbs shock and vibration
- Will not damage floors

Noise absorbing



ØD



B



C



ØA

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	C	ØA	Maximum load (kg)	Stock*	Price each 1 to 9
RBN80-34/ML	80	34	40	12	75	✓	2,79 €
RBN100-35/ML	100	35	39	12	100	✓	3,31 €
RBN125-38/ML	125	38	45	15	125	✓	5,19 €
RBN150-40/ML	150	40	45	15	150	✓	7,36 €
RBN160-38/ML	160	38	60	20	150	-	7,67 €
RBN200-47/ML	200	47	60	20	215	-	11,04 €

Dimensions in mm

Fax **0 825 88 6000**
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

273