


- Élément de levage

- Sangles polyester haute qualité suivant norme Européenne UNI EN 1492-1
- Sangle plate
- Largeur 30mm
- CMU : charge maximale d'utilisation



F Max
1000kg



0°



F

0°



F x 0,8

≤6°



F x 2

0° à 45°



F x 1,4

45° à 60°



F

0° à 45°



F x 1,4

0° à 45°



F x 1,12

45° à 60°



F

45° à 60°



F x 0,8


REMISES

Qté	1+	4+	10+	15+
Rem. Prix	-5%	-10%	Sur demande	


Références	Fmax (kg)	Longueur		W	E	L1	W2	Prix Uni. 1 à 3
		L						
SGL1-1000	1000	1000		30	7	200	15	
SGL1-1500	1000	1500		30	7	200	15	
SGL1-2000	1000	2000		30	7	200	15	
SGL1-2500	1000	2500		30	7	200	15	
SGL1-3000	1000	3000		30	7	200	15	
SGL1-4000	1000	4000		30	7	200	15	

Dimensions en mm

- **Elément de levage**
- Sangles polyester haute qualité suivant norme Européenne UNI EN 1492-1
- Sangle plate
- Largeur 60mm
- CMU : charge maximale d'utilisation



F Max
2000kg



0°



F

0°



F x 0,8

≤6°



F x 2

0° à 45°



F x 1,4

45° à 60°



F

0° à 45°



F x 1,4

0° à 45°



F x 1,12

45° à 60°



F

45° à 60°



F x 0,8

REMISES

Qté	1+	4+	10+	15+
Rem. Prix	-5%	-10%	Sur demande	Sur demande

Références	Fmax (kg)	Longueur L	W	E	L1	W2	Prix Uni. 1 à 3
SGL2-1000	2000	1000	60	7	300	30	
SGL2-1500	2000	1500	60	7	300	30	
SGL2-2000	2000	2000	60	7	300	30	
SGL2-2500	2000	2500	60	7	300	30	
SGL2-3000	2000	3000	60	7	300	30	
SGL2-4000	2000	4000	60	7	300	30	
SGL2-5000	2000	5000	60	7	300	30	
SGL2-6000	2000	6000	60	7	300	30	
SGL2-8000	2000	8000	60	7	300	30	
SGL2-10000	2000	10000	60	7	300	30	
SGL2-12000	2000	12000	60	7	300	30	

Dimensions en mm


Elingue sangle à 2 boucles

New

SGL3



Gamme jaune CMU 3000kg

- **Élément de levage**
- Sangles polyester haute qualité suivant norme Européenne UNI EN 1492-1
- Sangle plate
- Largeur 90mm
- CMU : charge maximale d'utilisation



F Max
3000kg

F



REMISES

Qté	1+	4+	10+	15+
Rem. Prix	-5%	-10%	Sur demande	


Références	Fmax (kg)	Longueur L	W	E	L1	W2	Prix Uni. 1 à 3
SGL3-1000	3000	1000	90	7	350	30	
SGL3-2000	3000	2000	90	7	350	30	
SGL3-3000	3000	3000	90	7	350	30	
SGL3-4000	3000	4000	90	7	350	30	
SGL3-5000	3000	5000	90	7	350	30	
SGL3-6000	3000	6000	90	7	350	30	
SGL3-8000	3000	8000	90	7	350	30	
SGL3-10000	3000	10000	90	7	350	30	
SGL3-12000	3000	12000	90	7	350	30	

Dimensions en mm

- **Elément de levage**
- Sangles polyester haute qualité suivant norme Européenne UNI EN 1492-1
- Sangle plate
- Largeur 120mm
- CMU : charge maximale d'utilisation



F Max
4000kg



0°



F

0°



F x 0,8

≤6°



F x 2

0° à 45°



F x 1,4

45° à 60°



F

0° à 45°



F x 1,4

0° à 45°



F x 1,12

45° à 60°



F

45° à 60°



F x 0,8

REMISES


Qté	1+	4+	10+	15+
Rem. Prix	-5%	-10%	Sur demande	

Références	Fmax (kg)	Longueur L	W	E	L1	W2	Prix Uni. 1 à 3
SGL4-1000	4000	1000	120	7	425	40	
SGL4-1500	4000	1500	120	7	425	40	
SGL4-2000	4000	2000	120	7	425	40	
SGL4-2500	4000	2500	120	7	425	40	
SGL4-3000	4000	3000	120	7	425	40	
SGL4-4000	4000	4000	120	7	425	40	
SGL4-5000	4000	5000	120	7	425	40	
SGL4-6000	4000	6000	120	7	425	40	
SGL4-8000	4000	8000	120	7	425	40	
SGL4-10000	4000	10000	120	7	425	40	
SGL4-12000	4000	12000	120	7	425	40	

Dimensions en mm



- Élément de levage

- Sangles polyester haute qualité suivant norme Européenne UNI EN 1492-1
- Sangle plate
- Largeur 150mm
- CMU : charge maximale d'utilisation



F Max
5000kg

F



0°



F

0°



F x 0,8

≤6°



F x 2

0° à 45°



F x 1,4

45° à 60°



F

0° à 45°



F x 1,4

0° à 45°



F x 1,12

45° à 60°



F

45° à 60°



F x 0,8

REMISES

Qté	1+	4+	10+	15+
Rem. Prix	-5%	-10%	Sur demande	

Références	Fmax (kg)	Longueur L	W	E	L1	W2	Prix Uni. 1 à 3
SGL5-1000	5000	1000	150	7	500	50	
SGL5-1500	5000	1500	150	7	500	50	
SGL5-2000	5000	2000	150	7	500	50	
SGL5-2500	5000	2500	150	7	500	50	
SGL5-3000	5000	3000	150	7	500	50	
SGL5-4000	5000	4000	150	7	500	50	

Dimensions en mm