
Decorative asymetric screwed hinge

Pla


CHAEA — Polyamide


- ***Screwed hinge***
- *Materials :*
  hinges glass fibre reinforced polyamide (30%)
  sealed pin : stainless steel 316L
- *Square and symetrical versions also available*



Advantage

- *Aesthetic design*
- *Max opening angle 270°*





Part number	Tensile strength	Shear strength	Screw torque (Nm)
CHAE4060A/PA	2200	2300	4
CHAE4080A/PA	2200	2300	4
CHAE5075A/PA	3600	2500	8
CHAE6090A/PA	5100	4200	8

Dimensions en mm

DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	E	F	G	H	ØS	For screw	Stock*	Price each 1 to 5
CHAE4060A/PA	40	60	5,2	4	5,7	13,5	25	19	5,3	M4	✔	7,94 €
CHAE4080A/PA	40	80	5,2	4	5,7	14,5	25	38	5,3	M4	✔	8,15 €
CHAE5075A/PA	50	75	5,9	5	6,4	16	30	24	6,4	M6	✔	10,09 €
CHAE6090A/PA	60	90	6,5	6	7	18	36	30	6,4	M6	✔	14,14 €

Dimensions in mm