Sta Diabolo shaped stainless steel elasto mount

Female / female mounting

CT-ZYss


- ***Radial elasticity greater than axial elasticity***
- *Cylinder works under both compression and shear*
- *Materials :*
  Core: Stainless steel (A2)
  Cylinder: Rubber
- ***Hardness NK55-60 Shore A***
- *Working temp: -40°C to +70°C*



Uses

- *Dampens sound and vibrations*





DISCOUNTS

Qty	1+	6+	20+	40+	100+
Disc.	List	-10%	-15%	-20%	On request

Part number	ØG	ØD	H	L	Stock*	Price each 1 to 5
CT-ZY4-10-10/SS	M4	10	10	4	✔	3,61 €
CT-ZY8-30-20/SS	M8	30	20	8	✔	8,17 €
CT-ZY8-40-48/SS	M8	40	48	8	✔	16,93 €
CT-ZY10-50-30/SS	M10	50	30	10	-	26,63 €

**Depending on availability - Dimensions in mm*