
Steel spur gear

Module 6.0

Steel 20NCD2



- ***Precision class 9***
- *Pressure angle 20°*
- *Linear speed 300m/min*





Option

- ***Alternative number of teeth, a datasheet is available from www.hpceurope.com in PDF format***

Torque and power indication				
For 50 teeth at 1000 rpm				
	20NCD2 Z10CNF18.09	20NCD2 hardened	brass	fibre
Nm	**441**	2350	120	180
kW	**46**	246	12.60	18.80

DISCOUNTS

Qty	1+	4+	20+
Disc.	List	-5%	On request

Part number	Teeth Z	PCD ØP	Outside ØD	Boss ØM	Bore ØA	Price each 1 to 3 HG	HPG
HG6-12	12	72,00	84,00	50	25	On request	On request
HG6-14	14	84,00	96,00	60	25	83,80 €	
HG6-15	15	90,00	102,00	65	25	89,79 €	
HG6-18	18	108,00	120,00	80	30	107,74 €	
HG6-19	19	114,00	126,00	80	30	113,74 €	
HG6-20	20	120,00	132,00	90	30	119,71 €	
HG6-21	21	126,00	138,00	90	30	On request	
HG6-22	22	132,00	144,00	90	30	On request	
HG6-23	23	138,00	150,00	90	30	137,69 €	
HG6-24	24	144,00	156,00	90	30	On request	
HG6-25	25	150,00	162,00	90	30	149,67 €	
HG6-30	30	180,00	192,00	100	30	214,75 €	
HG6-31	31	186,00	198,00	100	30	On request	
HG6-32	32	192,00	204,00	120	38	On request	
HG6-35	35	210,00	222,00	120	38	309,76 €	
HG6-38	38	228,00	240,00	120	38	On request	
HG6-40	40	240,00	252,00	150	38	354,01 €	
HG6-41	41	246,00	258,00	150	38	On request	
HG6-42	42	252,00	264,00	150	38	On request	
HG6-44	44	264,00	276,00	150	38	On request	
↓	**Gears available up to this size**					↓	
HG6-95	**95**	**570,00**	**582,00**	**Dimensions: contact us**		**On request**	

Dimensions in mm