HTD type timing pulley


Pitch 8mm

Steel or cast iron

Belt width 20mm



- **For use with RPP8 belt**
- Pitch: 8mm
- Material:
  Cast iron or phosphated steel depending on size




Accessories

- Belts **RPP8**
- Belt tension roller **GTC**

Info.

- **Pilot bore dimension is given as a guide only may vary between batches
- To be finished to size by customer
- **We are unable to modify these parts.**



DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-12%	On request

Part number	Material	No. of teeth	PCD Ø	external ØD	flange ØE	ØM	ØDi	F	L	Pilot bore **ØA	Stock*	Price each 1 to 5
22HTD8M-20F	Steel	22	56,02	54,65	60,0	43	-	28	38	12	✔	13,03 €
24HTD8M-20F		24	61,12	59,75	66,0	45	-	28	38	12	✔	14,47 €
26HTD8M-20F		26	66,21	64,85	70,0	48	-	28	38	12	✔	15,45 €
28HTD8M-20F		28	71,30	70,08	75,0	50	-	28	38	15	✔	17,13 €
30HTD8M-20F		30	76,39	75,13	82,5	55	-	28	38	15	✔	19,65 €
32HTD8M-20F		32	81,49	80,16	87,0	60	-	28	38	15	✔	21,69 €
34HTD8M-20F		34	86,58	85,22	91,0	66	-	28	38	15	✔	24,13 €
36HTD8M-20F		36	91,67	90,30	97,0	70	-	28	38	15	✔	26,66 €
38HTD8M-20F		38	96,77	95,39	102,0	75	-	28	38	15	-	29,26 €
40HTD8M-20F		40	101,86	100,49	106,0	75	-	28	38	15	-	31,59 €
44HTD8M-20F		44	112,05	110,67	120,0	75	-	28	38	15	✔	37,63 €
48HTD8M-20F		48	122,23	120,86	128,0	75	-	28	38	15	✔	43,41 €
56HTD8M-20F		56	142,60	141,23	150,0	80	116	28	38	15	✔	55,50 €
64HTD8M-20F		64	162,97	161,60	168,0	80	137	28	38	15	✔	68,16 €
72HTD8M-20F		72	183,35	181,97	192,0	80	158	28	38	15	✔	81,92 €
80HTD8M-20	Cast	80	203,72	202,35	-	90	180	28	38	15	-	77,95 €
90HTD8M-20		90	229,18	227,81	-	90	204	28	38	15	-	88,78 €

*Depending on availability - Dimensions in mm