


## KGS

## Rolled ball screw, class 7

- **Rolled ballscrew**
- **Material:**  
Polished steel, Cf53 or Cf60 induction hardened.
- **Hardness:** 60±2 HRC



### Options

- Ends can be machined to customer requirements
- Cut to length
- Other diameters available (up to 80mm)

### Accessories


- See **GBS-F, GBS-Z, GBM-F, GBM-Z** nuts



GBS nut

KGS screw

Extended range,  
new sizes available



### DISCOUNTS

Qty	1+	2+	6+	11+
Disc.	List	-7%	-13%	On request

Part number	For Movement		Unmachined screw		L (mm)	L max (mm)	Weight/m (kg)	Stock*	Price each
	Ød0 (mm)	screw per turn	Ød1	Ød2					
KGS1605-1000TR7	16	5	15,5	12,9	1000	3000	1,26	✓	85,76 €
KGS2005-1000TR7	20	5	19,5	16,9	1000	6000	1,26	✓	115,05 €
KGS2020-1000TR7	20	20	19,5	16,9	1000	6000	3,04	-	124,98 €
KGS2050-1000TR7	20	50	19,1	16,5	1000	6000	2,07	-	133,18 €
KGS2505-1000TR7	25	5	24,5	21,9	1000	6000	3,33	✓	154,46 €
KGS3205-1000TR7	32	5	31,5	28,9	1000	6000	5,61	✓	216,36 €
KGS3210-1000TR7	32	10	31,5	28,9	1000	6000	5,61	-	217,26 €
KGS3220-1000TR7	32	20	31,4	28,7	1000	6000	5,61	-	224,73 €
KGS3240-1000TR7	32	40	32,6	28,9	1000	6000	5,61	-	229,04 €
KGS4005-1000TR7	40	5	39,5	36,9	1000	6000	9,03	✓	305,37 €
KGS4010-1000TR7	40	10	39,5	34,1	1000	6000	8,33	-	286,99 €
KGS5010-1000TR7	50	10	49,2	44	1000	6000	13,48	-	387,31 €
KGS5020-1000TR7	50	20	49,4	44	1000	6000	13,48	-	431,55 €
KGS6310-1000TR7	63	10	62,2	57	1000	6000	22,04	-	612,27 €

\*Depending on availability - Dimensions in mm