


- Cold rolled (plastic deformation)
- Conforms to ISO 2901 / 2903
- Capable of transmitting large forces
- Good surface finish
- Material: Half-hard steel XC38
- Thread tolerance: 7e





Uses

- Machine tools
- Lathe main screw

Options

- Available in lengths up to 6000mm (for diameters 30mm or greater)



A DISCOUNTS and AVAILABLE LENGTHS

| Qty | 1+ | 10+ | 20+ | 40+ |
|-------|------|-------|-------|------------|
| Disc. | List | -30% | -40% | On request |
| Lngt. | 1000 | 2000 | 3000 | 6000 mm |
| Price | List | x2,12 | x3,18 | On request |

B DISCOUNTS and AVAILABLE LENGTHS


| Qté | 1+ | 5+ | 10+ |
|-------|------|-------|------------------|
| Rem. | List | -5% | On request |
| Lngt. | 1000 | 2000 | 3000 6000 mm |
| Price | Uni. | x2,12 | x3,18 On request |

| Part number | ØD | Pitch P (mm) | d mini. | Weight (kg/m) | Stock* | Price each per metre | |
|-------------|-----|--------------|---------|---------------|--------|----------------------|------------|
| | | | | | | 1 to 9 | 40 to 59** |
| LFM102 | 10 | 2 | 6,89 | 0,46 | ✓ | 7,73 € | 4.64 |
| LFM123 | 12 | 3 | 07,68 | 0,65 | ✓ | 10,97 € | 6.58 |
| LFM143 | 14 | 3 | 09,68 | 0,93 | ✓ | 14,13 € | 8.48 |
| LFM164 | 16 | 4 | 10,47 | 1,15 | ✓ | 17,46 € | 10.48 |
| LFM184 | 18 | 4 | 12,47 | 1,52 | ✓ | 21,53 € | 12.92 |
| LFM204 | 20 | 4 | 14,47 | 1,91 | ✓ | 25,80 € | 15.48 |
| LFM225 | 22 | 5 | 15,29 | 2,30 | ✓ | 30,93 € | 18.56 |
| LFM245 | 24 | 5 | 17,27 | 2,80 | ✓ | 35,50 € | 21.30 |
| LFM285 | 28 | 5 | 21,27 | 3,90 | ✓ | 49,22 € | 29.53 |
| LFM306 | 30 | 6 | 21,56 | 4,33 | ✓ | 53,84 € | 32.30 |
| LFM326 | 32 | 6 | 23,56 | 5,00 | ✓ | 61,57 € | 36.94 |
| LFM366 | 36 | 6 | 27,56 | 6,55 | ✓ | 46,16 € | On request |
| LFM407 | 40 | 7 | 30,38 | 8,00 | ✓ | 58,30 € | On request |
| LFM447 | 44 | 7 | 34,38 | 9,86 | ✓ | 77,09 € | On request |
| LFM508 | 50 | 8 | 39,17 | 12,76 | ✓ | 95,92 € | On request |
| LFM609 | 60 | 9 | 47,98 | 18,65 | - | 137,79 € | On request |
| LFM7010 | 70 | 10 | 56,82 | 25,65 | - | 188,06 € | On request |
| LFM8010 | 80 | 10 | 66,82 | 34,21 | - | 264,14 € | On request |
| LFM9012 | 90 | 12 | 74,44 | 43,00 | - | 402,70 € | On request |
| LFM9516 | 95 | 16 | 73,71 | 45,60 | - | 392,57 € | On request |
| LFM10016 | 100 | 16 | 78,71 | 51,00 | - | 441,94 € | On request |
| LFM12016 | 120 | 16 | 98,71 | 76,00 | - | 645,20 € | On request |

*Depending on availability - Dimensions in mm

** refer to discounts

- Cold rolled (plastic deformation)
- Conforms to ISO 2901 / 2903
- Capable of transmitting large forces
- Good surface finish
- Material: Half-hard steel XC38
- Thread tolerance: 7e





Uses

- Machine tools
- Lathe main screw

Options

- Available in lengths up to 6000mm (for diameters 30mm or greater)



A DISCOUNTS and AVAILABLE LENGTHS

| Qty | 1+ | 10+ | 20+ | 40+ |
|-------|------|-------|-------|------------|
| Disc. | List | -30% | -40% | On request |
| Lngt. | 1000 | 2000 | 3000 | 6000 mm |
| Price | Uni. | x2,12 | x3,18 | On request |

B DISCOUNTS and AVAILABLE LENGTHS

| Qté | 1+ | 5+ | 10+ | |
|-------|------|-------|------------|------------|
| Rem. | List | -5% | On request | |
| Lngt. | 1000 | 2000 | 3000 | 6000 mm |
| Price | Uni. | x2,12 | x3,18 | On request |

| Part number | ØD | Pitch P (mm) | d mini. | Weight (kg/m) | Stock* | Price each per metre | |
|-------------|-----|--------------|---------|---------------|--------|----------------------|------------|
| | | | | | | 1 to 9 | 40 to 59** |
| LFM102/LH | 10 | 2 | 6,89 | 0,46 | ✓ | 9,52 € | 5,71 |
| LFM123/LH | 12 | 3 | 07,68 | 0,65 | ✓ | 13,57 € | 8,14 |
| LFM143/LH | 14 | 3 | 09,68 | 0,93 | ✓ | 18,58 € | 11,15 |
| LFM164/LH | 16 | 4 | 10,47 | 1,15 | ✓ | 21,10 € | 12,66 |
| LFM184/LH | 18 | 4 | 12,47 | 1,52 | ✓ | 25,92 € | 15,55 |
| LFM204/LH | 20 | 4 | 14,47 | 1,91 | ✓ | 29,48 € | 17,69 |
| LFM225/LH | 22 | 5 | 15,29 | 2,30 | ✓ | 36,57 € | 21,94 |
| LFM245/LH | 24 | 5 | 17,27 | 2,80 | ✓ | 39,05 € | 23,43 |
| LFM285/LH | 28 | 5 | 21,27 | 3,90 | ✓ | 57,77 € | 34,66 |
| LFM306/LH | 30 | 6 | 21,56 | 4,33 | ✓ | 60,62 € | 36,37 |
| LFM326/LH | 32 | 6 | 23,56 | 5,00 | ✓ | 70,33 € | 42,20 |
| LFM366/LH | 36 | 6 | 27,56 | 6,55 | - | 52,29 € | On request |
| LFM407/LH | 40 | 7 | 30,38 | 8,00 | - | 71,95 € | On request |
| LFM447/LH | 44 | 7 | 34,38 | 9,86 | - | 102,22 € | On request |
| LFM508/LH | 50 | 8 | 39,17 | 12,76 | - | 117,32 € | On request |
| LFM559/LH | 55 | 9 | 42,98 | 15,40 | - | On request | On request |
| LFM609/LH | 60 | 9 | 47,98 | 18,65 | - | 178,92 € | On request |
| LFM7010/LH | 70 | 10 | 56,82 | 25,65 | - | 243,97 € | On request |
| LFM8010/LH | 80 | 10 | 66,82 | 34,21 | - | 354,53 € | On request |
| LFM9012/LH | 90 | 12 | 74,44 | 43,00 | - | On request | On request |
| LFM9516/LH | 95 | 16 | 73,71 | 45,60 | - | On request | On request |
| LFM10016/LH | 100 | 16 | 78,71 | 51,00 | - | On request | On request |
| LFM12016/LH | 120 | 16 | 98,71 | 76,00 | - | On request | On request |

*Depending on availability - Dimensions in mm

** refer to discounts