
Spur gear coaxial gearbox

Torque up to 40Nm


NT92
NH92

- ***Ratios from 1:1 to 36:1 (other ratios available on request)***
- *Output backlash: N/A*
- *Max. input speed: 3000 rpm*
- *Materials:*
  casing: anodised aluminium
  input & output: unhardened steel
- *Weight: 2 kg*




Options

- *Can be adapted to suit your motor*
- ***Ask for the ratio you require***
- *Also see* **NT91, NH91**
- *keyway conforms to DIN 6885*



NH92



NT92



Output face

OUTPUT TORQUE (In Nm, values given as a guide only)

Ratios		10:1	12:1	15:1	18:1	20:1	27:1	36:1
	3000	15	15	17	17	17	18	18
	2000	18	18	20	20	20	21	21
	1000	21	21	23	23	23	24	24
INPUT	500	24	24	26	26	26	27	27
SPEED	200	27	27	29	29	29	30	30
(rpm)	100	30	30	31	31	32	33	33
	50	32	33	34	34	35	36	36
	20	35	36	38	38	40	40	40

Large choice of reduction ratios ! Up to 36:1

DISCOUNTS

Qty	1+	2+	4+	6+
Disc.	List	-15%	-20%	On request

Part number		Ratios	Max. input speed (rpm)	Max. output speed (rpm)	Efficiency at 1000 rpm	Direction of input/output rotation	Price each NT	Price each NH
NT92-10	NH92-10	10:1	3000	300	84%	Same	899,05 €	On request
NT92-12	NH92-12	12:1	3000	250	84%	Same	899,05 €	
NT92-15	NH92-15	15:1	3000	200	84%	Same	899,05 €	
NT92-18	NH92-18	18:1	3000	166	84%	Same	899,05 €	
NT92-20	NH92-20	20:1	3000	150	84%	Same	899,05 €	
NT92-27	NH92-27	27:1	3000	125	84%	Same	899,05 €	
NT92-36	NH92-36	36:1	3000	83	84%	Same	898,93 €	
NT92-SP	NH92-SP	1:1 - 36:1	**Special ratios from 1:1 to 36:1**				1 022,64 €	

Dimensions in mm