With horizontal flange


PPG
PPH


- ***Mounting flange with screw holes***
- Materials:
  Body: Zamak with black plastic coating
  Pin: Stainless steel i.4305
  Button : PA6 with black matt finish
- Working temp range: -30 /+80 °C




Info

- For the locking version, if the button is pulled and turned through 90°, the pin retained by a notch





Locking version



Without locking version

DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Locking	ØD1	ØD2	B1	B2	B3	B4 (-0,2)	h1	h2
PPG4-16-22	Without	4	12	16,5	22	6	3,3	4	7
PPG5-22-28	Without	5	16	22	28	8	4,3	4,5	9,5
PPG6-27-32	Without	6	18	27,5	32	10	5,4	5	10,5
PPG8-33-34	Without	8	21	33	34	12	5,4	6	12,5
PPH4-19-22	With	4	12	19	22	6	3,3	4	7
PPH5-25-28	With	5	16	25,5	28	8	4,3	4,5	9,5
PPH6-30-32	With	6	18	30,5	32	10	5,4	5	10,5
PPH8-37-34	With	8	21	37,5	34	12	5,4	6	12,5

Part number	K1 (+/-0,05)	K2	K3	K4	L1	L2	Pressure F1 (N)	Pressure F2 (N)	Weight (g)	Price each 1 to 5
PPG4-16-22	14	4	8	4,5	30,5	4	3	12	11	7,44 €
PPG5-22-28	18	5	10	7	40	5	5	24	20	7,98 €
PPG6-27-32	21	5,5	12	10	49	6	5	21	37	9,16 €
PPG8-33-34	23	5,5	12	15,5	59	8	6	22	61	10,29 €
PPH4-19-22	14	4	8	4,5	33	4	3	12	10	7,49 €
PPH5-25-28	18	5	10	10,5	43,5	5	5	24	26	7,98 €
PPH6-30-32	21	5,5	12	13	52	6	5	21	40	9,16 €
PPH8-37-34	23	5,5	12	20	63,5	8	6	22	67	10,37 €

Dimensions in mm