Fixable articulated foot Ø83

Maximum load 20,000N

PR85

- **Levelling foot**
- Non slip base
- Materials:
  Base: Black glass reinforced polyamide (Shore 70)
  Spindle: Zinc plated steel or stainless 304 steel
- Supplied without nut




With non-slip base

Advantages

- Articulated rod allows auto-alignment with the ground
- Sole material ensures flexibility and grip

Info.

- Values given for static, should will be reduced in case of a vibrating load



DISCOUNTS

Qty	1+	20+	50+
Disc.	List	-10%	On request

Part number	ØD	Thread ØF	B	A	A/F	G	H	H1	Static load (N)	Type	Stock*	Price each 1 to 19
Steel spindle												
PR85-12-75	83	M12	75	38	14	27	113	116	15000	H	✔	10,59 €
PR85-12-125	83	M12	125	38	14	27	163	166	15000	H	✔	11,83 €
PR85-16-75	83	M16	75	38	16	27	113	116	20000	H	✔	11,14 €
PR85-16-150	83	M16	150	38	16	27	188	191	20000	H	✔	13,10 €
PR85-16-200	83	M16	200	38	16	27	238	241	20000	H	✔	14,43 €
PR85-20-125	83	M20	125	41	17	27	166	169	20000	M	✔	12,13 €
PR85-20-175	83	M20	175	41	17	27	216	219	20000	M	✔	13,86 €
PR85-20-225	83	M20	225	41	17	27	266	269	20000	M	✔	15,75 €
Stainless steel spindle												
PR85-12-75/SS	83	M12	75	38	14	27	113	116	15000	H	✔	17,99 €
PR85-12-125/SS	83	M12	125	38	14	27	163	166	15000	H	✔	20,70 €
PR85-16-75/SS	83	M16	75	41	13	27	116	119	20000	M	✔	17,99 €
PR85-16-150/SS	83	M16	150	41	13	27	191	194	20000	M	✔	22,05 €
PR85-16-200/SS	83	M16	200	41	13	27	241	244	20000	M	✔	24,79 €
PR85-20-125/SS	83	M20	125	41	17	27	166	169	20000	M	✔	25,21 €
PR85-20-175/SS	83	M20	175	41	17	27	216	219	20000	M	✔	29,70 €
PR85-20-225/SS	83	M20	225	41	17	27	266	269	20000	M	✔	35,90 €

*Depending on availability - Dimensions in mm