Precision stainless shim


PS — For use with ball bearings

- ***Material:***
  stainless steel 301
- Tolerance: S = ±0.015mm
  (For thicknesses greater than 0.25mm)
- Max. temperature: +430°C




Info.

- When ordering, replace ZZ in the part number by the desired thickness (S)
  E.g: **PSx2x3.5x0.8**



Typical application



DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-10%	-15%	-20%	-30%	On request

Part number	S ±0,01	Ød1	Ød2	Suits bearings with Bore Ø	Suits bearings with External Ø		Price each 1 to 5
PS3x4,5x10	0,10	3,30	4,40	3,00	-	✔	3,11 €
PS3x4,5x12	0,12	3,30	4,40	3,00	-	✔	3,11 €
PS4x6x10	0,10	4,30	5,85	4,00	6	-	On request
PS4x6x15	0,15	4,30	5,85	4,00	6	✔	3,11 €
PS5x7x10	0,10	5,30	6,85	5,00	7	-	On request
PS5x7x15	0,15	5,30	6,85	5,00	7	-	3,11 €
PS6x8x12	0,12	6,30	7,85	6,00	8	✔	On request
PS6x8x18	0,18	6,30	7,85	6,00	8	✔	3,11 €
PS8x10x18	0,18	8,30	9,80	8,00	10	-	3,11 €
PS8x10x20	0,20	8,30	9,80	8,00	10	✔	3,11 €
PS10x12x20	0,20	10,30	11,80	10,00	12	-	3,11 €
PS10x12x22	0,22	10,30	11,80	10,00	12	-	3,11 €

Dimensions in mm