Articulated levelling foot, pressed base Ø80


Accepts loads up to 10.000N

PTA80
PTA80ss

- **Articulated foot**
- Up to +/- 10° from vertical
- Materials:
  - **Steel version:**
    Base: Galvanised sheet steel C40
    Shaft: Galvanised steel (nut not supplied)
    Sole: Vulcanised NBR rubber, hardness 80° Shore
  - **Stainless steel version:**
    Base: Stainless steel sheet 304
    Shaft: Stainless steel 304 (nut not supplied)
    Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version, sanded finish





Advantages

- Excellent Price-Quality ratio

DISCOUNTS

Qty	1+	15+	20+	25+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	Thread ØF	B	A	A/F	G	H	Load static (N)	Stock*	Price each 1 to 14
Steel foot										
PTA80-12-100	80	M12	100	35	14	25	135	10000	✔	20,92 €
PTA80-12-150	80	M12	150	35	14	25	185	10000	-	23,24 €
PTA80-16-100	80	M16	100	35	16	25	135	10000	✔	23,08 €
PTA80-16-150	80	M16	150	35	16	25	185	10000	-	25,53 €
PTA80-20-100	80	M20	100	36	20	25	136	10000	-	24,24 €
PTA80-20-150	80	M20	150	36	20	25	186	10000	-	27,21 €
PTA80-20-200	80	M20	200	36	20	25	236	10000	✔	29,72 €
Stainless steel foot										
PTA80-12-100/SS	80	M12	100	35	14	25	135	10000	✔	31,90 €
PTA80-12-150/SS	80	M12	150	35	14	25	185	10000	-	34,27 €
PTA80-16-100/SS	80	M16	100	35	13	25	135	10000	-	34,27 €
PTA80-16-150/SS	80	M16	150	35	13	25	185	10000	✔	36,64 €
PTA80-20-100/SS	80	M20	100	38	17	25	138	10000	-	38,44 €
PTA80-20-150/SS	80	M20	150	38	17	25	188	10000	✔	41,36 €
PTA80-20-200/SS	80	M20	200	38	17	25	238	10000	✔	45,83 €

*Depending on availability - Dimensions in mm