Radial contact ball bearing

Ste € Eco

Q6

Steel

- ***Radial contact ball bearing***
- *Single row of balls*
- *Static and dynamic loads are both radial loads*



Versions

- *Open: no protection*
- ***ZZ**: bearing with 2 shields*
- ***2RS**: bearing with 2 seals*

Info.


- *** Open*
- *2 widths are given in the tables as bearings without seals are thinner*

DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-10%	-15%	-20%	-30%	On request

Part number	Bore ØA	ØD	Width	Max. speed (rpm)	Dynamic load (N)	Static load (N)	Stock* 2RS	Price each 1 to 5 Open	ZZ	2RS
Q693	3	8	3** / 4	60 000	560	179	-	16,92 €	9,44 €	On request
Q624	4	13	5	40 000	1 300	485	✔	2,96 €	3,55 €	3,84 €
Q634	4	16	5	36 000	1 730	670	-	12,08 €	4,55 €	13,88 €
Q685	5	11	3** / 5	45 000	715	281	✔	16,53 €	8,18 €	12,13 €
Q625	5	16	5	36 000	1 730	670	✔	3,55 €	2,96 €	3,55 €
Q686	6	13	3,5** / 5	40 000	1 080	440	✔	12,19 €	12,89 €	6,54 €
Q626	6	19	6	32 000	2 340	885	✔	3,40 €	3,11 €	2,67 €
Q608	8	22	7	34 000	3 300	1 370	✔	2,55 €	4,29 €	2,55 €
Q61800	10	19	5	24 000	1 720	840	✔	3,84 €	4,42 €	4,55 €
Q6000	10	26	8	22 000	4 550	1 970	✔	3,69 €	3,84 €	3,99 €
Q6200	10	30	9	18 000	5 100	2 390	✔	2,67 €	4,42 €	4,42 €
Q6300	10	35	11	17 000	8 100	3 450	✔	8,03 €	5,29 €	5,44 €
Q61801	12	21	5	20 000	1 920	1 040	✔	5,56 €	5,29 €	5,29 €
Q6001	12	28	8	18 000	5 100	2 370	✔	3,84 €	3,99 €	4,10 €
Q6201	12	32	10	17 000	6 800	3 050	✔	4,55 €	4,42 €	4,55 €
Q6301	12	37	12	16 000	9 700	4 200	✔	7,20 €	6,59 €	5,56 €
Q61802	15	24	5	17 000	2 070	1 260	✔	5,56 €	6,00 €	5,88 €
Q6002	15	32	9	15 000	5 600	2 830	✔	4,55 €	4,42 €	4,55 €
Q6202	15	35	11	14 000	7 650	3 750	✔	4,98 €	4,84 €	4,71 €
Q6302	15	42	13	13 000	11 400	5 450	-	7,44 €	6,30 €	6,59 €
Q61803	17	26	5	15 000	2 630	1 570	✔	6,45 €	6,88 €	6,88 €
Q6003	17	35	10	13 000	6 000	3 250	✔	5,14 €	4,84 €	4,84 €
Q6203	17	40	12	12 000	9 550	4 800	✔	7,00 €	5,56 €	5,73 €
Q6303	17	47	14	11 000	13 600	6 650	-	11,81 €	7,77 €	7,89 €

**Depending on availablity - Dimensions in mm*



DISCOUNTS

Qty	1+	6+	20+	40+	60+	100+
Disc.	List	-10%	-15%	-20%	-30%	On request

Part number	Bore ØA	ØD	Width	Max. speed (rpm)	Dynamic load (N)	Static load (N)	Stock* 2RS	Price each 1 to 5 Open	ZZ	2RS
Q61804	20	32	7	13 000	4 000	2 470	✔	7,77 €	8,62 €	7,30 €
Q6004	20	42	12	11 000	9 400	5 000	✔	6,88 €	6,00 €	6,00 €
Q6204	20	47	14	11 000	12 800	6 600	✔	8,62 €	6,59 €	6,74 €
Q6304	20	52	15	10 000	15 900	7 900	✔	12,10 €	8,62 €	8,90 €
Q61805	25	37	7	10 000	4 300	2 950	✔	11,65 €	10,50 €	10,50 €
Q6005	25	47	12	9 500	10 100	5 850	✔	7,00 €	6,59 €	6,74 €
Q6205	25	52	15	9 000	14 000	7 850	✔	9,61 €	7,89 €	8,03 €
Q61806	30	42	7	9 000	4 500	3 450	✔	12,39 €	12,81 €	13,99 €
Q6006	30	55	13	8 000	13 200	8 300	✔	11,81 €	7,77 €	7,89 €
Q6206	30	62	16	7 500	19 500	11 300	✔	15,28 €	10,50 €	10,64 €
Q61807	35	47	7	7 500	4 750	3 900	-	14,98 €	17,76 €	16,17 €
Q6007	35	62	14	6 700	16 000	10 300	-	13,11 €	9,19 €	9,35 €
Q6207	35	72	17	6 300	25 700	15 300	✔	19,93 €	13,53 €	13,83 €
Q61808	40	52	7	6 700	4 900	4 350	-	20,64 €	22,10 €	21,81 €
Q6008	40	68	15	6 000	16 800	11 500	✔	19,64 €	10,64 €	10,79 €
Q6208	40	80	18	5 600	29 100	17 800	✔	25,87 €	16,59 €	17,03 €
Q61809	45	58	7	6 000	5 350	5 250	-	28,49 €	37,16 €	28,20 €
Q6009	45	75	16	5 300	20 900	15 200	-	19,33 €	12,97 €	13,41 €
Q6209	45	85	19	5 300	31 500	20 400	-	29,36 €	19,64 €	19,93 €
Q61810	50	65	7	5 300	6 400	6 200	-	33,71 €	103,20 €	37,47 €
Q6010	50	80	16	4 800	21 800	16 600	-	25,87 €	15,87 €	15,17 €
Q6210	50	90	20	4 800	35 000	23 200	-	48,14 €	21,97 €	22,51 €

*Depending on availablity - Dimensions in mm