Vertical stirrup toggle clamp Ste Sta Stock

SEV

Hook fastening

- ***2 materials to choose from***
- *Materials:*
  SEH *body: zinc plated steel*
  SEH/SS *body: stainless steel 18.9 (303)*
  Handle: Oil-resistant plastic
- *Supplied with anchoring base*




Advantages

- *Distance of hook from toggle clamp easily adjustable*

Uses

- *Designed to secure covers and shutters*



DISCOUNTS

Qty	1+	6+	15+	20+
Disc.	List	-5%	-10%	On request

Size	Traction force F1(N)	Pressure F2(N)	Manual force (N)	Opening angle of handle	Adjustable distance L Min.	L Max.	L1 Min.	L1 Max.	Locking distance L2	L3
SEV-01	1800	2000	100	145°	25	49	1	25	22	76
SEV-02	2700	4000	150	145°	33	60	1	28	34	115
SEV-04	4500	7000	200	145°	41	80	1	40	45	152

Part number Steel	Stainless steel	A	A1	A2	A3	A4	B	B1	B2	B3	D	D1	H	S	Price each 1 to 5 Steel	StS
SEV-0140	SEV-0140SS	26	13	4,5	11	24	36	24	19	16	5,2	4	42	2,5	46,34 €	60,00 €
SEV-0250	SEV-0250SS	35	19	6,0	14	32	48	33	26	21	6,5	6	64	3,0	68,47 €	84,38 €
SEV-0450	SEV-0450SS	51	32	8,0	19	40	64	45	36	28	8,5	8	85	4,0	114,76 €	160,18 €

Dimensions in mm