


# Actuator guide kit




## UGPC

## Short bearing, ball bushes



- Allows the assembly of short stroke actuator guides with 1-4 guide shafts
- Equipped with 2 ball bearings with wiper joints
- Material:
  - Body: anodised aluminium
  - Bearing housing: Plastic
  - Joint: Nitrile rubber
- Working temperature: +5°C to +80°C
- Maximum speed 2 m/s



**Excellent price  
Quality/ratio**



### Load diagrams



Loads given for a system with 2 guide rods



Dynamic or static load

**DISCOUNTS**

Qty	1+	2+	4+
Disc.	List	-5%	On request

Part number	ØC (Ø rod)	ØD	L	E	ØM	Weight (kg)	Price each
UGPC-10A	10	30	59	23	M4	0,10	68,55 €
UGPC-12A	12	35	63	27	M5	0,14	72,32 €
UGPC-16A	16	40	67	32	M5	0,18	82,51 €
UGPC-20A	20	50	75	39	M6	0,31	95,06 €
UGPC-25A	25	55	90	45	M6	0,44	115,67 €

Dimensions in mm

**HPC**

WEB  
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15€/min + prix appel