


Hexagonal headed screw, **DIN 933**

VTH

Chromed steel (Class 8.8)

- Screw conforming to DIN 933
- Full threaded
- Material:
Chromed steel (Class 8.8)
- Mechanical characteristics conform to ISO 898-1
- Supplied by the packet



DISCOUNTS

| | | | |
|-------|------|------|------------|
| Qty | 1+ | 2+ | 4+ |
| Disc. | List | -20% | On request |

| Part number | ØM | Pitch | | K | A/F across flats | Qty per packet | Price each |
|-------------|----|-------|----|------|---------------------|-------------------|------------|
| | | P | L | | | | |
| VTH4-10/B | M4 | 0,70 | 10 | 2,92 | 7,0 | 500 | 9,78 € |
| VTH4-12/B | M4 | 0,70 | 12 | 2,92 | 7,0 | 500 | 10,71 € |
| VTH4-16/B | M4 | 0,70 | 16 | 2,92 | 7,0 | 500 | 12,70 € |
| VTH4-20/B | M4 | 0,70 | 20 | 2,92 | 7,0 | 500 | 14,33 € |
| VTH4-25/B | M4 | 0,70 | 25 | 2,92 | 7,0 | 500 | 16,90 € |
| VTH4-30/B | M4 | 0,70 | 30 | 2,92 | 7,0 | 500 | 19,18 € |
| VTH4-35/B | M4 | 0,70 | 35 | 2,92 | 7,0 | 200 | 11,97 € |
| VTH4-40/B | M4 | 0,70 | 40 | 2,92 | 7,0 | 200 | 13,42 € |
| VTH5-10/B | M5 | 0,80 | 10 | 3,65 | 8,0 | 500 | 9,90 € |
| VTH5-12/B | M5 | 0,80 | 12 | 3,65 | 8,0 | 500 | 10,91 € |
| VTH5-16/B | M5 | 0,80 | 16 | 3,65 | 8,0 | 500 | 12,73 € |
| VTH5-20/B | M5 | 0,80 | 20 | 3,65 | 8,0 | 500 | 14,60 € |
| VTH5-25/B | M5 | 0,80 | 25 | 3,65 | 8,0 | 500 | 16,90 € |
| VTH5-30/B | M5 | 0,80 | 30 | 3,65 | 8,0 | 500 | 19,24 € |
| VTH5-35/B | M5 | 0,80 | 35 | 3,65 | 8,0 | 200 | 8,62 € |
| VTH5-40/B | M5 | 0,80 | 40 | 3,65 | 8,0 | 200 | 9,55 € |
| VTH5-45/B | M5 | 0,80 | 45 | 3,65 | 8,0 | 200 | 11,06 € |
| VTH5-50/B | M5 | 0,80 | 50 | 3,65 | 8,0 | 200 | 12,29 € |

Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

DISCOUNTS

| | | | |
|-------|------|------|------------|
| Qty | 1+ | 2+ | 4+ |
| Disc. | List | -20% | On request |

| Part number | ØM | Pitch | | | A/F | Qty per packet | Price each |
|-------------|-----|-------|-----|------|------|----------------|------------|
| | | P | L | K | | | |
| VTH6-10/B | M6 | 1,00 | 10 | 4,15 | 10,0 | 500 | 14,54 € |
| VTH6-16/B | M6 | 1,00 | 16 | 4,15 | 10,0 | 500 | 15,57 € |
| VTH6-20/B | M6 | 1,00 | 20 | 4,15 | 10,0 | 500 | 17,58 € |
| VTH6-25/B | M6 | 1,00 | 25 | 4,15 | 10,0 | 500 | 20,18 € |
| VTH6-30/B | M6 | 1,00 | 30 | 4,15 | 10,0 | 500 | 21,66 € |
| VTH6-40/B | M6 | 1,00 | 40 | 4,15 | 10,0 | 200 | 10,94 € |
| VTH6-50/B | M6 | 1,00 | 50 | 4,15 | 10,0 | 200 | 13,36 € |
| VTH6-60/B | M6 | 1,00 | 60 | 4,15 | 10,0 | 200 | 15,45 € |
| VTH8-20/B | M8 | 1,25 | 20 | 5,45 | 13,0 | 200 | 13,87 € |
| VTH8-30/B | M8 | 1,25 | 30 | 5,45 | 13,0 | 200 | 16,79 € |
| VTH8-40/B | M8 | 1,25 | 40 | 5,45 | 13,0 | 100 | 9,69 € |
| VTH8-50/B | M8 | 1,25 | 50 | 5,45 | 13,0 | 100 | 12,29 € |
| VTH8-60/B | M8 | 1,25 | 60 | 5,45 | 13,0 | 100 | 14,12 € |
| VTH8-70/B | M8 | 1,25 | 70 | 5,45 | 13,0 | 100 | 16,32 € |
| VTH8-80/B | M8 | 1,25 | 80 | 5,45 | 13,0 | 100 | 18,18 € |
| VTH10-20/B | M10 | 1,50 | 20 | 6,58 | 17,0 | 200 | 23,05 € |
| VTH10-30/B | M10 | 1,50 | 30 | 6,58 | 17,0 | 200 | 28,49 € |
| VTH10-40/B | M10 | 1,50 | 40 | 6,58 | 17,0 | 100 | 16,93 € |
| VTH10-50/B | M10 | 1,50 | 50 | 6,58 | 17,0 | 100 | 19,63 € |
| VTH10-60/B | M10 | 1,50 | 60 | 6,58 | 17,0 | 50 | 11,52 € |
| VTH10-70/B | M10 | 1,50 | 70 | 6,58 | 17,0 | 50 | 13,06 € |
| VTH10-80/B | M10 | 1,50 | 80 | 6,58 | 17,0 | 50 | 14,48 € |
| VTH10-100/B | M10 | 1,50 | 100 | 6,58 | 17,0 | 50 | 17,73 € |
| VTH12-20/B | M12 | 1,75 | 20 | 7,68 | 19,0 | 100 | 17,50 € |
| VTH12-35/B | M12 | 1,75 | 35 | 7,68 | 19,0 | 100 | 23,34 € |
| VTH12-45/B | M12 | 1,75 | 45 | 7,68 | 19,0 | 100 | 27,39 € |
| VTH12-55/B | M12 | 1,75 | 55 | 7,68 | 19,0 | 50 | 15,48 € |
| VTH12-60/B | M12 | 1,75 | 60 | 7,68 | 19,0 | 50 | 16,22 € |
| VTH12-70/B | M12 | 1,75 | 70 | 7,68 | 19,0 | 50 | 19,24 € |
| VTH12-80/B | M12 | 1,75 | 80 | 7,68 | 19,0 | 50 | 21,30 € |
| VTH12-100/B | M12 | 1,75 | 100 | 7,68 | 19,0 | 50 | 25,50 € |

Dimensions in mm