
Brush ring


New

BAD


For shafts from Ø9 to Ø68


- ***Dual purpose brush that seals and cleans***
- *Material:*
  Smooth black PA6 fibres






NEW!







DISCOUNTS

Qty	1+	20+	50+
Disc.	List	-5%	On request

Part number	For shaft ØW	ØD	ØA	ØM	ØT	Fibre Ø	Price each 1 to 19
BAD35-10	9-18	85	35	65	75	0,15	15,91 €
BAD35-20	19-28	85	35	65	75	0,15	15,91 €
BAD75-30	29-38	125	75	105	115	0,20	18,42 €
BAD75-40	39-48	125	75	105	115	0,20	18,42 €
BAD75-50	49-58	125	75	105	115	0,15	18,42 €
BAD75-60	59-68	125	75	105	115	0,15	18,42 €

Dimensions in mm

Our other products



Spacer for tube carrier, Fixing accessory Ø10 to Ø14




Sliding lock adjustment system, Sliding lock for square profile



Deep groove ball bearing, Stainless steel



Worm and wheel gear reducer, from 2.20 to 4.10 Nm



Worm and wheel set, Machined plastic (delrin)



Eccentric cam follower, Eccentric



Tools Hygienic Usit® and Hygienic Design®, Protective inserts for ...




Extension spring in metre length steel, by the metre



AT type timing pulley, Economy range - AT10 aluminium



Cylindrical bronze nut, Bronze - 2 threads



Flat Guide, Flat guide for conical profile



Shaft for linear guides, Hardened ground stainless steel

Complementary products



Sealing brush strip, 1m length



Sealing brush strip, 1m length