

Angular miter gear 45°




Module 1,5 to 3

Steel

- Shaft angle 45°
- Ratio 1/1
- Gear teeth Gleason
- Precision grade JIS B 1704: 1978 grade 3
- Material:
Steel S45C black oxide coating

Info

- Sold per pair



DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-5%	On request

Part number	Module	Z teeth	ØP PCD	ØD outside	ØB	ØA	E	F	G	H	L	J	K	Mass (kg)	Price each
CCA45-1.5-20/20	1,5	20	30	32,77	25	8	45	19,33	9,36	7,75	18	11	17,00	0,067	
CCA45-2-20/20	2,0	20	40	43,69	30	10	60	26,08	12,48	9,65	24	15	20,92	0,150	
CCA45-2.5-20/20	2,5	20	50	54,62	40	12	75	31,92	15,60	12,58	30	18	30,07	0,310	
CCA45-3-20/20	3,0	20	60	65,54	50	14	90	38,66	18,72	15,51	36	22	34,00	0,550	

Dimensions in mm

Sept 2026

HPC

www.hpceurope.com

Tel. +33(0)4 37 496 496

Angular miter gear 60°




Steel

Module
1,5 to 3

- Shaft angle 60°
- Ratio 1/1
- Gear teeth Gleason
- Precision grade JIS B 1704: 1978 grade 3
- Material:
Steel S45C black oxide coating

Info

- Sold per pair



DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-5%	On request

Part number	Module	Z teeth	ØP PCD	ØD outside	ØB	ØA	E	F	G	H	L	J	K	Mass (kg)	Price each
CCA60-1.5-20/20	1,5	20	30	32,59	25	8	40	22,30	14,77	12,58	21	9	18,18	0,077	
CCA60-2-20/20	2,0	20	40	43,46	30	12	50	26,39	16,36	13,05	24	12	21,93	0,150	
CCA60-2.5-20/20	2,5	20	50	54,33	40	14	60	30,49	17,94	13,82	28	15	29,15	0,270	
CCA60-3-20/20	3,0	20	60	65,19	50	16	70	34,59	19,54	15,16	32	18	36,36	0,470	

Dimensions in mm

Angular miter gear 120°

Module 1,5 to 3

Steel


- Shaft angle 120°
- Ratio 1/1
- Gear teeth Gleason
- Precision grade JIS B 1704: 1978 grade 3
- Material:
Steel S45C black oxide coating

Info


- Sold per pair

Shaft angle
120°

NEW !



Shaft angle 120°



DISCOUNTS

Qty	1+	2+	5+
Disc.	List	-5%	On request

Part number	Module	Z teeth	ØP PCD	ØD outside	ØB	ØA	E	F	G	H	L	J	K	Mass (kg)	Price each
CCA120-1.5-20/20	1,5	20	30	31,50	26	8	26	20,69	18,64	13,88	18	5,0	19,22	0,073	
CCA120-2-20/20	2,0	20	40	42,00	34	12	34	26,86	24,18	17,26	24	6,5	26,78	0,160	
CCA120-2.5-20/20	2,5	20	50	52,50	42	14	42	33,22	29,73	20,64	29	8,5	32,03	0,310	
CCA120-3-20/20	3,0	20	60	63,00	50	16	50	39,39	35,28	24,02	35	10,0	39,59	0,530	

Dimensions in mm

Sept 2026

HPC

www.hpceurope.com

Tel. +33(0)4 37 496 496

Our other products



VQTplqn
Quarter-turn clamp
lock - Clamping plate,
Flush mounting



PSG1
Spur gear - precision
range, Pre-hardened
Steel 35NCD6



PRF_PIV
Internal hinge pin for
aluminium profile,
Internal hinge pin



RCX-6
Spherical tilt washer -
DIN6319, concave



GET-AL
Jaw coupling,
economy range,
Aluminium



PPF
Indexing plunger with
flange, with drilled
flange



ACL
Joints for aluminium
profile, Variable angle
hinge



DILC
Indexing plunger with
cam, with cam



OP7
Mechanical digital
position indicator, 5
numbers



M1
Worm, Non hardened
steel



OPFL_OPPM
Numerical counter
accessories, Locking
clamp



ACLEPP
Right angled bracket
for aluminium profile,
4 holes

Complementary products