Spur gear for use in food industry

Module 0,5


Moulded blue PA6 Nylon

- ***Moulded gear for use in food applications***
- *Pressure angle:20°*
- *Material:*
  Blue glass-fibre reinforced Polyamide



Info

- **Pre-bore after de-moulding, must be machined before installation.*
- *Alternative numbers of teeth (up to 150) possible but minimum quantity applies.*
- ***We are unable to modify these products***



DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc.	Net	-10%	-15%	-25%	On request

Part N°	Z	ØP PCD	ØD External	ØM Hub	ØA* Pre-bore	Transmissible torque (Nm)	Price each. 1 to 9
CLG0.5-24/ALI	24	12,0	13,0	10	-	0,6	3,74 €
CLG0.5-25/ALI	25	12,5	13,5	10	-	0,6	3,77 €
CLG0.5-30/ALI	30	15,0	16,0	10	-	0,8	3,80 €
CLG0.5-32/ALI	32	16,0	17,0	10	-	0,8	3,80 €
CLG0.5-36/ALI	36	18,0	19,0	10	-	0,9	3,89 €
CLG0.5-40/ALI	40	20,0	21,0	10	-	1,0	3,89 €
CLG0.5-45/ALI	45	22,5	23,5	10	-	1,2	4,07 €
CLG0.5-48/ALI	48	24,0	25,0	10	-	1,2	4,32 €
CLG0.5-50/ALI	50	25,0	26,0	10	-	1,3	5,05 €
CLG0.5-55/ALI	55	27,5	28,5	20	-	1,4	5,67 €
CLG0.5-60/ALI	60	30,0	31,0	20	4	1,6	7,54 €

All dimensions in mm

Our other products



SRG

Adjustable latch clamp with strike plate, Stroke from 78mm to 90mm



CLG2

Moulded plastic spur gear, Moulded plastic (nylon)



DTR

Chain idler sprocket, Chain idler sprocket - Steel



DOMI120

Domino 120 adjustable slide, Slide DOMILINE 120



RHT

High Temperature wheel, up to 200kg



OP6

Mechanical digital position indicator, 5 numbers



AZY

Cylindrical elasto mount, Steel



PRF-SCREEN-4

Screen support, Support with 4 axes of rotation




RLXAC8

Free roller, Steel



RDERSS

Stainless steel manual rigging screw,



GPBSS

Threaded spherical knob, Stainless steel



TMR

Rigid manual tensioner, Adjustable

Complementary products