


- For locking on part to another
- Stress spread uniformly across width
- Absorbs shocks and vibrations
- For information on shear strength, please see technical information
- Material:
Stainless steel A1



Info.

- Sold by the packet



DISCOUNTS

N° packets	1+	5+	10+	21+
Discount	List	-10%	-20%	On request

Part number	ØD expanded			L	ØB	Chamfer C	Hole Ø		Qty. per packet	Stock*	Price per packet
	Nom. Ø	Min. Ø	Max. Ø				Min.	Max.			
SRP1.5-6/B	1,5	1,70	1,80	6	1,40	0,50	1,50	1,60	100	-	10,42 €
SRP1.5-8/B	1,5	1,70	1,80	8	1,40	0,50	1,50	1,60	100	✓	11,12 €
SRP1.5-10/B	1,5	1,70	1,80	10	1,40	0,50	1,50	1,60	100	✓	11,34 €
SRP1.5-14/B	1,5	1,70	1,80	14	1,40	0,50	1,50	1,60	100	✓	12,09 €
SRP1.5-20/B	1,5	1,70	1,80	20	1,40	0,50	1,50	1,60	100	✓	14,41 €
SRP2-5/B	2,0	2,30	2,40	5	1,90	0,70	2,00	2,10	100	✓	11,66 €
SRP2-8/B	2,0	2,30	2,40	8	1,90	0,70	2,00	2,10	100	✓	10,42 €
SRP2-10/B	2,0	2,30	2,40	10	1,90	0,70	2,00	2,10	100	✓	12,09 €
SRP2-12/B	2,0	2,30	2,40	12	1,90	0,70	2,00	2,10	100	✓	11,34 €
SRP2-14/B	2,0	2,30	2,40	14	1,90	0,70	2,00	2,10	100	✓	12,89 €
SRP2-16/B	2,0	2,30	2,40	16	1,90	0,70	2,00	2,10	100	✓	13,67 €
SRP2-18/B	2,0	2,30	2,40	18	1,90	0,70	2,00	2,10	100	✓	14,02 €
SRP2-20/B	2,0	2,30	2,40	20	1,90	0,70	2,00	2,10	100	✓	14,41 €
SRP2-24/B	2,0	2,30	2,40	24	1,90	0,70	2,00	2,10	100	✓	16,75 €
SRP2-30/B	2,0	2,30	2,40	30	1,90	0,70	2,00	2,10	100	✓	19,81 €

*Depending on availability - Dimensions in mm

DISCOUNTS

N° packets	1+	5+	10+	21+
Discount	List	-10%	-20%	On request

Part number	ØD expanded				Chamfer			Hole Ø		Qty. per packet	Stock*	Price per packet
	Nom. Ø	Min. Ø	Max. Ø	L	ØB	C	Min.	Max.				
SRP2.5-8/B	2,5	2,80	2,90	8	2,40	0,70	2,50	2,60	100	-	12,80 €	
SRP2.5-10/B	2,5	2,80	2,90	10	2,40	0,70	2,50	2,60	100	✓	13,29 €	
SRP2.5-16/B	2,5	2,80	2,90	16	2,40	0,70	2,50	2,60	100	✓	14,41 €	
SRP2.5-20/B	2,5	2,80	2,78	20	2,40	0,70	2,49	2,60	100	-	15,46 €	
SRP2.5-30/B	2,5	2,80	2,78	30	2,40	0,70	2,49	2,60	100	✓	17,63 €	
SRP3-8/B	3,0	3,30	3,30	8	2,90	0,90	3,00	3,10	100	-	12,09 €	
SRP3-10/B	3,0	3,30	3,30	10	2,90	0,90	3,00	3,10	100	✓	13,67 €	
SRP3-12/B	3,0	3,30	3,30	12	2,90	0,90	3,00	3,10	100	✓	12,89 €	
SRP3-14/B	3,0	3,30	3,30	14	2,90	0,90	3,00	3,10	100	-	15,03 €	
SRP3-16/B	3,0	3,30	3,30	16	2,90	0,90	3,00	3,10	100	✓	13,88 €	
SRP3-18/B	3,0	3,30	3,30	18	2,90	0,90	3,00	3,10	100	✓	16,01 €	
SRP3-20/B	3,0	3,30	3,30	20	2,90	0,90	3,00	3,10	100	✓	16,56 €	
SRP3-24/B	3,0	3,30	3,30	24	2,90	0,90	3,00	3,10	100	✓	19,08 €	
SRP3-30/B	3,0	3,30	3,30	30	2,90	0,90	3,00	3,10	100	✓	19,08 €	
SRP3-40/B	3,0	3,30	3,30	40	2,90	0,90	3,00	3,10	100	✓	23,68 €	
SRP4-10/B	4,0	4,40	4,60	10	3,90	1,10	4,00	4,12	100	-	18,15 €	
SRP4-12/B	4,0	4,40	4,60	12	3,90	1,10	4,00	4,12	100	✓	19,08 €	
SRP4-16/B	4,0	4,40	4,60	16	3,90	1,10	4,00	4,12	100	✓	19,08 €	
SRP4-20/B	4,0	4,40	4,60	20	3,90	1,10	4,00	4,12	100	✓	20,58 €	
SRP4-24/B	4,0	4,40	4,60	24	3,90	1,10	4,00	4,12	100	✓	22,15 €	
SRP4-26/B	4,0	4,40	4,60	26	3,90	1,10	4,00	4,12	100	-	23,68 €	
SRP4-28/B	4,0	4,40	4,60	28	3,90	1,10	4,00	4,12	100	-	26,72 €	
SRP4-30/B	4,0	4,40	4,60	30	3,90	1,10	4,00	4,12	100	✓	27,50 €	
SRP4-35/B	4,0	4,40	4,60	35	3,90	1,10	4,00	4,12	50	-	On request	
SRP4-40/B	4,0	4,40	4,60	40	3,90	1,10	4,00	4,12	50	✓	17,39 €	
SRP4-45/B	4,0	4,40	4,60	45	3,90	1,10	4,00	4,12	50	-	18,57 €	
SRP4-50/B	4,0	4,40	4,60	50	3,90	1,10	4,00	4,12	50	-	20,13 €	
SRP5-10/B	5,0	5,40	5,60	10	4,85	1,30	5,00	5,12	50	-	11,20 €	
SRP5-16/B	5,0	5,40	5,60	16	4,85	1,30	5,00	5,12	50	✓	12,42 €	
SRP5-20/B	5,0	5,40	5,60	20	4,85	1,30	5,00	5,12	50	✓	15,87 €	
SRP5-24/B	5,0	5,40	5,60	24	4,85	1,30	5,00	5,12	50	✓	16,12 €	
SRP5-30/B	5,0	5,40	5,60	30	4,85	1,30	5,00	5,12	50	-	14,71 €	
SRP5-35/B	5,0	5,40	5,45	35	4,85	1,30	5,00	5,12	50	-	On request	
SRP5-40/B	5,0	5,40	5,45	40	4,85	1,30	5,00	5,12	50	✓	21,58 €	
SRP5-50/B	5,0	5,40	5,45	50	4,85	1,30	5,00	5,12	50	✓	24,75 €	
SRP6-20/B	6,0	6,40	6,70	20	5,85	1,50	6,00	6,12	50	✓	18,48 €	
SRP6-30/B	6,0	6,40	6,70	30	5,85	1,50	6,00	6,12	50	✓	23,55 €	
SRP6-40/B	6,0	6,40	6,70	40	5,85	1,50	6,00	6,12	50	✓	28,96 €	
SRP6-50/B	6,0	6,40	6,70	50	5,85	1,50	6,00	6,12	50	✓	33,99 €	
SRP8-30/B	8,0	8,50	8,80	30	7,80	2,00	8,00	8,15	25	-	16,90 €	
SRP8-40/B	8,0	8,50	8,80	40	7,80	2,00	8,00	8,15	10	✓	10,07 €	
SRP8-50/B	8,0	8,50	8,80	50	7,80	2,00	8,00	8,15	10	✓	11,62 €	
SRP10-30/B	10,0	10,50	10,80	30	9,75	2,50	10,00	10,15	10	-	14,88 €	
SRP10-40/B	10,0	10,50	10,80	40	9,75	2,50	10,00	10,15	10	-	On request	
SRP10-50/B	10,0	10,50	10,80	50	9,75	2,50	10,00	10,15	10	-	On request	

*Depending on availability - Dimensions in mm

- For locking one part to another
- Relative positioning
- 15° chamfer
- Material: hardened steel 100 Cr6 rectified 58-60HRC
- Conforms to DIN 6325 (ISO 8734)
- For information on shear strength, please see technical information
- Sold by the packet



Info.

- Exist in box (tome 1 p.636)


DISCOUNTS

Qty	1+	5+	10+	20+
Disc.	List	-20%	-30%	On request

Part number	ØD m6	Length L	Qty per packet	Stock*	Price per packet
DH1-5/B	1.0	5	100	✓	18,35 €
DH1-6/B	1.0	6	100	✓	17,96 €
DH1.5-5/B	1.5	5	100	✓	7,69 €
DH1.5-6/B	1.5	6	100	✓	7,71 €
DH1.5-8/B	1.5	8	100	✓	8,01 €
DH1.5-10/B	1.5	10	100	✓	8,35 €
DH2-6/B	2.0	6	100	✓	14,58 €
DH2-8/B	2.0	8	100	✓	8,39 €
DH2-10/B	2.0	10	100	✓	10,28 €
DH2-12/B	2.0	12	100	✓	16,97 €
DH2-14/B	2.0	14	100	✓	6,78 €
DH2-16/B	2.0	16	100	✓	9,79 €
DH2-30/B	2.0	30	100	✓	18,85 €
DH2.5-10/B	2.5	10	100	✓	6,89 €
DH2.5-12/B	2.5	12	100	✓	7,75 €
DH3-6/B	3.0	6	100	✓	5,69 €
DH3-8/B	3.0	8	100	✓	13,93 €
DH3-10/B	3.0	10	100	✓	21,42 €
DH3-12/B	3.0	12	100	✓	15,95 €
DH3-16/B	3.0	16	100	✓	7,30 €
DH3-18/B	3.0	18	100	✓	7,84 €
DH3-20/B	3.0	20	100	✓	13,10 €
DH3-24/B	3.0	24	100	✓	9,38 €
DH3-30/B	3.0	30	100	✓	11,30 €
DH3-32/B	3.0	32	100	✓	12,08 €
DH3-40/B	3.0	40	100	✓	14,81 €
DH4-6/B	4.0	6	100	✓	8,46 €
DH4-8/B	4.0	8	100	✓	6,88 €

Part number	ØD m6	Length L	Qty per packet	Stock*	Price per packet
DH4-10/B	4.0	10	100	✓	9,86 €
DH4-12/B	4.0	12	100	✓	7,70 €
DH4-14/B	4.0	14	100	✓	12,42 €
DH4-16/B	4.0	16	100	✓	12,56 €
DH4-18/B	4.0	18	100	✓	9,77 €
DH4-20/B	4.0	20	100	✓	14,31 €
DH4-28/B	4.0	28	100	✓	15,00 €
DH4-30/B	4.0	30	100	✓	14,70 €
DH4-32/B	4.0	32	100	-	15,40 €
DH4-40/B	4.0	40	100	✓	21,97 €
DH4-50/B	4.0	50	100	✓	25,72 €
DH4-60/B	4.0	60	100	✓	30,06 €
DH5-8/B	5.0	8	25	✓	5,21 €
DH5-10/B	5.0	10	25	✓	5,23 €
DH5-12/B	5.0	12	25	✓	5,31 €
DH5-14/B	5.0	14	25	✓	5,45 €
DH5-16/B	5.0	16	25	✓	5,61 €
DH5-20/B	5.0	20	25	✓	5,80 €
DH5-24/B	5.0	24	25	✓	6,10 €
DH5-26/B	5.0	26	25	✓	6,27 €
DH5-28/B	5.0	28	25	-	6,36 €
DH5-30/B	5.0	30	25	✓	6,46 €
DH5-36/B	5.0	36	25	✓	6,94 €
DH5-40/B	5.0	40	25	✓	7,15 €
DH5-50/B	5.0	50	25	✓	9,23 €
DH6-10/B	6.0	10	25	✓	5,69 €
DH6-12/B	6.0	12	25	✓	7,85 €
DH6-14/B	6.0	14	25	✓	8,23 €

*Depending on availability - Dimensions in mm



DISCOUNTS

Qty	1+	5+	10+	20+
Disc.	List	-20%	-30%	On request

Part number	ØD m6	Length L	Qty per packet	Stock*	Price per packet	Part number	ØD m6	Length L	Qty per packet	Stock*	Price per packet
DH6-16/B	6,0	16	25	✓	5,90 €	DH8-40/B	8,0	40	25	✓	10,93 €
DH6-18/B	6,0	18	25	✓	6,05 €	DH8-50/B	8,0	50	25	✓	12,44 €
DH6-20/B	6,0	20	25	✓	7,05 €	DH8-80/B	8,0	80	25	✓	25,76 €
DH6-24/B	6,0	24	25	✓	6,46 €	DH10-20/B	10,0	20	25	✓	9,85 €
DH6-26/B	6,0	26	25	✓	6,74 €	DH10-26/B	10,0	26	25	✓	11,23 €
DH6-28/B	6,0	28	25	✓	6,88 €	DH10-30/B	10,0	30	25	✓	13,34 €
DH6-30/B	6,0	30	25	✓	7,04 €	DH10-36/B	10,0	36	25	-	15,44 €
DH6-36/B	6,0	36	25	-	7,50 €	DH10-40/B	10,0	40	25	-	14,21 €
DH6-40/B	6,0	40	25	✓	7,83 €	DH10-45/B	10,0	45	25	✓	19,35 €
DH6-50/B	6,0	50	25	✓	8,99 €	DH10-50/B	10,0	50	25	✓	16,11 €
DH6-60/B	6,0	60	25	✓	10,31 €	DH10-60/B	10,0	60	25	✓	25,09 €
DH8-16/B	8,0	16	25	✓	11,11 €	DH10-80/B	10,0	80	25	-	25,31 €
DH8-18/B	8,0	18	25	✓	8,40 €	DH12-20/B	12,0	20	25	-	14,99 €
DH8-20/B	8,0	20	25	✓	8,45 €	DH12-30/B	12,0	30	25	✓	41,64 €
DH8-24/B	8,0	24	25	✓	8,94 €	DH12-40/B	12,0	40	25	✓	23,47 €
DH8-30/B	8,0	30	25	✓	9,71 €						

*Depending on availability - Dimensions in mm

- For locking one part to another
- Relative positioning
- Material:
stainless steel A1

Info.

- Sold by the packet



DISCOUNTS

No. pack	1+	5+	10+	20+
Disc.	List -20%	-30%	On request	

Part number	ØD m6	C	Length L	Qty per packet	Stock*	Price per packet
DP0.8-10/B	0,8	0,12	10	100	✓	14,75 €
DP1.0-4/B	1,0	0,15	4	100	✓	5,91 €
DP1.0-5/B	1,0	0,15	5	100	✓	6,21 €
DP1.0-6/B	1,0	0,15	6	100	✓	6,37 €
DP1.0-8/B	1,0	0,15	8	100	✓	7,20 €
DP1.0-10/B	1,0	0,15	10	100	✓	6,74 €
DP1.0-12/B	1,0	0,15	12	100	✓	6,89 €
DP1.5-5/B	1,5	0,23	5	100	✓	9,48 €
DP1.5-6/B	1,5	0,23	6	100	✓	6,89 €
DP1.5-8/B	1,5	0,23	8	100	✓	9,93 €
DP1.5-10/B	1,5	0,23	10	100	✓	7,11 €
DP1.5-12/B	1,5	0,23	12	100	✓	8,77 €
DP1.5-14/B	1,5	0,23	14	100	✓	11,08 €
DP1.5-16/B	1,5	0,23	16	100	✓	10,31 €
DP2.0-4/B	2,0	0,30	4	100	✓	6,89 €
DP2.0-5/B	2,0	0,30	5	100	✓	6,94 €
DP2.0-6/B	2,0	0,30	6	100	✓	11,53 €
DP2.0-8/B	2,0	0,30	8	100	✓	7,45 €
DP2.0-10/B	2,0	0,30	10	100	✓	9,96 €
DP2.0-12/B	2,0	0,30	12	100	✓	10,18 €
DP2.0-14/B	2,0	0,30	14	100	✓	8,57 €
DP2.0-16/B	2,0	0,30	16	100	✓	12,53 €
DP2.0-18/B	2,0	0,30	18	100	✓	12,81 €
DP2.0-20/B	2,0	0,30	20	100	✓	10,57 €
DP2.5-6/B	2,5	0,40	6	100	✓	8,33 €
DP2.5-8/B	2,5	0,40	8	100	✓	8,94 €
DP2.5-10/B	2,5	0,40	10	100	✓	11,78 €
DP2.5-12/B	2,5	0,40	12	100	✓	12,11 €
DP2.5-16/B	2,5	0,40	16	100	✓	11,33 €
DP2.5-20/B	2,5	0,40	20	100	-	On request
DP2.5-24/B	2,5	0,40	24	100	✓	14,31 €
DP3.0-5/B	3,0	0,45	5	100	✓	9,38 €
DP3.0-6/B	3,0	0,45	6	100	✓	15,60 €
DP3.0-8/B	3,0	0,45	8	100	✓	11,56 €
DP3.0-10/B	3,0	0,45	10	100	✓	13,39 €
DP3.0-12/B	3,0	0,45	12	100	✓	13,10 €

*Depending on availability - Dimensions in mm

Part number	ØD m6	C	Length L	Qty per packet	Stock*	Price per packet
DP3.0-14/B	3,0	0,45	14	100	✓	13,74 €
DP3.0-16/B	3,0	0,45	16	100	✓	14,16 €
DP3.0-18/B	3,0	0,45	18	100	✓	12,95 €
DP3.0-20/B	3,0	0,45	20	100	✓	13,62 €
DP3.0-24/B	3,0	0,45	24	100	✓	14,74 €
DP3.0-30/B	3,0	0,45	30	100	✓	22,00 €
DP4.0-6/B	4,0	0,60	6	100	✓	12,64 €
DP4.0-8/B	4,0	0,60	8	100	✓	13,53 €
DP4.0-10/B	4,0	0,60	10	100	✓	18,99 €
DP4.0-12/B	4,0	0,60	12	100	✓	14,53 €
DP4.0-14/B	4,0	0,60	14	100	✓	20,49 €
DP4.0-16/B	4,0	0,60	16	100	✓	27,77 €
DP4.0-18/B	4,0	0,60	18	100	✓	28,44 €
DP4.0-20/B	4,0	0,60	20	100	✓	22,36 €
DP4.0-24/B	4,0	0,60	24	100	✓	33,35 €
DP4.0-40/B	4,0	0,60	40	100	✓	34,55 €
DP4.0-50/B	4,0	0,60	50	100	✓	49,68 €
DP5.0-10/B	5,0	0,75	10	25	✓	5,45 €
DP5.0-12/B	5,0	0,75	12	25	✓	5,91 €
DP5.0-14/B	5,0	0,75	14	25	✓	6,50 €
DP5.0-16/B	5,0	0,75	16	25	✓	6,89 €
DP5.0-20/B	5,0	0,75	20	25	✓	11,56 €
DP5.0-24/B	5,0	0,75	24	25	✓	9,10 €
DP5.0-30/B	5,0	0,75	30	25	✓	10,10 €
DP5.0-40/B	5,0	0,75	40	25	✓	12,64 €
DP5.0-50/B	5,0	0,75	50	25	✓	16,29 €
DP6.0-10/B	6,0	0,90	10	25	✓	7,38 €
DP6.0-12/B	6,0	0,90	12	25	✓	7,96 €
DP6.0-14/B	6,0	0,90	14	25	✓	10,78 €
DP6.0-16/B	6,0	0,90	16	25	✓	10,78 €
DP6.0-20/B	6,0	0,90	20	25	✓	10,79 €
DP6.0-24/B	6,0	0,90	24	25	✓	11,72 €
DP6.0-28/B	6,0	0,90	28	25	✓	14,30 €
DP6.0-30/B	6,0	0,90	30	25	✓	13,92 €
DP6.0-40/B	6,0	0,90	40	25	✓	21,81 €
DP6.0-45/B	6,0	0,90	45	25	✓	22,19 €
DP8.0-14/B	8,0	1,20	14	25	✓	14,93 €
DP8.0-16/B	8,0	1,20	16	25	✓	16,57 €
DP8.0-20/B	8,0	1,20	20	25	✓	19,62 €
DP8.0-24/B	8,0	1,20	24	25	✓	19,42 €
DP8.0-30/B	8,0	1,20	30	25	✓	22,19 €
DP8.0-40/B	8,0	1,20	40	25	✓	35,32 €
DP8.0-50/B	8,0	1,20	50	25	✓	31,91 €
DP10.0-20/B	10,0	1,50	20	25	✓	74,02 €
DP10.0-40/B	10,0	1,50	40	25	✓	40,24 €
DP10.0-50/B	10,0	1,50	50	25	-	48,52 €

*Depending on availability - Dimensions in mm


Extractable dowel pin **DIN 7979D** **Ste** **DIN** **Stock**

DHX Hardened steel

- Easy extraction for holes where access is difficult or restricted
- External diameter tolerance: m6
- Material: hardened steel (DIN 7979D)
- Sold by the packet

Info.

- Ground flat along length allows air to escape during insertion/removal
- Exist in box (tome 1) p.637



DISCOUNTS

Qty	1+	3+	5+	10+
Disc.	List	-20%	-30%	On request

Part number	ØD	Thread	Length L	Qty per packet	Price per packet
DHX4-10/B	4	M2	10	10	✓ 38,72 €
DHX4-12/B	4	M2	12	10	✓ 38,88 €
DHX4-14/B	4	M2	14	10	✓ 39,00 €
DHX4-16/B	4	M2	16	10	✓ 39,16 €
DHX4-20/B	4	M2	20	10	✓ 39,56 €
DHX5-10/B	5	M3	10	10	✓ 22,19 €
DHX5-12/B	5	M3	12	10	✓ 22,31 €
DHX5-16/B	5	M3	16	10	✓ 22,44 €
DHX5-20/B	5	M3	20	10	✓ 22,93 €
DHX5-24/B	5	M3	24	10	✓ 23,30 €
DHX5-30/B	5	M3	30	10	✓ 24,39 €
DHX6-12/B	6	M4	12	10	✓ 21,52 €
DHX6-16/B	6	M4	16	10	✓ 19,29 €
DHX6-20/B	6	M4	20	10	✓ 18,07 €
DHX6-24/B	6	M4	24	10	✓ 18,15 €
DHX6-30/B	6	M4	30	10	✓ 18,37 €
DHX6-40/B	6	M4	40	10	✓ 18,85 €
DHX6-60/B	6	M4	60	10	✓ 21,78 €

Part number	ØD	Thread	Length L	Qty per packet	Price per packet
DHX8-16/B	8	M5	16	10	- 22,23 €
DHX8-20/B	8	M5	20	10	✓ 18,92 €
DHX8-24/B	8	M5	24	10	✓ 19,11 €
DHX8-28/B	8	M5	28	10	- 19,24 €
DHX8-30/B	8	M5	30	10	- 19,82 €
DHX8-40/B	8	M5	40	10	✓ 20,54 €
DHX8-50/B	8	M5	50	10	✓ 21,52 €
DHX10-20/B	10	M6	20	10	- 24,22 €
DHX10-24/B	10	M6	24	10	- 24,85 €
DHX10-30/B	10	M6	30	10	✓ 21,40 €
DHX10-40/B	10	M6	40	10	- 22,36 €
DHX10-45/B	10	M6	45	10	- 22,97 €
DHX10-50/B	10	M6	50	10	- 23,64 €
DHX10-60/B	10	M6	60	10	- 24,85 €
DHX12-40/B	12	M6	40	10	✓ 25,50 €
DHX12-60/B	12	M6	60	10	✓ 70,39 €
DHX12-90/B	12	M6	90	10	- 47,06 €
DHX12-100/B	12	M6	100	10	- 44,02 €

*Depending on availability - Dimensions in mm

Technical information

Minimum double shear resistance (kN) according to ISO 8749

EP range - nickel stainless steel A1

Diameter Ø	0,8	1,0	1,2	1,5	2,0	2,5	3,0	3,5	4,0	5,0	6,0	8,0	10,0	12,0
Standard series														
ISO 8750	0,30	0,45	0,65	1,05	1,9	2,9	4,2	5,7	7,6	11,5	16,8	30	48	67

SRP range - stainless steel A1

Diameter Ø	1,5	2,0	2,5	3,0	4,0	5,0	6,0	8,0	10,0
Standard series									
ISO 8752	0,98	1,81	2,84	4,07	7,25	10,75	16,17	26,46	42,14

DH range - hardened steel

Diameter Ø	1,0	1,5	2,0	2,5	3,0	4,0	5,0	6,0	8,0	10,0	12,0	16,0	20,0
Standard series													
DIN 6325	1,5	3,4	5,5	8,0	13,0	22,0	31,0	53,0	88,0	132,0	210,0	350,0	485,0

DP range - stainless steel A1

Diameter Ø	1,0	1,5	2,0	2,5	3,0	4,0	5,0	6,0	8,0	10,0	12,0
Standard series											
ISO 2338	0,7	1,7	2,9	4,4	6,6	11,7	18,1	26,0	47,0	64,1	92,0