
Curved track for plate chain


For chain range 882 TAB — GCB882T

- ***Used to support and guide CAP882T and CAP881T/SS plate chains***
- *Material*
  High density Black DESLIDUR

Info.

- *Comprises 2 tracks (carry and return)*





DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	For chain	AG (mm)	R1 (mm)	K (mm)	Weight (kg)	Price each 1 to 4
GCB882T-190	CAP882T-190	200	610	190,5	8,9	372,55 €
GCB882T-254	CAP882T-254	270	610	254,0	13,2	509,82 €
GCB882T-304	CAP882T-304	320	610	304,8	16,3	547,58 €

Dimensions in mm

Our other products


PR105

Articulated foot Ø103, Ø 103


CMM

Male rod ends DIN ISO12240-4, Steel / bronze


ZG0

Plastic spur gear, Machined plastic (delrin)


M0

Worm and wheel set, Hardened steel


BOXdh

Boxed set of cylindrical dowel pins DIN6325, Boxed set - Solid DIN 6...


BPLF

Ball transfer unit light duty, Light


MHMEP

Arm with rotating handle, Prebored


CHAR7530

Spring hinge, welded


PTA50

Articulated levelling foot, pressed base Ø50, Ø 50


RPP

Connecting plate for RPP type timing belts, RPP14


BOX-WM

Box set of washer - DIN125, Box set of steel washers


PCS37K

Chain sprocket with hardened teeth, 9.525mm (DIN06B-1)

Complementary products


CAP882

Flexible slat top chain acetal, Large range 882


PR882

Idler sprocket for slat top chain, Range 882