

Chain sprocket

Sta Size XS

PITCH 4mm

Stainless steel





stainless steel

- **Pitch 4mm**
- Roller diameter 2.5mm
- Material: stainless steel (303) Z10CNF 18.09

Accessories

- **SUA-4** chain *(tome 4 p.122)*

bore-size, keyway
MODIFY IT!
tapped hole, pin, etc...

Smallest size

DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	Z Teeth	ØP	ØD	ØM	ØA	Undercut Ø x width	Price each 1 to 5 S	AS
S 4-10	10	12,94	14,71	12	4	8,00 x 2,5	18,98 €	On request
S 4-11	11	14,20	16,02	12	4	8,00 x 2,5	20,16 €	
S 4-12	12	15,45	17,32	12	4	8,00 x 2,5	21,18 €	
S 4-13	13	16,71	18,62	12	4	9,05 x 2,5	22,24 €	
S 4-14	14	17,97	19,92	12	4	10,33 x 2,5	24,11 €	
S 4-15	15	19,23	21,21	12	4	11,60 x 2,5	24,71 €	
S 4-16	16	20,50	22,50	12	4	-	26,25 €	
S 4-17	17	21,76	23,79	12	4	-	28,43 €	
S 4-18	18	23,06	25,08	12	4	-	29,67 €	
S 4-19	19	24,29	26,37	12	4	-	31,01 €	
S 4-20	20	25,57	27,65	15	5	-	32,45 €	
S 4-21	21	26,83	28,94	15	5	-	33,81 €	
S 4-23	23	29,37	31,50	15	5	-	35,23 €	
S 4-25	25	31,91	34,06	15	5	-	36,59 €	
S 4-27	27	34,45	36,62	15	5	-	39,93 €	
S 4-30	30	38,26	40,45	15	5	-	44,56 €	
S 4-33	33	42,08	44,29	15	5	-	46,95 €	
S 4-35	35	44,62	46,84	15	5	-	48,29 €	
S 4-36	36	45,89	48,12	15	5	-	49,62 €	
S 4-38	38	48,43	50,67	15	5	-	49,97 €	
S 4-40	40	50,98	53,22	20	6	-	50,34 €	
S 4-42	42	53,52	55,77	20	6	-	50,54 €	
S 4-44	44	56,07	58,32	20	6	-	51,00 €	
S 4-48	48	61,12	63,42	20	6	-	51,47 €	
S 4-50	50	63,66	65,98	20	6	-	51,94 €	
S 4-60	60	76,39	78,72	20	6	-	53,99 €	
S 4-80	80	101,86	104,20	20	6	-	167,38 €	

Dimensions in mm


C45 steel

DIN 04-1

6mm

Economy range

- **Pitch 6mm (DIN 04-1)**
- Roller diameter 4mm
- Material:
  C45 UNI7845 steel
- **HPC are unable to modify these parts**
- **The prebore dimensions are given as a guide only and are subject to change





Accessories

- Chain part number **SUA-6/M** **(tome 4 p.122)**

DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part number	Z teeth	ØP	ØD	ØM	ØA**	E	Weight (kg)	Price each
PCS6-10	10	19,42	21,70	13	6	10	0,01	2,02 €
PCS6-11	11	21,30	23,60	14	6	10	0,01	2,16 €
PCS6-12	12	23,18	25,40	16	6	10	0,02	3,38 €
PCS6-13	13	25,05	27,30	18	8	10	0,02	3,39 €
PCS6-14	14	26,96	29,20	20	8	10	0,03	3,32 €
PCS6-15	15	28,86	31,00	20	8	10	0,03	3,40 €
PCS6-16	16	30,76	33,00	20	8	13	0,03	3,41 €
PCS6-17	17	32,65	35,00	20	8	13	0,04	3,36 €
PCS6-18	18	34,55	36,90	20	8	13	0,04	3,36 €
PCS6-19	19	36,44	38,80	20	8	13	0,04	3,33 €
PCS6-20	20	38,34	40,70	20	8	13	0,04	3,31 €
PCS6-21	21	40,25	42,60	25	8	13	0,06	3,64 €
PCS6-22	22	42,16	44,50	25	8	13	0,06	4,04 €
PCS6-23	23	44,06	46,40	25	8	13	0,06	4,23 €
PCS6-24	24	45,96	48,30	25	8	13	0,07	4,33 €
PCS6-25	25	47,87	50,20	25	8	13	0,07	4,73 €
PCS6-27	27	51,67	54,00	30	8	15	0,10	5,02 €
PCS6-30	30	57,42	59,80	30	8	15	0,11	6,67 €
PCS6-33	33	63,11	65,50	30	8	15	0,12	7,17 €
PCS6-35	35	66,93	69,30	30	8	15	0,13	7,55 €
PCS6-36	36	68,84	71,20	30	8	15	0,13	8,16 €
PCS6-38	38	72,66	75,00	30	8	15	0,14	8,34 €
PCS6-40	40	76,47	78,90	30	8	15	0,15	9,08 €
PCS6-45	45	86,01	88,50	40	10	16	0,46	11,41 €
PCS6-48	48	91,74	94,20	62	12	18	0,48	11,79 €
PCS6-50	50	95,55	98,00	50	12	20	0,49	11,81 €
PCS6-57	57	108,93	111,40	50	12	20	0,53	13,13 €
PCS6-76	76	145,19	147,60	60	12	20	1,58	25,90 €

Dimensions in mm

Chain sprocket

DIN 05B-1


8mm

C45 steel

- **Pitch 8mm (DIN 05B-1)**
- Roller diameter 5mm
- Material:
  C45 UNI7845 steel
- **HPC are unable to modify these parts**
- **The prebore dimensions are given as a guide only and are subject to change

Economy range





Accessories

- Chain part number **SBR-8/M, SBS-8/M** **(tome 4 p.122, p.124)**

DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part number	Z teeth	ØP	ØD	ØM	ØA**	E	Weight (kg)	Price each
PCS8-8	8	20,90	24,0	13	6	12	0,01	1,93 €
PCS8-9	9	23,39	26,6	15	6	12	0,02	1,92 €
PCS8-10	10	25,89	29,2	17	8	12	0,02	2,03 €
PCS8-11	11	28,39	31,7	18	8	13	0,03	2,15 €
PCS8-12	12	30,91	34,2	20	8	13	0,04	3,09 €
PCS8-13	13	33,42	36,7	23	8	13	0,05	3,13 €
PCS8-14	14	35,95	39,2	25	8	13	0,05	3,27 €
PCS8-15	15	38,48	41,7	28	8	13	0,07	3,50 €
PCS8-16	16	41,01	44,3	30	8	14	0,08	3,49 €
PCS8-17	17	43,53	46,8	30	8	14	0,09	3,64 €
PCS8-18	18	46,07	49,3	30	8	14	0,09	4,21 €
PCS8-19	19	48,61	51,9	30	8	14	0,09	4,20 €
PCS8-20	20	51,14	54,4	30	8	14	0,10	4,19 €
PCS8-21	21	53,68	57,0	35	8	14	0,12	4,28 €
PCS8-23	23	58,75	62,0	35	8	14	0,13	4,47 €
PCS8-25	25	63,83	67,5	35	8	14	0,15	4,93 €
PCS8-27	27	68,91	72,2	40	10	16	0,20	5,17 €
PCS8-30	30	76,53	79,8	40	10	16	0,22	7,08 €
PCS8-33	33	84,16	87,5	40	10	16	0,24	7,61 €
PCS8-35	35	89,25	92,5	40	10	16	0,25	8,33 €
PCS8-36	36	91,79	95,0	40	10	16	0,26	8,70 €
PCS8-38	38	96,88	100,2	40	10	16	0,28	9,64 €
PCS8-39	39	99,42	102,7	40	10	16	0,29	9,51 €
PCS8-40	40	101,97	105,3	40	10	16	0,58	10,84 €
PCS8-45	45	114,69	118,0	60	12	20	0,67	14,23 €
PCS8-48	48	122,32	125,6	60	12	20	0,63	16,78 €
PCS8-50	50	127,41	130,7	60	12	20	1,00	16,54 €


Dimensions in mm

C45 steel

Pitch 1/4”

Economy range

- **Pitch 1/4” (6,35mm)**
- Roller diameter 3,3mm
- Material:
  C45 UNI7845 steel
- **HPC *are unable to modify these parts***
- **The prebore dimensions are given as a guide only and are subject to change





Accessories

- Chain part number **SUA-250/M** **(tome 4 p.122)**

DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part number	Z teeth	ØP	ØD	ØM	ØA**	E	Weight (kg)	Price each
PCS25-8	8	16,58	19,4	10	6	12	0,01	2,24 €
PCS25-9	9	18,56	21,4	11,5	6	12	0,01	2,25 €
PCS25-10	10	20,55	23,3	13	6	12	0,02	2,36 €
PCS25-11	11	22,54	25,3	15	8	13	0,02	3,06 €
PCS25-12	12	24,53	27,3	17	8	13	0,02	3,52 €
PCS25-13	13	26,53	29,3	17	8	13	0,03	3,51 €
PCS25-14	14	28,53	31,3	17	8	13	0,03	3,72 €
PCS25-15	15	30,53	33,3	20	8	13	0,04	3,96 €
PCS25-16	16	32,55	35,3	22	8	14	0,05	3,94 €
PCS25-17	17	34,55	37,3	22	8	14	0,05	4,00 €
PCS25-18	18	36,56	39,4	25	8	14	0,06	4,14 €
PCS25-19	19	38,58	41,4	25	8	14	0,06	4,24 €
PCS25-20	20	40,58	43,4	25	8	14	0,06	4,34 €
PCS25-21	21	42,60	45,4	30	8	14	0,08	4,67 €
PCS25-25	25	50,66	53,5	30	8	14	0,10	5,63 €
PCS25-28	28	56,71	59,5	30	8	16	0,12	7,13 €
PCS25-29	29	58,73	61,5	30	8	16	0,12	7,53 €
PCS25-30	30	60,75	63,6	30	8	16	0,13	7,59 €
PCS25-32	32	64,78	67,6	30	8	16	0,13	8,81 €
PCS25-33	33	66,80	69,6	30	8	16	0,14	9,20 €
PCS25-34	34	68,82	71,6	30	8	16	0,17	9,31 €
PCS25-35	35	70,84	73,6	30	8	16	0,17	9,74 €
PCS25-36	36	72,85	75,6	30	8	16	0,15	10,22 €
PCS25-37	37	74,87	77,7	30	8	16	0,18	11,98 €
PCS25-38	38	76,89	79,7	30	8	16	0,16	13,22 €
PCS25-39	39	78,91	81,7	30	8	16	0,19	14,43 €
PCS25-40	40	80,93	83,7	30	8	16	0,17	15,81 €

Dimensions in mm

Chain sprocket


DIN06B-1
3/8"



C43 steel

Economy range

- **Pitch 3/8" (9.525mm) (DIN 06B-1)**
- Roller diameter 6.35mm
- Material:
  Steel C43
- **We are unable to modify these parts**
- **Pilot bore dimensions are given as a guide only and are subject to change**





Options

- American pitch (ASA) on request
- **Custom made versions are available**

Accessories

- **SBR-375** chains
(tome 4 p.122)

DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part number	Z Teeth	ØP	ØD	ØM	Pilot bore not guaranteed ØA**	E	Stock*	Price each 1 to 5
PCS37-8	8	24,89	28,0	15	8	22	✔	2,00 €
PCS37-9	9	27,85	31,0	18	8	22	✔	2,16 €
PCS37-10	10	30,82	34,0	20	8	22	✔	2,13 €
PCS37-12	12	36,80	40,0	25	8	25	✔	3,21 €
PCS37-13	13	39,80	43,0	28	10	25	✔	3,42 €
PCS37-14	14	42,80	46,3	31	10	25	✔	3,84 €
PCS37-15	15	45,81	49,3	34	10	25	✔	3,88 €
PCS37-16	16	48,82	52,3	37	10	28	✔	4,46 €
PCS37-17	17	51,83	55,3	40	10	28	✔	5,04 €
PCS37-18	18	54,85	58,3	43	10	28	✔	5,19 €
PCS37-20	20	60,89	64,3	46	10	28	✔	5,97 €
PCS37-21	21	63,91	68,0	48	12	28	✔	6,05 €
PCS37-22	22	66,93	71,0	50	12	28	✔	6,81 €
PCS37-23	23	69,95	73,5	52	12	28	-	7,39 €
PCS37-24	24	72,97	77,0	54	12	28	✔	7,86 €
PCS37-25	25	76,00	80,0	57	12	28	✔	8,60 €
PCS37-26	26	79,02	83,0	60	12	28	✔	8,73 €
PCS37-27	27	82,04	86,0	60	12	28	✔	8,97 €
PCS37-28	28	85,07	89,0	60	12	28	-	9,15 €
PCS37-29	29	88,09	92,0	60	12	28	-	9,69 €
PCS37-30	30	91,12	94,7	60	12	28	✔	10,14 €
PCS37-32	32	97,17	101,3	65	14	30	✔	11,95 €
PCS37-33	33	100,20	104,3	65	14	30	-	12,74 €
PCS37-34	34	103,23	107,3	65	14	30	✔	12,72 €
PCS37-35	35	106,26	110,4	65	14	30	-	13,58 €
PCS37-36	36	109,29	113,4	70	14	30	-	14,15 €
PCS37-38	38	115,34	119,5	70	14	30	-	14,72 €
PCS37-40	40	121,40	125,5	70	14	30	✔	15,16 €

*Depending on availability - Dimensions in mm

Stainless steel chain sprocket

304 stainless steel

DIN 06B-1
3/8"

- **Pitch 3/8" (9.525mm) (DIN 06B-1)**
- Roller diameter 6.35mm
- Material:
  stainless steel AISI 304
- ***We are unable to modify these parts***
- *Pilot bore dimensions are given as a guide only and are suject to change

stainless steel




Options

- American pitch (ASA) on request
- ***Custom made versions are available***

Accessories

- ***SBS-375*** chain
  tome 4 p.122)



DISCOUNTS

Qty	1+	4+	10+
Disc.	List	-12%	On request

Part number	Z teeth	ØP	ØD	ØM	Pilot bore no guaranteed ØA*	E	Stock*	Price each 1 to 3
PCS37-12/SS	12	36,80	40,0	25	8	25	✔	16,24 €
PCS37-13/SS	13	39,80	43,0	28	10	25	✔	16,93 €
PCS37-15/SS	15	45,81	49,3	34	10	25	✔	18,59 €
PCS37-16/SS	16	48,82	52,3	37	10	28	✔	22,70 €
PCS37-17/SS	17	51,83	55,3	40	10	28	✔	24,22 €
PCS37-18/SS	18	54,85	58,3	43	10	28	✔	25,23 €
PCS37-19/SS	19	57,87	61,3	46	10	28	-	25,69 €
PCS37-20/SS	20	60,89	64,3	46	10	28	✔	27,23 €
PCS37-21/SS	21	63,91	68,0	48	12	28	-	25,16 €
PCS37-23/SS	23	69,95	73,5	52	12	28	-	30,55 €
PCS37-25/SS	25	76,00	80,0	57	12	28	✔	33,59 €
PCS37-30/SS	30	91,12	94,7	60	12	30	✔	41,49 €

*Depending on availability - Dimensions in mm

Chain sprocket

DIN 08B-1


1/2"

C43 steel

Economy range



- **Pitch 1/2" (12.7mm) (DIN 08B-1)**
- Roller diameter 8.51mm
- Material: steel C43
- **We are unable to modify these parts**
- **Pilot bore dimensions are given as a guide only and are sujebct to change





Options

- American pitch (ASA) on request
- **Custom made versions are available**

Accessories

- **SBR-500** chains **(tome 4 p.122)**

DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part number	Z Teeth	ØP	ØD	ØM	Pilot bore not guaranteed ØA**	E	Stock*	Price each 1 to 5
PCS50-8	8	33,18	37,2	20	10	25	✔	2,31 €
PCS50-9	9	37,13	41,0	24	10	25	✔	3,47 €
PCS50-10	10	41,10	45,2	26	10	25	✔	4,02 €
PCS50-12	12	49,07	53,0	33	10	28	✔	5,35 €
PCS50-15	15	61,09	65,5	45	10	28	✔	6,76 €
PCS50-16	16	65,10	69,5	50	12	28	✔	7,48 €
PCS50-18	18	73,14	77,8	56	12	28	✔	8,11 €
PCS50-20	20	81,19	85,8	64	12	28	✔	10,48 €
PCS50-21	21	85,22	89,7	68	14	28	✔	11,11 €
PCS50-22	22	89,24	93,8	70	14	28	✔	11,48 €
PCS50-23	23	93,27	98,2	70	14	28	-	11,90 €
PCS50-24	24	97,29	101,8	70	14	28	✔	12,67 €
PCS50-25	25	101,33	105,8	70	14	28	✔	12,92 €
PCS50-26	26	105,36	110,0	70	16	30	✔	13,74 €
PCS50-27	27	109,40	114,0	70	16	30	-	13,94 €
PCS50-28	28	113,42	118,0	70	16	30	✔	14,28 €
PCS50-29	29	117,46	122,0	80	16	30	-	16,18 €
PCS50-30	30	121,50	126,1	80	16	30	✔	18,00 €
PCS50-31	31	125,54	130,2	90	16	30	-	18,93 €
PCS50-32	32	129,56	134,3	90	16	30	-	19,18 €
PCS50-33	33	133,60	138,4	90	16	30	-	19,39 €
PCS50-34	34	137,64	142,6	90	16	30	-	21,75 €
PCS50-35	35	141,68	146,7	90	16	30	-	22,36 €
PCS50-36	36	145,72	151,0	90	20	35	✔	24,79 €
PCS50-37	37	149,76	154,6	90	20	35	-	25,47 €
PCS50-38	38	153,80	158,6	90	20	35	-	25,63 €
PCS50-39	39	157,83	162,7	90	20	35	-	26,91 €
PCS50-40	40	161,87	166,8	90	20	35	✔	27,43 €

*Depending on availability - Dimensions in mm

Stainless steel chain sprocket

304 Stainless steel

DIN 08B-1

1/2”



- **Pitch 1/2” (12.7mm) (DIN 08B-1)**
- Roller diameter 8.51mm
- Material:
  stainless steel AISI 304
- ***We are unable to modify these parts***
- *Pilot bore dimensions are given as a guide only and are suject to change




Options

- American pitch (ASA) on request
- ***Custom made versions are available***

Accessories

- ***SBS-500*** chain
  tome 4 p.124)



DISCOUNTS

Qty	1+	4+	10+
Disc.	List	-12%	On request

Part number	Z teeth	ØP	ØD	ØM	Pilot bore no guaranteed ØA*	E	Stock*	Price each 1 to 3
PCS50-12/SS	12	49,07	53,0	33	10	28	✔	20,44 €
PCS50-13/SS	13	53,06	57,4	37	10	28	✔	22,75 €
PCS50-15/SS	15	61,09	65,5	45	10	28	✔	25,91 €
PCS50-16/SS	16	65,10	69,5	50	12	28	-	27,20 €
PCS50-17/SS	17	69,11	73,6	52	12	28	✔	29,60 €
PCS50-18/SS	18	73,14	77,8	56	12	28	-	34,05 €
PCS50-19/SS	19	77,16	81,7	60	12	28	✔	36,12 €
PCS50-20/SS	20	81,19	85,8	64	12	28	✔	39,95 €
PCS50-21/SS	21	85,22	89,7	68	14	28	-	44,07 €
PCS50-23/SS	23	93,27	98,2	70	14	28	-	49,55 €
PCS50-25/SS	25	101,33	105,8	70	14	28	✔	59,14 €
PCS50-30/SS	30	121,50	126,1	80	16	30	-	88,13 €


*Depending on availability - Dimensions in mm

Chain sprocket

DIN 10B-1

5/8"

C43 steel





- **Pitch 5/8" (15.875 mm) (DIN 10B-1)**
- Roller diameter 10.16mm
- Material: Steel C43
- **We are unable to modify these parts**
- **Pilot bore dimensions are given as a guide only and are subject to change

Options

- American pitch (ASA) on request
- **Custom made versions are available**

Accessories

- **SBR-625** chains **(tome 4 p.122)**

Economy range

DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part number	Z Teeth	ØP	ØD	ØM	Pilot bore not guaranteed ØA**	E	Stock*	Price each 1 to 5
PCS62-8	8	41,48	47,0	25	10	25	✔	3,88 €
PCS62-9	9	46,42	52,6	30	10	25	-	4,40 €
PCS62-10	10	51,37	57,5	35	10	25	✔	5,25 €
PCS62-13	13	66,32	73,0	47	12	30	✔	8,34 €
PCS62-15	15	76,36	83,0	57	12	30	✔	9,65 €
PCS62-16	16	81,37	88,0	60	14	30	✔	10,93 €
PCS62-17	17	86,39	93,0	60	14	30	✔	11,60 €
PCS62-18	18	91,42	98,3	70	14	30	✔	14,23 €
PCS62-20	20	101,49	108,4	75	14	30	✔	14,47 €
PCS62-21	21	106,52	113,4	75	16	30	✔	15,01 €
PCS62-22	22	111,55	118,0	80	16	30	-	16,07 €
PCS62-23	23	116,58	123,4	80	16	30	-	16,77 €
PCS62-24	24	121,62	128,3	80	16	30	-	17,43 €
PCS62-25	25	126,66	134,0	80	16	30	-	18,70 €
PCS62-26	26	131,70	139,0	85	20	35	-	22,23 €
PCS62-27	27	136,75	144,0	85	20	35	-	24,00 €
PCS62-28	28	141,78	148,7	90	20	35	-	24,98 €
PCS62-29	29	146,83	153,8	90	20	35	-	26,39 €
PCS62-30	30	151,87	158,8	90	20	35	✔	27,52 €
PCS62-31	31	156,92	163,9	95	20	35	-	29,40 €
PCS62-32	32	161,95	168,9	95	20	35	-	30,84 €
PCS62-33	33	167,00	174,5	95	20	35	-	31,85 €
PCS62-34	34	172,05	179,0	95	20	35	-	30,98 €
PCS62-35	35	177,10	184,1	95	20	35	-	31,58 €
PCS62-38	38	192,24	199,2	100	20	35	-	38,54 €
PCS62-39	39	197,29	204,2	100	20	35	-	40,35 €
PCS62-40	40	202,34	209,3	100	20	35	✔	41,45 €

*Depending on availability - Dimensions in mm

Stainless steel chain sprocket

304 stainless steel

DIN 10B-1

5/8”

- **Pitch 5/8” (15.875mm) (DIN 10B-1)**
- Roller diameter 10.16mm
- Material:
  strainless steel AISI 304
- **We are unable to modify these parts**
- *Pilot bore dimensions are given as a guide only and are suject to change

stainless steel




Options

- American pitch(ASA) on request
- **Custom made versions are available**

Accessories

- **SBS-625** chain **(tome 4 p.124)**



DISCOUNTS

Qty	1+	4+	10+
Disc.	List	-12%	On request

Part number	Z Teeth	ØP	ØD	ØM	*Pilot bore not guaranteed ØA	E	Price each. 1 to 3
PCS62-12/SS	12	61,34	68,0	42	12	30	29,13 €
PCS62-13/SS	13	66,32	73,0	47	12	30	31,60 €
PCS62-15/SS	15	76,36	83,0	57	12	30	38,89 €
PCS62-16/SS	16	81,37	88,0	60	14	30	43,62 €
PCS62-17/SS	17	86,39	93,0	60	14	30	46,52 €
PCS62-18/SS	18	91,42	98,3	70	14	30	58,24 €
PCS62-19/SS	19	96,45	103,3	70	14	30	59,08 €
PCS62-20/SS	20	101,49	108,4	75	14	30	68,26 €
PCS62-21/SS	21	106,52	113,4	75	16	30	65,79 €
PCS62-23/SS	23	116,58	123,4	80	16	30	82,38 €
PCS62-25/SS	25	126,66	134,0	80	16	30	98,02 €
PCS62-30/SS	30	151,87	158,8	90	20	35	117,53 €

Dimensions in mm


Chain sprocket with hardened teeth Ste DIN

DIN06B-1 3/8”



C45 tempered steel

- **Pitch 9.525mm (DIN06B-1)**
- Roller diameter 6.35mm
- Materials:
  C45 steel UNI7845
  Hardened teeth 45-53HRC




Info

- DIN 6885 keyway on the central tooth line
- 2 threaded holes, 1 on keyway and 1 at 90°

Accessories

- **SBR-375/M** *chain* **tome 4 p.122)**



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Stock*	Price each 1 to 5
PCS37-12H-12K	12	36,80	40,45	30	25	12	4	1,80	M4	✔	7,33 €
PCS37-12H-14K						14	5	2,30	M4	-	7,33 €
PCS37-12H-15K						15	5	2,30	M4	✔	7,33 €
PCS37-12H-16K						16	5	2,30	M4	✔	7,33 €
PCS37-13H-12K	13	39,80	43,50	28	25	12	4	1,80	M4	✔	7,83 €
PCS37-13H-14K						14	5	2,30	M4	-	7,83 €
PCS37-13H-15K						15	5	2,30	M4	✔	7,83 €
PCS37-13H-16K						16	5	2,30	M4	-	7,83 €
PCS37-13H-18K						18	6	2,80	M5	-	7,83 €
PCS37-14H-12K	14	42,80	46,50	31	25	12	4	1,80	M4	✔	8,44 €
PCS37-14H-14K						14	5	2,30	M4	-	8,44 €
PCS37-14H-15K						15	5	2,30	M4	✔	8,44 €
PCS37-14H-16K						16	5	2,30	M4	✔	8,44 €
PCS37-14H-18K						18	6	2,80	M5	-	8,44 €

*Depending on availability - Dimensions in mm

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Stock*	Price each 1 to 5
PCS37-15H-14K	15	45,81	49,50	34	25	14	5	2,30	M4	✔	8,62 €
PCS37-15H-15K						15	5	2,30	M4	-	8,62 €
PCS37-15H-16K						16	5	2,30	M4	-	8,62 €
PCS37-15H-18K						18	6	2,80	M4	✔	8,62 €
PCS37-15H-19K						19	6	2,80	M5	-	8,62 €
PCS37-15H-20K						20	6	2,80	M5	✔	8,62 €
PCS37-15H-22K						22	6	2,80	M5	-	8,62 €
PCS37-15H-24K						24	8	3,30	M6	-	8,62 €
PCS37-16H-14K	16	48,82	52,30	37	28	14	5	2,30	M4	✔	8,57 €
PCS37-16H-15K						15	5	2,30	M4	✔	8,15 €
PCS37-16H-16K						16	5	2,30	M4	-	8,57 €
PCS37-16H-18K						18	6	2,80	M5	-	8,57 €
PCS37-16H-19K						19	6	2,80	M5	-	8,57 €
PCS37-16H-20K						20	6	2,80	M5	✔	8,57 €
PCS37-16H-22K						22	6	2,80	M5	-	8,57 €
PCS37-16H-24K						24	8	3,30	M6	-	8,57 €
PCS37-17H-14K	17	51,83	55,50	40	28	14	5	2,30	M4	-	9,10 €
PCS37-17H-15K						15	5	2,30	M4	✔	9,10 €
PCS37-17H-16K						16	5	2,30	M4	-	9,10 €
PCS37-17H-18K						18	6	2,80	M5	✔	9,10 €
PCS37-17H-19K						19	6	2,80	M5	-	9,10 €
PCS37-17H-20K						20	6	2,80	M5	✔	9,10 €
PCS37-17H-22K						22	6	2,80	M5	-	9,10 €
PCS37-17H-24K						24	8	3,30	M6	✔	9,10 €
PCS37-18H-14K	18	54,85	58,30	43	28	14	5	2,30	M4	-	9,18 €
PCS37-18H-15K						15	5	2,30	M4	✔	9,18 €
PCS37-18H-16K						16	5	2,30	M4	-	9,18 €
PCS37-18H-18K						18	6	2,80	M5	-	9,18 €
PCS37-18H-19K						19	6	2,80	M5	-	9,18 €
PCS37-18H-20K						20	6	2,80	M5	✔	9,18 €
PCS37-18H-22K						22	6	2,80	M5	-	9,18 €
PCS37-18H-24K						24	8	3,30	M6	-	9,18 €
PCS37-19H-15K	19	57,87	61,60	45	28	15	5	2,30	M4	✔	9,59 €
PCS37-19H-16K						16	5	2,30	M4	-	9,59 €
PCS37-19H-18K						18	6	2,80	M5	-	9,59 €
PCS37-19H-19K						19	6	2,80	M5	-	9,59 €
PCS37-19H-20K						20	6	2,80	M5	✔	9,59 €
PCS37-19H-22K						22	6	2,80	M5	-	9,59 €
PCS37-19H-24K						24	8	3,30	M6	-	9,59 €
PCS37-19H-25K						25	8	3,30	M6	✔	9,59 €
PCS37-20H-15K	20	60,89	64,30	46	28	15	5	2,30	M4	-	10,19 €
PCS37-20H-16K						16	5	2,30	M4	-	10,19 €
PCS37-20H-18K						18	6	2,80	M5	-	10,19 €
PCS37-20H-19K						19	6	2,80	M5	-	10,19 €
PCS37-20H-20K						20	6	2,80	M5	✔	10,19 €
PCS37-20H-22K						22	6	2,80	M5	-	10,19 €
PCS37-20H-24K						24	8	3,30	M6	-	10,19 €
PCS37-20H-25K						25	8	3,30	M6	✔	10,19 €

*Depending on availability - Dimensions in mm

Chain sprocket with hardened teeth Ste DIN

DIN06B-1 3/8”



C45 tempered steel


- **Pitch 9.525mm (DIN06B-1)**
- Roller diameter 6.35mm
- Materials:
  C45 steel UNI7845
  Hardened teeth 45-53HRC

Info

- DIN 6885 keyway on the central tooth line
- 2 threaded holes, 1 on keyway and 1 at 90°

Accessories

- **SBR-375/M** *chain* **tome 4 p.122)**




DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Stock*	Price each 1 to 5
PCS37-21H-15K	21	63,91	67,60	48	28	15	5	2,30	M4	-	10,53 €
PCS37-21H-16K						16	5	2,30	M4	-	10,53 €
PCS37-21H-18K						18	6	2,80	M5	-	10,53 €
PCS37-21H-19K						19	6	2,80	M5	-	10,53 €
PCS37-21H-20K						20	6	2,80	M5	-	10,53 €
PCS37-21H-22K						22	6	2,80	M5	-	10,53 €
PCS37-21H-24K						24	8	3,30	M6	-	10,53 €
PCS37-21H-25K						25	8	3,30	M6	✔	10,53 €
PCS37-23H-15K	23	69,95	73,70	52	28	15	5	2,30	M4	✔	12,06 €
PCS37-23H-16K						16	5	2,30	M4	-	12,06 €
PCS37-23H-18K						18	6	2,80	M5	-	12,06 €
PCS37-23H-19K						19	6	2,80	M5	-	12,06 €
PCS37-23H-20K						20	6	2,80	M5	✔	12,06 €
PCS37-23H-22K						22	6	2,80	M5	-	12,06 €
PCS37-23H-24K						24	8	3,30	M6	-	12,06 €
PCS37-23H-25K						25	8	3,30	M6	✔	12,06 €

*Depending on availability - Dimensions in mm



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Stock*	Price each 1 to 5
PCS37-24H-18K						18	6	2,80	M5	-	12,88 €
PCS37-24H-19K						19	6	2,80	M5	-	12,88 €
PCS37-24H-20K						20	6	2,80	M5	✔	12,88 €
PCS37-24H-22K	24	72,97	76,70	54	28	22	6	2,80	M5	-	12,88 €
PCS37-24H-24K						24	8	3,30	M6	-	12,88 €
PCS37-24H-25K						25	8	3,30	M6	-	12,88 €
PCS37-24H-28K						28	8	3,30	M6	-	12,88 €
PCS37-24H-30K						30	8	3,30	M6	-	12,88 €
PCS37-25H-18K						18	6	2,80	M5	-	13,82 €
PCS37-25H-19K						19	6	2,80	M5	-	15,15 €
PCS37-25H-20K						20	6	2,80	M5	-	13,82 €
PCS37-25H-22K	25	76,00	79,70	57	28	22	6	2,80	M5	-	13,82 €
PCS37-25H-24K						24	8	3,30	M6	-	13,82 €
PCS37-25H-25K						25	8	3,30	M6	-	13,82 €
PCS37-25H-28K						28	8	3,30	M6	-	13,82 €
PCS37-25H-30K						30	8	3,30	M6	-	13,82 €
PCS37-27H-20K						20	6	2,80	M5	✔	16,46 €
PCS37-27H-22K						22	6	2,80	M5	-	16,46 €
PCS37-27H-24K	27	82,05	85,70	60	28	24	8	3,30	M6	-	16,46 €
PCS37-27H-25K						25	8	3,30	M6	-	16,46 €
PCS37-27H-28K						28	8	3,30	M6	-	16,46 €
PCS37-27H-30K						30	8	3,30	M6	-	16,46 €
PCS37-30H-20K						20	6	2,80	M5	-	19,18 €
PCS37-30H-22K						22	6	2,80	M5	-	19,18 €
PCS37-30H-24K	30	91,12	94,80	60	30	24	8	3,30	M6	-	19,18 €
PCS37-30H-25K						25	8	3,30	M6	✔	19,18 €
PCS37-30H-28K						28	8	3,30	M6	-	19,18 €
PCS37-30H-30K						30	8	3,30	M6	-	19,18 €


*Depending on availability - Dimensions in mm

Chain sprocket with hardened teeth Ste DIN

DIN08B-1
1/2”



C45 tempered steel




- **Pitch 12,7mm (DIN 08B-1)**
- Roller diameter 8,51mm
- Materials:
  C45 steel UNI7845
  Hardened teeth 45-53HRC


Info


- DIN 6885 keyway on the central tooth line
- 2 threaded holes, 1 on keyway and 1 at 90°

Accessories

- **SBR-500/M** chain **(tome 4 p.122)**







DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Stock*	Price each 1 to 5
PCS50-12H-12K						12	4	1,80	M4	✔	9,81 €
PCS50-12H-14K						14	5	2,30	M4	✔	9,81 €
PCS50-12H-15K						15	5	2,30	M4	-	9,81 €
PCS50-12H-16K	12	49,07	53,90	33	28	16	5	2,30	M4	✔	9,81 €
PCS50-12H-18K						18	6	2,80	M5	✔	9,81 €
PCS50-12H-19K						19	6	2,80	M5	✔	9,81 €
PCS50-12H-20K						20	6	2,80	M5	✔	9,81 €
PCS50-13H-12K						12	4	1,80	M4	✔	10,04 €
PCS50-13H-14K						14	5	2,30	M4	✔	10,04 €
PCS50-13H-15K						15	5	2,30	M4	-	10,04 €
PCS50-13H-16K						16	5	2,30	M4	-	10,04 €
PCS50-13H-18K	13	53,06	57,90	37	28	18	6	2,80	M5	-	10,04 €
PCS50-13H-19K						19	6	2,80	M5	✔	10,04 €
PCS50-13H-20K						20	6	2,80	M5	✔	10,04 €
PCS50-13H-22K						22	6	2,80	M5	-	10,04 €
PCS50-13H-24K						24	8	3,30	M6	✔	10,04 €

*Depending on availability - Dimensions in mm

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Stock*	Price each 1 to 5
PCS50-14H-14K						14	5	2,30	M4	-	10,84 €
PCS50-14H-15K						15	5	2,30	M4	-	10,84 €
PCS50-14H-16K						16	5	2,30	M4	-	10,84 €
PCS50-14H-18K						18	6	2,80	M5	✔	10,84 €
PCS50-14H-19K	14	57,07	61,60	41	28	19	6	2,80	M5	-	10,84 €
PCS50-14H-20K						20	6	2,80	M5	✔	10,84 €
PCS50-14H-22K						22	6	2,80	M5	-	10,84 €
PCS50-14H-24K						24	8	3,30	M6	-	10,84 €
PCS50-14H-25K						25	8	3,30	M6	✔	10,84 €
PCS50-15H-14K						14	5	2,30	M4	✔	11,44 €
PCS50-15H-15K						15	5	2,30	M4	-	11,44 €
PCS50-15H-16K						16	5	2,30	M4	-	11,44 €
PCS50-15H-18K						18	6	2,80	M4	-	11,44 €
PCS50-15H-19K						19	6	2,80	M5	✔	11,44 €
PCS50-15H-20K	15	61,09	65,90	45	28	20	6	2,80	M5	✔	11,44 €
PCS50-15H-22K						22	6	2,80	M5	-	11,44 €
PCS50-15H-24K						24	8	3,30	M6	-	11,44 €
PCS50-15H-25K						25	8	3,30	M6	✔	11,44 €
PCS50-15H-28K						28	8	3,30	M6	✔	11,44 €
PCS50-15H-30K						30	8	3,30	M6	-	11,44 €
PCS50-16H-15K						15	5	2,30	M4	-	12,82 €
PCS50-16H-16K						16	5	2,30	M4	-	12,82 €
PCS50-16H-18K						18	6	2,80	M4	-	12,82 €
PCS50-16H-19K						19	6	2,80	M5	-	12,82 €
PCS50-16H-20K	16	65,10	69,50	50	28	20	6	2,80	M5	✔	12,82 €
PCS50-16H-22K						22	6	2,80	M5	-	12,82 €
PCS50-16H-24K						24	8	3,30	M6	-	12,82 €
PCS50-16H-25K						25	8	3,30	M6	✔	12,82 €
PCS50-16H-28K						28	8	3,30	M6	✔	12,82 €
PCS50-16H-30K						30	8	3,30	M6	-	12,82 €
PCS50-17H-15K						15	5	2,30	M4	-	13,23 €
PCS50-17H-16K						16	5	2,30	M4	-	13,23 €
PCS50-17H-18K						18	6	2,80	M4	-	13,23 €
PCS50-17H-19K						19	6	2,80	M5	-	13,23 €
PCS50-17H-20K	17	69,11	74,00	52	28	20	6	2,80	M5	✔	13,23 €
PCS50-17H-22K						22	6	2,80	M5	-	13,23 €
PCS50-17H-24K						24	8	3,30	M6	-	13,23 €
PCS50-17H-25K						25	8	3,30	M6	-	13,23 €
PCS50-17H-28K						28	8	3,30	M6	-	13,23 €
PCS50-17H-30K						30	8	3,30	M6	✔	13,23 €
PCS50-18H-16K						16	5	2,30	M4	-	13,79 €
PCS50-18H-18K						18	6	2,80	M4	-	13,79 €
PCS50-18H-19K						19	6	2,80	M5	-	13,79 €
PCS50-18H-20K						20	6	2,80	M5	✔	13,79 €
PCS50-18H-22K						22	6	2,80	M5	-	13,79 €
PCS50-18H-24K	18	73,14	77,80	56	28	24	8	3,30	M6	✔	13,79 €
PCS50-18H-25K						25	8	3,30	M6	-	13,79 €
PCS50-18H-28K						28	8	3,30	M6	-	13,79 €
PCS50-18H-30K						30	8	3,30	M6	✔	13,79 €
PCS50-18H-32K						32	10	3,30	M8	-	13,79 €
PCS50-18H-35K						35	10	3,30	M8	-	13,79 €

*Depending on availability - Dimensions in mm


Chain sprocket with hardened teeth Ste DIN

DIN08B-1
1/2”



C45 tempered steel

- **Pitch 12,7mm (DIN 08B-1)**
- Roller diameter 8,51mm
- Materials:
  C45 steel UNI7845
  Hardened teeth 45-53HRC




Info

- DIN 6885 keyway on the central tooth line
- 2 threaded holes, 1 on keyway and 1 at 90°

Accessories

- **SBR-500/M** *chain* **(tome 4 p.122)**



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Stock*	Price each 1 to 5
PCS50-19H-19K						19	6	2,80	M5	-	15,28 €
PCS50-19H-20K						20	6	2,80	M5	✔	15,28 €
PCS50-19H-22K						22	8	3,30	M6	-	15,28 €
PCS50-19H-24K						24	8	3,30	M6	-	15,28 €
PCS50-19H-25K	19	77,16	82,00	60	28	25	8	3,30	M6	✔	15,28 €
PCS50-19H-28K						28	8	3,30	M6	-	15,28 €
PCS50-19H-30K						30	10	3,30	M8	-	15,28 €
PCS50-19H-32K						32	10	3,30	M8	-	15,28 €
PCS50-19H-35K						35	10	3,30	M8	-	15,28 €
PCS50-20H-19K						19	6	2,80	M5	-	15,97 €
PCS50-20H-20K						20	6	2,80	M5	✔	15,97 €
PCS50-20H-22K						22	6	2,80	M5	-	15,97 €
PCS50-20H-24K						24	8	3,30	M6	-	15,97 €
PCS50-20H-25K	20	81,19	85,80	64	28	25	8	3,30	M6	-	15,97 €
PCS50-20H-28K						28	8	3,30	M6	-	15,97 €
PCS50-20H-30K						30	8	3,30	M6	✔	15,97 €
PCS50-20H-32K						32	10	3,30	M8	-	15,97 €
PCS50-20H-35K						35	10	3,30	M8	-	15,97 €

*Depending on availability - Dimensions in mm

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Stock*	Price each 1 to 5
PCS50-21H-19K						19	6	2,80	M5	-	16,73 €
PCS50-21H-20K						20	6	2,80	M5	✔	16,73 €
PCS50-21H-22K						22	6	2,80	M5	-	16,73 €
PCS50-21H-24K						24	8	3,30	M6	-	16,73 €
PCS50-21H-25K	21	85,22	90,10	68	28	25	8	3,30	M6	-	16,73 €
PCS50-21H-28K						28	8	3,30	M6	-	16,73 €
PCS50-21H-30K						30	8	3,30	M6	-	16,73 €
PCS50-21H-32K						32	10	3,30	M8	-	16,73 €
PCS50-21H-35K						35	10	3,30	M8	-	16,73 €
PCS50-23H-20K						20	6	2,80	M5	✔	18,00 €
PCS50-23H-22K						22	6	2,80	M5	-	18,00 €
PCS50-23H-24K						24	8	3,30	M6	-	18,00 €
PCS50-23H-25K						25	8	3,30	M6	-	18,00 €
PCS50-23H-28K	23	93,27	98,10	70	28	28	8	3,30	M6	-	18,00 €
PCS50-23H-30K						30	8	3,30	M6	-	18,00 €
PCS50-23H-32K						32	10	3,30	M8	-	18,00 €
PCS50-23H-35K						35	10	3,30	M8	-	18,00 €
PCS50-23H-38K						38	10	3,30	M8	-	18,00 €
PCS50-24H-20K						20	6	2,80	M5	-	19,19 €
PCS50-24H-22K						22	6	2,80	M5	-	19,19 €
PCS50-24H-24K						24	8	3,30	M6	✔	19,19 €
PCS50-24H-25K						25	8	3,30	M6	✔	19,19 €
PCS50-24H-28K	24	97,29	102,70	70	28	28	8	3,30	M6	-	19,19 €
PCS50-24H-30K						30	8	3,30	M6	-	19,19 €
PCS50-24H-32K						32	10	3,30	M8	-	19,19 €
PCS50-24H-35K						35	10	3,30	M8	-	19,19 €
PCS50-24H-38K						38	10	3,30	M8	-	19,19 €
PCS50-25H-20K						20	6	2,80	M5	✔	19,84 €
PCS50-25H-22K						22	6	2,80	M5	-	19,84 €
PCS50-25H-24K						24	8	3,30	M6	-	19,84 €
PCS50-25H-25K						25	8	3,30	M6	-	19,84 €
PCS50-25H-28K	25	101,33	105,80	70	28	28	8	3,30	M6	-	19,84 €
PCS50-25H-30K						30	8	3,30	M6	-	19,84 €
PCS50-25H-32K						32	10	3,30	M8	-	19,84 €
PCS50-25H-35K						35	10	3,30	M8	-	19,84 €
PCS50-25H-38K						38	10	3,30	M8	-	19,84 €
PCS50-27H-22K						22	6	2,80	M5	-	23,41 €
PCS50-27H-25K						25	8	3,30	M6	✔	23,41 €
PCS50-27H-28K						28	8	3,30	M6	-	23,41 €
PCS50-27H-30K	27	109,40	114,00	70	30	30	8	3,30	M6	✔	23,41 €
PCS50-27H-32K						32	10	3,30	M8	-	23,41 €
PCS50-27H-35K						35	10	3,30	M8	-	23,41 €
PCS50-27H-38K						38	10	3,30	M8	-	23,41 €
PCS50-30H-25K						25	8	3,30	M6	-	27,09 €
PCS50-30H-28K						28	8	3,30	M6	-	27,09 €
PCS50-30H-30K	30	121,50	126,00	80	30	30	8	3,30	M6	✔	27,09 €
PCS50-30H-32K						32	10	3,30	M8	-	27,09 €
PCS50-30H-35K						35	10	3,30	M8	-	27,09 €
PCS50-30H-38K						38	10	3,30	M8	-	27,09 €

*Depending on availability - Dimensions in mm


Chain sprocket with hardened teeth Ste DIN

DIN10B-1 5/8”

C45 tempered steel



- **Pitch 15,875mm (DIN 10B-1)**
- Roller diameter 10,16mm
- Materials:
  C45 steel UNI7845
  Hardened teeth 45-53HRC





Info


- DIN 6885 keyway on the central tooth line
- 2 threaded holes, 1 on keyway and 1 at 90°

Accessories

- **SBR-625/M** *chain* **(tome 4 p.122)**







DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS62-12H-16K	12	61,34	68,20	42	30	16	5	2,30	M4	12,81 €
PCS62-12H-19K						19	6	2,80	M5	12,81 €
PCS62-12H-20K						20	6	2,80	M5	12,81 €
PCS62-12H-22K						22	6	2,80	M5	12,81 €
PCS62-12H-24K						24	8	3,30	M6	12,81 €
PCS62-12H-25K						25	8	3,30	M6	12,81 €
PCS62-12H-28K				51	30	28	8	3,30	M6	12,81 €
PCS62-12H-30K				51	30	30	8	3,30	M6	12,81 €
PCS62-13H-16K	13	66,32	73,20	47	30	16	5	2,30	M4	13,17 €
PCS62-13H-19K						19	6	2,80	M5	13,17 €
PCS62-13H-20K						20	6	2,80	M5	13,17 €
PCS62-13H-22K						22	6	2,80	M5	13,17 €
PCS62-13H-24K						24	8	3,30	M6	13,17 €
PCS62-13H-25K						25	8	3,30	M6	13,17 €
PCS62-13H-28K						28	8	3,30	M6	13,17 €
PCS62-13H-30K						30	8	3,30	M6	13,17 €

All dimensions in mm

DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 à 5
PCS62-14H-16K	14	71,34	78,20	52	30	16	5	2,30	M4	14,33 €
PCS62-14H-19K						19	6	2,80	M5	14,33 €
PCS62-14H-20K						20	6	2,80	M5	14,33 €
PCS62-14H-22K						22	6	2,80	M5	14,33 €
PCS62-14H-24K						24	8	3,30	M6	14,33 €
PCS62-14H-25K						25	8	3,30	M6	14,33 €
PCS62-14H-28K						28	8	3,30	M6	14,33 €
PCS62-14H-30K						30	8	3,30	M6	14,33 €
PCS62-15H-19K	15	76,36	83,20	57	30	19	6	2,80	M5	16,12 €
PCS62-15H-20K						20	6	2,80	M5	16,12 €
PCS62-15H-22K						22	6	2,80	M5	16,12 €
PCS62-15H-24K						24	8	3,30	M6	16,12 €
PCS62-15H-25K						25	8	3,30	M6	16,12 €
PCS62-15H-28K						28	8	3,30	M6	16,12 €
PCS62-15H-30K						30	8	3,30	M6	16,12 €
PCS62-15H-32K						32	10	3,30	M8	16,12 €
PCS62-15H-35K						35	10	3,30	M8	16,12 €
PCS62-16H-20K	16	81,37	88,00	60	30	20	6	2,80	M5	17,39 €
PCS62-16H-22K						22	6	2,80	M5	17,39 €
PCS62-16H-24K						24	8	3,30	M6	17,39 €
PCS62-16H-25K						25	8	3,30	M6	17,39 €
PCS62-16H-28K						28	8	3,30	M6	17,39 €
PCS62-16H-30K						30	8	3,30	M6	17,39 €
PCS62-16H-32K						32	10	3,30	M8	17,39 €
PCS62-16H-35K						35	10	3,30	M8	17,39 €
PCS62-17H-20K	17	86,39	93,20	60	30	20	6	2,80	M5	18,25 €
PCS62-17H-22K						22	6	2,80	M5	18,25 €
PCS62-17H-24K						24	8	3,30	M6	18,25 €
PCS62-17H-25K						25	8	3,30	M6	18,25 €
PCS62-17H-28K						28	8	3,30	M6	18,25 €
PCS62-17H-30K						30	8	3,30	M6	18,25 €
PCS62-17H-32K						32	10	3,30	M8	18,25 €
PCS62-17H-35K						35	10	3,30	M8	18,25 €
PCS62-18H-20K	18	91,42	98,30	70	30	20	6	2,80	M5	20,40 €
PCS62-18H-22K						22	6	2,80	M5	20,40 €
PCS62-18H-24K						24	8	3,30	M6	20,40 €
PCS62-18H-25K						25	8	3,30	M6	20,40 €
PCS62-18H-28K						28	8	3,30	M6	20,40 €
PCS62-18H-30K						30	8	3,30	M6	20,40 €
PCS62-18H-32K						32	10	3,30	M8	20,40 €
PCS62-18H-35K						35	10	3,30	M8	20,40 €
PCS62-18H-38K						38	10	3,30	M8	20,40 €
PCS62-18H-40K						40	12	3,30	M10	20,40 €

All dimensions in mm


Chain sprocket with hardened teeth Ste DIN

DIN10B-1
5/8”

C45 tempered steel



- **Pitch 15,875mm (DIN 10B-1)**
- Roller diameter 10,16mm
- Materials:
  C45 steel UNI7845
  Hardened teeth 45-53HRC




Info

- DIN 6885 keyway on the central tooth line
- 2 threaded holes, 1 on keyway and 1 at 90°

Accessories

- **SBR-625/M** chain **(tome 4 p.122)**



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS62-19H-20K	19	96,45	103,30	70	30	20	6	2,80	M5	22,01 €
PCS62-19H-22K						22	6	2,80	M5	22,01 €
PCS62-19H-24K						24	8	3,30	M6	22,01 €
PCS62-19H-25K						25	8	3,30	M6	22,01 €
PCS62-19H-28K						28	8	3,30	M6	22,01 €
PCS62-19H-30K						30	8	3,30	M6	22,01 €
PCS62-19H-32K						32	10	3,30	M8	22,01 €
PCS62-19H-35K						35	10	3,30	M8	22,01 €
PCS62-19H-38K						38	10	3,30	M8	22,01 €
PCS62-19H-40K						40	12	3,30	M10	22,01 €

All dimensions in mm

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS62-20H-20K						20	6	2,80	M5	23,20 €
PCS62-20H-22K						22	6	2,80	M5	23,20 €
PCS62-20H-24K						24	8	3,30	M6	23,20 €
PCS62-20H-25K						25	8	3,30	M6	23,20 €
PCS62-20H-28K						28	8	3,30	M6	23,20 €
PCS62-20H-30K	20	101,49	108,40	75	30	30	8	3,30	M6	23,20 €
PCS62-20H-32K						32	10	3,30	M8	23,20 €
PCS62-20H-35K						35	10	3,30	M8	23,20 €
PCS62-20H-38K						38	10	3,30	M8	23,20 €
PCS62-20H-40K						40	12	3,30	M10	23,20 €
PCS62-21H-20K						20	6	2,80	M5	24,57 €
PCS62-21H-22K						22	6	2,80	M5	24,57 €
PCS62-21H-24K						24	8	3,30	M6	24,57 €
PCS62-21H-25K						25	8	3,30	M6	24,57 €
PCS62-21H-28K						28	8	3,30	M6	24,57 €
PCS62-21H-30K	21	106,52	113,40	75	30	30	8	3,30	M6	24,57 €
PCS62-21H-32K						32	10	3,30	M8	24,57 €
PCS62-21H-35K						35	10	3,30	M8	24,57 €
PCS62-21H-38K						38	10	3,30	M8	24,57 €
PCS62-21H-40K						40	12	3,30	M10	24,57 €
PCS62-23H-20K						20	6	2,80	M5	26,77 €
PCS62-23H-22K						22	6	2,80	M5	26,77 €
PCS62-23H-24K						24	8	3,30	M6	26,77 €
PCS62-23H-25K						25	8	3,30	M6	26,77 €
PCS62-23H-28K						28	8	3,30	M6	26,77 €
PCS62-23H-30K	23	116,58	123,40	80	30	30	8	3,30	M6	26,77 €
PCS62-23H-32K						32	10	3,30	M8	26,77 €
PCS62-23H-35K						35	10	3,30	M8	26,77 €
PCS62-23H-38K						38	10	3,30	M8	26,77 €
PCS62-23H-40K						40	12	3,30	M10	26,77 €
PCS62-23H-42K						42	12	3,30	M10	26,77 €
PCS62-24H-20K						20	6	2,80	M5	28,21 €
PCS62-24H-22K						22	6	2,80	M5	28,21 €
PCS62-24H-24K						24	8	3,30	M6	28,21 €
PCS62-24H-25K						25	8	3,30	M6	28,21 €
PCS62-24H-28K						28	8	3,30	M6	28,21 €
PCS62-24H-30K	24	121,62	128,50	80	30	30	8	3,30	M6	28,21 €
PCS62-24H-32K						32	10	3,30	M8	28,21 €
PCS62-24H-35K						35	10	3,30	M8	28,21 €
PCS62-24H-38K						38	10	3,30	M8	28,21 €
PCS62-24H-40K						40	12	3,30	M10	28,21 €
PCS62-24H-42K						42	12	3,30	M10	28,21 €
PCS62-25H-22K						22	6	2,80	M5	29,15 €
PCS62-25H-24K						24	8	3,30	M6	29,15 €
PCS62-25H-25K						25	8	3,30	M6	29,15 €
PCS62-25H-28K						28	8	3,30	M6	29,15 €
PCS62-25H-30K	25	126,66	133,50	80	30	30	8	3,30	M6	29,15 €
PCS62-25H-32K						32	10	3,30	M8	29,15 €
PCS62-25H-35K						35	10	3,30	M8	29,15 €
PCS62-25H-38K						38	10	3,30	M8	29,15 €
PCS62-25H-40K						40	12	3,30	M10	29,15 €
PCS62-25H-42K						42	12	3,30	M10	29,15 €

All dimensions in mm


Chain sprocket with hardened teeth Ste DIN

DIN12B-1
3/4”

C45 tempered steel



- **Pitch 19,05mm (DIN 12B-1)**
- Roller diameter 12,07mm
- Materials:
  C45 steel UNI7845
  Hardened teeth 45-53HRC





Info


- DIN 6885 keyway on the central tooth line
- 2 threaded holes, 1 on keyway and 1 at 90°

Accessories

- **SBR-750/M** chain **(tome 4 p.122)**







DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS75-12H-20K	12	73,60	81,80	52	35	20	6	2,80	M5	16,66 €
PCS75-12H-22K						22	6	2,80	M5	16,66 €
PCS75-12H-24K						24	8	3,30	M6	16,66 €
PCS75-12H-25K						25	8	3,30	M6	16,66 €
PCS75-12H-28K						28	8	3,30	M6	16,66 €
PCS75-12H-30K						30	8	3,30	M6	16,66 €
PCS75-13H-20K	13	79,60	87,10	58	35	20	6	2,80	M5	19,32 €
PCS75-13H-22K						22	6	2,80	M5	19,32 €
PCS75-13H-24K						24	8	3,30	M6	19,32 €
PCS75-13H-25K						25	8	3,30	M6	19,32 €
PCS75-13H-28K						28	8	3,30	M6	19,32 €
PCS75-13H-30K						30	8	3,30	M6	19,32 €
PCS75-13H-32K						32	10	3,30	M8	19,32 €
PCS75-13H-35K						35	10	3,30	M8	19,32 €

All dimensions in mm

DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS75-14H-20K	14	85,61	93,80	64	35	20	6	2,80	M5	22,00 €
PCS75-14H-22K						22	6	2,80	M5	22,00 €
PCS75-14H-24K						24	8	3,30	M6	22,00 €
PCS75-14H-25K						25	8	3,30	M6	22,00 €
PCS75-14H-28K						28	8	3,30	M6	22,00 €
PCS75-14H-30K						30	8	3,30	M6	22,00 €
PCS75-14H-32K						32	10	3,30	M8	22,00 €
PCS75-14H-35K						35	10	3,30	M8	22,00 €
PCS75-15H-20K	15	91,63	99,20	70	35	20	6	2,80	M5	24,00 €
PCS75-15H-22K						22	6	2,80	M5	24,00 €
PCS75-15H-24K						24	8	3,30	M6	24,00 €
PCS75-15H-25K						25	8	3,30	M6	24,00 €
PCS75-15H-28K						28	8	3,30	M6	24,00 €
PCS75-15H-30K						30	8	3,30	M6	24,00 €
PCS75-15H-32K						32	10	3,30	M8	24,00 €
PCS75-15H-35K						35	10	3,30	M8	24,00 €
PCS75-15H-38K						38	10	3,30	M8	24,00 €
PCS75-15H-40K						40	12	3,30	M10	24,00 €
PCS75-16H-20K	16	97,65	105,50	75	35	20	6	2,80	M5	25,64 €
PCS75-16H-22K						22	6	2,80	M5	25,64 €
PCS75-16H-24K						24	8	3,30	M6	28,00 €
PCS75-16H-25K						25	8	3,30	M6	25,64 €
PCS75-16H-28K						28	8	3,30	M6	25,64 €
PCS75-16H-30K						30	8	3,30	M6	25,64 €
PCS75-16H-32K						32	10	3,30	M8	25,64 €
PCS75-16H-35K						35	10	3,30	M8	25,64 €
PCS75-16H-38K						38	10	3,30	M8	25,64 €
PCS75-16H-40K						40	12	3,30	M10	25,64 €
PCS75-17H-22K	17	103,67	111,20	80	35	22	6	2,80	M5	27,51 €
PCS75-17H-24K						24	8	3,30	M6	30,13 €
PCS75-17H-25K						25	8	3,30	M6	27,51 €
PCS75-17H-28K						28	8	3,30	M6	27,51 €
PCS75-17H-30K						30	8	3,30	M6	27,51 €
PCS75-17H-32K						32	10	3,30	M8	27,51 €
PCS75-17H-35K						35	10	3,30	M8	27,51 €
PCS75-17H-38K						38	10	3,30	M8	27,51 €
PCS75-17H-40K						40	12	3,30	M10	27,51 €
PCS75-18H-22K	18	109,71	118,00	80	35	22	6	2,80	M5	28,28 €
PCS75-18H-24K						24	8	3,30	M6	31,05 €
PCS75-18H-25K						25	8	3,30	M6	28,28 €
PCS75-18H-28K						28	8	3,30	M6	28,28 €
PCS75-18H-30K						30	8	3,30	M6	28,28 €
PCS75-18H-32K						32	10	3,30	M8	28,28 €
PCS75-18H-35K						35	10	3,30	M8	28,28 €
PCS75-18H-38K						38	10	3,30	M8	28,28 €
PCS75-18H-40K						40	12	3,30	M10	28,28 €

All dimensions in mm


Chain sprocket with hardened teeth Ste DIN

DIN12B-1
3/4”

C45 tempered steel



2 threaded holes



Bore and keyway


- **Pitch 19,05mm (DIN 12B-1)**
- Roller diameter 12,07mm
- Materials:
  C45 steel UNI7845
  Hardened teeth 45-53HRC


Info


- DIN 6885 keyway on the central tooth line
- 2 threaded holes, 1 on keyway and 1 at 90°

Accessories

- **SBR-750/M** chain **(tome 4 p.122)**







DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS75-19H-25K						25	8	3,30	M6	30,88 €
PCS75-19H-28K						28	8	3,30	M6	30,88 €
PCS75-19H-30K						30	8	3,30	M6	30,88 €
PCS75-19H-32K						32	10	3,30	M8	30,88 €
PCS75-19H-35K	19	115,75	123,30	80	35	35	10	3,30	M8	30,88 €
PCS75-19H-38K						38	10	3,30	M8	30,88 €
PCS75-19H-40K						40	12	3,30	M10	30,88 €
PCS75-19H-42K						42	12	3,30	M10	30,88 €
PCS75-19H-45K						45	14	3,80	M12	30,88 €
PCS75-20H-25K						25	8	3,30	M6	31,83 €
PCS75-20H-28K						28	8	3,30	M6	32,68 €
PCS75-20H-30K						30	8	3,30	M6	32,68 €
PCS75-20H-32K						32	10	3,30	M8	32,68 €
PCS75-20H-35K	20	121,78	129,70	80	35	35	10	3,30	M8	32,68 €
PCS75-20H-38K						38	10	3,30	M8	32,68 €
PCS75-20H-40K						40	12	3,30	M10	32,68 €
PCS75-20H-42K						42	12	3,30	M10	32,68 €
PCS75-20H-45K						45	14	3,80	M12	32,68 €

All dimensions in mm

DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-12%	-25%	On request

Part Number	Z Teeth	ØP	ØD	ØM	E	ØA	K (H9)	T2	ØT	Price each 1 to 5
PCS75-21H-28K	21	127,82	135,40	90	40	28	8	3,30	M6	38,65 €
PCS75-21H-30K						30	8	3,30	M6	38,65 €
PCS75-21H-32K						32	10	3,30	M8	38,65 €
PCS75-21H-35K						35	10	3,30	M8	38,65 €
PCS75-21H-38K						38	10	3,30	M8	38,65 €
PCS75-21H-40K						40	12	3,30	M10	38,65 €
PCS75-21H-42K						42	12	3,30	M10	38,65 €
PCS75-21H-45K						45	14	3,80	M12	38,65 €
PCS75-21H-48K						48	14	3,80	M12	38,65 €
PCS75-21H-50K						50	14	3,80	M12	38,65 €
PCS75-23H-28K	23	139,90	147,40	90	40	28	8	3,30	M6	44,15 €
PCS75-23H-30K						30	8	3,30	M6	44,15 €
PCS75-23H-32K						32	10	3,30	M8	44,15 €
PCS75-23H-35K						35	10	3,30	M8	44,15 €
PCS75-23H-38K						38	10	3,30	M8	44,15 €
PCS75-23H-40K						40	12	3,30	M10	44,15 €
PCS75-23H-42K						42	12	3,30	M10	44,15 €
PCS75-23H-45K						45	14	3,80	M12	44,15 €
PCS75-23H-48K						48	14	3,80	M12	44,15 €
PCS75-23H-50K						50	14	3,80	M12	44,15 €
PCS75-24H-28K	24	145,94	154,10	90	40	28	8	3,30	M6	44,76 €
PCS75-24H-30K						30	8	3,30	M6	44,76 €
PCS75-24H-32K						32	10	3,30	M8	44,76 €
PCS75-24H-35K						35	10	3,30	M8	44,76 €
PCS75-24H-38K						38	10	3,30	M8	44,76 €
PCS75-24H-40K						40	12	3,30	M10	44,76 €
PCS75-24H-42K						42	12	3,30	M10	44,76 €
PCS75-24H-45K						45	14	3,80	M12	44,76 €
PCS75-24H-48K						48	14	3,80	M12	44,76 €
PCS75-24H-50K						50	14	3,80	M12	44,76 €
PCS75-25H-28K	25	152,00	159,50	90	40	28	8	3,30	M6	47,53 €
PCS75-25H-30K						30	8	3,30	M6	47,53 €
PCS75-25H-32K						32	10	3,30	M8	47,53 €
PCS75-25H-35K						35	10	3,30	M8	47,53 €
PCS75-25H-38K						38	10	3,30	M8	47,53 €
PCS75-25H-40K						40	12	3,30	M10	47,53 €
PCS75-25H-42K						42	12	3,30	M10	47,53 €
PCS75-25H-45K						45	14	3,80	M12	47,53 €
PCS75-25H-48K						48	14	3,80	M12	47,53 €
PCS75-25H-50K						50	14	3,80	M12	47,53 €

All dimensions in mm